



CoreLine Wall-mounted – the clear choice for LED

CoreLine Wall-mounted

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Wall-mounted range of LED products can be used to replace traditional wall-mounted luminaires incorporating compact fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Benefits

- Up to 55% energy savings compared with luminaires with PL-C lamps
- Direct replacement for traditional wall-mounted luminaires
- Complete range covering all application requirements in one product (light levels, IP65, IK10, certified emergency lighting, built-in controls)

Features

- Unobtrusive design
- Three lumen packages replacing traditional wall-mounted luminaires with 1x18 W / 2x18 W / 2x26 W PL-C
- Water- and vandal-proof as standard
- Phase-cut dimming as standard
- Frosted diffuser ensuring homogeneous light effect and visual comfort
- Optional emergency lighting
- Optional on/off movement detection or programmed 100%-10%-0% corridor dimming functionality

CoreLine Wall-mounted

Application

- Corridors
- Staircases
- Public entrance areas
- Bathrooms
- Emergency exits
- Parking garages
- Outdoor safety lighting

Warnings and Safety


- For outdoor operations; wall-mounted applications only and all cables should run indoors with a maximum distance of 10 meters

Versions



CoreLine wall-mounted WL140V All-in

Dimensional drawing



CoreLine Wall-mounted

Product details



CoreLine Wall-mounted WL140V
Rim Black



CoreLine Wall-mounted WL140V
Rim Grey



CoreLine Wall-mounted WL140V
Wall-mounted Black



CoreLine Wall-mounted WL140V
Wall-mounted PSU



CoreLine Wall-mounted WL140V
Ceiling-mounted Grey



CoreLine Wall-mounted WL140V
Ceiling-mounted Black



CoreLine Wall-mounted WL140V
Wall-mounted White with Half-
moon Accessory



CoreLine Wall-mounted WL140V
Wall-mounted Grey with Half-
moon Accessory

CoreLine Wall-mounted

Product details



Coreline Wall-mounted WL140V
Top View (with screw locations)



CoreLine Wall-mounted WL140V
Wall-mounted Switchable Lumen
& CCT



CoreLine Wall-mounted WL140V
Half-moon Accessory Black



CoreLine Wall-mounted WL140V
Half-moon Accessory Grey



CoreLine Wall-mounted WL140V
Ceiling-mounted



CoreLine Wall-mounted WL140V
Wall-mounted PSR MDU



CoreLine Wall-mounted WL140V
Wall-mounted Grey



CoreLine Wall-mounted WL140V
Half-moon Accessory White

CoreLine Wall-mounted

Product details



Coreline Wall-mounted WL140V
Top View

General Information	
Driver included	Yes
Number of gear units	1 unit
Light Technical	
Color rendering index (CRI)	>80
Optic type	Symmetrical
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Suitable for random switching	No
Mechanical and Housing	
Mech. impact protection code	IK10
Ingress protection code	IP65
Approval and Application	
CE mark	Yes
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Light source replaceable
52879699	WL140V LED12_20S/827_830_840 PSU WH	Yes
52880299	WL140V LED20_34S/827_830_840 PSU WH	Yes
30713299	WL140V 14_24_40S/827_830_840 PSU WH	-
30714999	WL140V 14_24_40S/827_830_840 PSU MDU WH	-
30715699	WL140V 14_24_40S/827_830_840 PSR MDU WH	-
30716399	WL140V 40S/827_830_840 PSED WH	-
30717099	WL140V 40S/827_830_840 WIA WH	-
97853200	WL140V LED20S/840 PSED WH	No
52871099	WL140V LED12S/830 PSU WH	Yes
52872799	WL140V LED12S/840 PSU WH	Yes
52873499	WL140V LED20S/830 PSU WH	Yes
52874199	WL140V LED20S/840 PSU WH	Yes
52875899	WL140V LED34S/830 PSU WH	Yes
52876599	WL140V LED34S/840 PSU WH	Yes
52877299	WL140V LED20S/830 PSU MDU WH	Yes
52878999	WL140V LED20S/840 PSU MDU WH	Yes
53082999	WL140V LED12S/830 PSR MDU WH	Yes
53083699	WL140V LED12S/840 PSR MDU WH	Yes
53084399	WL140V LED20S/830 PSR MDU WH	Yes
53085099	WL140V LED20S/840 PSR MDU WH	Yes
53086799	WL140V LED34S/830 PSR MDU WH	Yes
53087499	WL140V LED34S/840 PSR MDU WH	Yes

Light Technical (1/2)

Order Code	Full Product Name	All-in Type	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
52879699	WL140V LED12_20S/827_830_840 PSU WH	All-in, Multi Lumen	120 degree(s)	2700 K	100 lm/W
52880299	WL140V LED20_34S/827_830_840 PSU WH	All-in, Multi Lumen	120 degree(s)	2700 K	100 lm/W

Order Code	Full Product Name	All-in Type	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
30713299	WL140V 14_24_40S/827_830_840 PSU WH	All-in, Multi Color Temperature	-	2700 K	140 lm/W

CoreLine Wall-mounted

Order Code	Full Product Name	All-in Type	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
30714999	WL140V 14_24_40S/827_830_840 PSU MDU WH	All-in, Multi Color Temperature	-	2700 K	135 lm/W
30715699	WL140V 14_24_40S/827_830_840 PSR MDU WH	All-in, Multi Color Temperature	-	2700 K	135 lm/W
30716399	WL140V 40S/827_830_840 PSED WH	All-in, Multi Color Temperature	-	2700 K	140 lm/W
30717099	WL140V 40S/827_830_840 WIA WH	All-in, Multi Color Temperature	-	2700 K	140 lm/W
97853200	WL140V LED20S/840 PSED WH	-	120 degree(s)	4000 K	100 lm/W
52871099	WL140V LED12S/830 PSU WH	-	120 degree(s)	3000 K	105 lm/W
52872799	WL140V LED12S/840 PSU WH	-	120 degree(s)	4000 K	110 lm/W
52873499	WL140V LED20S/830 PSU WH	-	120 degree(s)	3000 K	105 lm/W
52874199	WL140V LED20S/840 PSU WH	-	120 degree(s)	4000 K	110 lm/W
52875899	WL140V LED34S/830 PSU WH	-	120 degree(s)	3000 K	105 lm/W

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux
52879699	WL140V LED12_20S/827_830_840 PSU WH	1,200 lm
52880299	WL140V LED20_34S/827_830_840 PSU WH	2,000 lm
30713299	WL140V 14_24_40S/827_830_840 PSU WH	1,400 lm
30714999	WL140V 14_24_40S/827_830_840 PSU MDU WH	1,400 lm
30715699	WL140V 14_24_40S/827_830_840 PSR MDU WH	1,400 lm
30716399	WL140V 40S/827_830_840 PSED WH	4,050 lm
30717099	WL140V 40S/827_830_840 WIA WH	4,050 lm
97853200	WL140V LED20S/840 PSED WH	2,200 lm
52871099	WL140V LED12S/830 PSU WH	1,275 lm
52872799	WL140V LED12S/840 PSU WH	1,350 lm
52873499	WL140V LED20S/830 PSU WH	2,100 lm

Order Code	Full Product Name	All-in Type	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
52876599	WL140V LED34S/840 PSU WH	-	120 degree(s)	4000 K	110 lm/W
52877299	WL140V LED20S/830 PSU MDU WH	-	120 degree(s)	3000 K	95 lm/W
52878999	WL140V LED20S/840 PSU MDU WH	-	120 degree(s)	4000 K	100 lm/W
53082999	WL140V LED12S/830 PSR MDU WH	-	120 degree(s)	3000 K	90 lm/W
53083699	WL140V LED12S/840 PSR MDU WH	-	120 degree(s)	4000 K	95 lm/W
53084399	WL140V LED20S/830 PSR MDU WH	-	120 degree(s)	3000 K	90 lm/W
53085099	WL140V LED20S/840 PSR MDU WH	-	120 degree(s)	4000 K	95 lm/W
53086799	WL140V LED34S/830 PSR MDU WH	-	120 degree(s)	3000 K	98 lm/W
53087499	WL140V LED34S/840 PSR MDU WH	-	120 degree(s)	4000 K	103 lm/W

Order Code	Full Product Name	Luminous Flux
52874199	WL140V LED20S/840 PSU WH	2,200 lm
52875899	WL140V LED34S/830 PSU WH	3,400 lm
52876599	WL140V LED34S/840 PSU WH	3,550 lm
52877299	WL140V LED20S/830 PSU MDU WH	1,850 lm
52878999	WL140V LED20S/840 PSU MDU WH	1,950 lm
53082999	WL140V LED12S/830 PSR MDU WH	1,200 lm
53083699	WL140V LED12S/840 PSR MDU WH	1,250 lm
53084399	WL140V LED20S/830 PSR MDU WH	2,100 lm
53085099	WL140V LED20S/840 PSR MDU WH	2,200 lm
53086799	WL140V LED34S/830 PSR MDU WH	2,950 lm
53087499	WL140V LED34S/840 PSR MDU WH	3,100 lm

Operating and Electrical

CoreLine Wall-mounted

Order Code	Full Product Name	Power Consumption
52879699	WL140V LED12_20S/827_830_840 PSU WH	20 W
52880299	WL140V LED20_34S/827_830_840 PSU WH	33 W
30713299	WL140V 14_24_40S/827_830_840 PSU WH	29 W
30714999	WL140V 14_24_40S/827_830_840 PSU MDU WH	30 W
30715699	WL140V 14_24_40S/827_830_840 PSR MDU WH	30 W
30716399	WL140V 40S/827_830_840 PSED WH	29 W
30717099	WL140V 40S/827_830_840 WIA WH	29 W
97853200	WL140V LED20S/840 PSED WH	22 W
52871099	WL140V LED12S/830 PSU WH	12 W
52872799	WL140V LED12S/840 PSU WH	12 W
52873499	WL140V LED20S/830 PSU WH	20 W

Order Code	Full Product Name	Power Consumption
52874199	WL140V LED20S/840 PSU WH	20 W
52875899	WL140V LED34S/830 PSU WH	32 W
52876599	WL140V LED34S/840 PSU WH	32 W
52877299	WL140V LED20S/830 PSU MDU WH	19 W
52878999	WL140V LED20S/840 PSU MDU WH	19 W
53082999	WL140V LED12S/830 PSR MDU WH	13 W
53083699	WL140V LED12S/840 PSR MDU WH	13 W
53084399	WL140V LED20S/830 PSR MDU WH	23 W
53085099	WL140V LED20S/840 PSR MDU WH	23 W
53086799	WL140V LED34S/830 PSR MDU WH	30 W
53087499	WL140V LED34S/840 PSR MDU WH	30 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
52879699	WL140V LED12_20S/827_830_840 PSU WH	No	-	Not applicable
52880299	WL140V LED20_34S/827_830_840 PSU WH	No	-	Not applicable
30713299	WL140V 14_24_40S/827_830_840 PSU WH	No	-	-
30714999	WL140V 14_24_40S/827_830_840 PSU MDU WH	Yes	-	-
30715699	WL140V 14_24_40S/827_830_840 PSR MDU WH	Yes	-	-
30716399	WL140V 40S/827_830_840 PSED WH	Yes	-	-
30717099	WL140V 40S/827_830_840 WIA WH	Yes	-	-
97853200	WL140V LED20S/840 PSED WH	Yes	-	1%
52871099	WL140V LED12S/830 PSU WH	No	-	Not applicable
52872799	WL140V LED12S/840 PSU WH	No	-	Not applicable
52873499	WL140V LED20S/830 PSU WH	No	-	Not applicable
52874199	WL140V LED20S/840 PSU WH	No	-	Not applicable
52875899	WL140V LED34S/830 PSU WH	No	-	Not applicable
52876599	WL140V LED34S/840 PSU WH	No	-	Not applicable

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
52877299	WL140V LED20S/830 PSU MDU WH	Yes	Programmable movement and light sensor	Not applicable
52878999	WL140V LED20S/840 PSU MDU WH	Yes	Programmable movement and light sensor	Not applicable
53082999	WL140V LED12S/830 PSR MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%
53083699	WL140V LED12S/840 PSR MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%
53084399	WL140V LED20S/830 PSR MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%
53085099	WL140V LED20S/840 PSR MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%
53086799	WL140V LED34S/830 PSR MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%
53087499	WL140V LED34S/840 PSR MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%

Mechanical and Housing

Order Code	Full Product Name	Housing Color
52879699	WL140V LED12_20S/827_830_840 PSU WH	White

Order Code	Full Product Name	Housing Color
52880299	WL140V LED20_34S/827_830_840 PSU WH	White

CoreLine Wall-mounted

Order Code	Full Product Name	Housing Color
30713299	WL140V 14_24_40S/827_830_840 PSU WH	White RAL 9003
30714999	WL140V 14_24_40S/827_830_840 PSU MDU WH	White RAL 9003
30715699	WL140V 14_24_40S/827_830_840 PSR MDU WH	White RAL 9003
30716399	WL140V 40S/827_830_840 PSED WH	White RAL 9003
30717099	WL140V 40S/827_830_840 WIA WH	White RAL 9003
97853200	WL140V LED20S/840 PSED WH	White
52871099	WL140V LED12S/830 PSU WH	White
52872799	WL140V LED12S/840 PSU WH	White
52873499	WL140V LED20S/830 PSU WH	White
52874199	WL140V LED20S/840 PSU WH	White

Order Code	Full Product Name	Housing Color
52875899	WL140V LED34S/830 PSU WH	White
52876599	WL140V LED34S/840 PSU WH	White
52877299	WL140V LED20S/830 PSU MDU WH	White
52878999	WL140V LED20S/840 PSU MDU WH	White
53082999	WL140V LED12S/830 PSR MDU WH	White
53083699	WL140V LED12S/840 PSR MDU WH	White
53084399	WL140V LED20S/830 PSR MDU WH	White
53085099	WL140V LED20S/840 PSR MDU WH	White
53086799	WL140V LED34S/830 PSR MDU WH	White
53087499	WL140V LED34S/840 PSR MDU WH	White

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Power consumption during Central DC emergency mode
52879699	WL140V LED12_20S/827_830_840 PSU WH	-	-	-	-
52880299	WL140V LED20_34S/827_830_840 PSU WH	-	-	-	-
30713299	WL140V 14_24_40S/827_830_840 PSU WH	No	-	-	-
30714999	WL140V 14_24_40S/827_830_840 PSU MDU WH	No	-	-	-
30715699	WL140V 14_24_40S/827_830_840 PSR MDU WH	No	-	-	-
30716399	WL140V 40S/827_830_840 PSED WH	Yes	DC operated central emergency lighting	-	-
30717099	WL140V 40S/827_830_840 WIA WH	No	-	-	-
97853200	WL140V LED20S/840 PSED WH	Yes	DC operated central emergency lighting	350 lm	3 W

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Power consumption during Central DC emergency mode
52871099	WL140V LED12S/830 PSU WH	-	-	-	-
52872799	WL140V LED12S/840 PSU WH	-	-	-	-
52873499	WL140V LED20S/830 PSU WH	-	-	-	-
52874199	WL140V LED20S/840 PSU WH	-	-	-	-
52875899	WL140V LED34S/830 PSU WH	-	-	-	-
52876599	WL140V LED34S/840 PSU WH	-	-	-	-
52877299	WL140V LED20S/830 PSU MDU WH	-	-	-	-
52878999	WL140V LED20S/840 PSU MDU WH	-	-	-	-
53082999	WL140V LED12S/830 PSR MDU WH	-	-	-	-
53083699	WL140V LED12S/840 PSR MDU WH	-	-	-	-
53084399	WL140V LED20S/830 PSR MDU WH	-	-	-	-

CoreLine Wall-mounted

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Power consumption during Central DC emergency mode
53085099	WL140V LED20S/840 PSR MDU WH	-	-	-	-
53086799	WL140V LED34S/830 PSR MDU WH	-	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Power consumption during Central DC emergency mode
53087499	WL140V LED34S/840 PSR MDU WH	-	-	-	-

Approval and Application (1/2)

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3
52879699	WL140V LED12_20S/ 827_830_840 PSU WH	-20 to +40 °C	ENEC mark	-	1
52880299	WL140V LED20_34S/ 827_830_840 PSU WH	-20 to +40 °C	ENEC mark	-	1
30713299	WL140V 14_24_40S/ 827_830_840 PSU WH	-20 to +40 °C	ENEC mark	For mounting on normally flammable surfaces	-
30714999	WL140V 14_24_40S/ 827_830_840 PSU MDU WH	-20 to +40 °C	ENEC mark	For mounting on normally flammable surfaces	-
30715699	WL140V 14_24_40S/ 827_830_840 PSR MDU WH	-20 to +40 °C	ENEC mark	For mounting on normally flammable surfaces	-
30716399	WL140V 40S/ 827_830_840 PSED WH	-20 to +40 °C	ENEC mark	For mounting on normally flammable surfaces	-
30717099	WL140V 40S/ 827_830_840 WIA WH	-20 to +40 °C	ENEC mark	For mounting on normally flammable surfaces	-
97853200	WL140V LED20S/840 PSED WH	0 to +25 °C	-	-	1

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3
52871099	WL140V LED12S/830 PSU WH	-20 to +40 °C	ENEC mark	-	1
52872799	WL140V LED12S/840 PSU WH	-20 to +40 °C	ENEC mark	-	1
52873499	WL140V LED20S/830 PSU WH	-20 to +40 °C	ENEC mark	-	1
52874199	WL140V LED20S/840 PSU WH	-20 to +40 °C	ENEC mark	-	1
52875899	WL140V LED34S/830 PSU WH	-20 to +40 °C	ENEC mark	-	1
52876599	WL140V LED34S/840 PSU WH	-20 to +40 °C	ENEC mark	-	1
52877299	WL140V LED20S/830 PSU MDU WH	-20 to +40 °C	ENEC mark	-	1
52878999	WL140V LED20S/840 PSU MDU WH	-20 to +40 °C	ENEC mark	-	1
53082999	WL140V LED12S/830 PSR MDU WH	-20 to +40 °C	ENEC mark	-	1
53083699	WL140V LED12S/840 PSR MDU WH	-20 to +40 °C	ENEC mark	-	1

CoreLine Wall-mounted

					Flickering value (PstLM) - Flickering value as per
Order	Full Product	Ambient	ENEC	Flammability	EN
Code	Name	temperature range	mark	mark	61000-3-3
53084399	WL140V	-20 to +40 °C	ENEC	-	1
	LED20S/830 PSR		mark		
	MDU WH				
53085099	WL140V	-20 to +40 °C	ENEC	-	1
	LED20S/840 PSR		mark		
	MDU WH				

					Flickering value (PstLM) - Flickering value as per
Order	Full Product	Ambient			
Code	Name	temperature range	ENEC mark	Flammability mark	EN 61000-3-3
53086799	WL140V	-20 to +40 °C	ENEC	-	1
	LED34S/830 PSR		mark		
	MDU WH				
53087499	WL140V	-20 to +40 °C	ENEC	-	1
	LED34S/840 PSR		mark		
	MDU WH				

Approval and Application (2/2)

Order Code	Full Product Name	Stroboscopic effect visibility measure (SVM)
52879699	WL140V LED12_20S/827_830_840 PSU WH	1.6
52880299	WL140V LED20_34S/827_830_840 PSU WH	1.6
30713299	WL140V 14_24_40S/827_830_840 PSU WH	0.4
30714999	WL140V 14_24_40S/827_830_840 PSU MDU WH	0.4
30715699	WL140V 14_24_40S/827_830_840 PSR MDU WH	0.4
30716399	WL140V 40S/827_830_840 PSED WH	0.4
30717099	WL140V 40S/827_830_840 WIA WH	0.4
97853200	WL140V LED20S/840 PSED WH	1.6
52871099	WL140V LED12S/830 PSU WH	1.6
52872799	WL140V LED12S/840 PSU WH	1.6
52873499	WL140V LED20S/830 PSU WH	1.6

Order Code	Full Product Name	Stroboscopic effect visibility measure (SVM)
52874199	WL140V LED20S/840 PSU WH	1.6
52875899	WL140V LED34S/830 PSU WH	1.6
52876599	WL140V LED34S/840 PSU WH	1.6
52877299	WL140V LED20S/830 PSU MDU WH	1.6
52878999	WL140V LED20S/840 PSU MDU WH	1.6
53082999	WL140V LED12S/830 PSR MDU WH	1.6
53083699	WL140V LED12S/840 PSR MDU WH	1.6
53084399	WL140V LED20S/830 PSR MDU WH	1.6
53085099	WL140V LED20S/840 PSR MDU WH	1.6
53086799	WL140V LED34S/830 PSR MDU WH	1.6
53087499	WL140V LED34S/840 PSR MDU WH	1.6

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
52879699	WL140V LED12_20S/827_830_840 PSU WH	(0.3818,0.3797) SDCM <5
	WH	
52880299	WL140V LED20_34S/827_830_840 PSU WH	(0.3818,0.3797) SDCM <5
	WH	
30713299	WL140V 14_24_40S/827_830_840 PSU WH	(0.46,0.42) SDCM<3; (0.43,0.40) SDCM<5; (0.38,0.38) SDCM<5
	WH	
30714999	WL140V 14_24_40S/827_830_840 PSU MDU WH	(0.46,0.42) SDCM<3; (0.43,0.40) SDCM<5; (0.38,0.38) SDCM<5
	MDU WH	
30715699	WL140V 14_24_40S/827_830_840 PSR MDU WH	(0.46,0.42) SDCM<3; (0.43,0.40) SDCM<5; (0.38,0.38) SDCM<5
	MDU WH	
30716399	WL140V 40S/827_830_840 PSED WH	(0.46,0.42) SDCM<3; (0.43,0.40) SDCM<5; (0.38,0.38) SDCM<5
	WH	
30717099	WL140V 40S/827_830_840 WIA WH	(0.46,0.42) SDCM<3; (0.43,0.40) SDCM<5; (0.38,0.38) SDCM<5
	WH	
97853200	WL140V LED20S/840 PSED WH	(0.3818,0.3797) SDCM <3

Order Code	Full Product Name	Initial chromaticity
52871099	WL140V LED12S/830 PSU WH	(0.4338,0.4030) SDCM <3
52872799	WL140V LED12S/840 PSU WH	(0.3818,0.3797) SDCM <3
52873499	WL140V LED20S/830 PSU WH	(0.4338,0.4030) SDCM <3
52874199	WL140V LED20S/840 PSU WH	(0.3818,0.3797) SDCM <3
52875899	WL140V LED34S/830 PSU WH	(0.4338,0.4030) SDCM <3
52876599	WL140V LED34S/840 PSU WH	(0.3818,0.3797) SDCM <3
52877299	WL140V LED20S/830 PSU MDU WH	(0.4338,0.4030) SDCM <3
52878999	WL140V LED20S/840 PSU MDU WH	(0.3818,0.3797) SDCM <3
53082999	WL140V LED12S/830 PSR MDU WH	(0.4338,0.4030) SDCM <3
53083699	WL140V LED12S/840 PSR MDU WH	(0.3818,0.3797) SDCM <3
53084399	WL140V LED20S/830 PSR MDU WH	(0.4338,0.4030) SDCM <3
53085099	WL140V LED20S/840 PSR MDU WH	(0.3818,0.3797) SDCM <3
53086799	WL140V LED34S/830 PSR MDU WH	(0.4338,0.4030) SDCM <3
53087499	WL140V LED34S/840 PSR MDU WH	(0.3818,0.3797) SDCM <3




Product Data

CoreLine Wall-mounted

Order Code	Full Product Name	Product family code
52879699	WL140V LED12_20S/827_830_840 PSU WH	-
52880299	WL140V LED20_34S/827_830_840 PSU WH	-
30713299	WL140V 14_24_40S/827_830_840 PSU WH	-
30714999	WL140V 14_24_40S/827_830_840 PSU MDU WH	-
30715699	WL140V 14_24_40S/827_830_840 PSR MDU WH	-
30716399	WL140V 40S/827_830_840 PSED WH	-
30717099	WL140V 40S/827_830_840 WIA WH	-
97853200	WL140V LED20S/840 PSED WH	WL140V
52871099	WL140V LED12S/830 PSU WH	-
52872799	WL140V LED12S/840 PSU WH	-
52873499	WL140V LED20S/830 PSU WH	-

Order Code	Full Product Name	Product family code
52874199	WL140V LED20S/840 PSU WH	-
52875899	WL140V LED34S/830 PSU WH	-
52876599	WL140V LED34S/840 PSU WH	-
52877299	WL140V LED20S/830 PSU MDU WH	-
52878999	WL140V LED20S/840 PSU MDU WH	-
53082999	WL140V LED12S/830 PSR MDU WH	-
53083699	WL140V LED12S/840 PSR MDU WH	-
53084399	WL140V LED20S/830 PSR MDU WH	-
53085099	WL140V LED20S/840 PSR MDU WH	-
53086799	WL140V LED34S/830 PSR MDU WH	-
53087499	WL140V LED34S/840 PSR MDU WH	-



Polar Wide Diagrams



Polar Normal (separate) - WL140VI - 910505101539




Polar Normal (separate) - null - 911401874087

Polar Normal (separate) - null - 911401873787



Polar Normal (separate) - null - 911401873887

Polar Normal (separate) - null - 911401873987




Polar Normal (separate) - null - 911401873687

Polar Normal (separate) - null - 911401851882



Polar Normal (separate) - null - 911401852082

Polar Wide Diagrams



CoreLine Wall-mounted

Polar Wide Diagrams



Polar Normal (separate) - null - 911401851782

Polar Normal (separate) - null - 911401851982

