



CoreLine wall-mounted – For every project, where light really matters. Suits your specific application.

CoreLine Wall-mounted

CoreLine wall-mounted solutions deliver on the CoreLine promise of innovative, easy-to-install and high-quality luminaires. These circular-shaped, surface-mounted luminaires are suitable for both ceiling and wall installations and are easy to apply in circulation areas such as corridors, hallways and staircases. The modern, unobtrusive design, combined with a homogeneous light distribution, ensures this luminaire will blend into the architecture of most buildings. All-in features provide up to three lumen packages and three color temperature options in one luminaire. Installers can easily fit the luminaire according to the application need on site. And thanks to the push-in connectors, installation of the CoreLine WL140V is fast and straightforward. This family includes Interact ready luminaires with integrated wireless communications, ready for use with Interact gateways, sensors and software.

CoreLine Wall-mounted

Benefits

- Delivers the right lighting settings for various applications
- Easy installation with push-in connectors and through wiring possibility
- Slim and unobtrusive design in black or grey, plus half-moon (eye-lid) accessories
- One product serves multi-functional purposes with dipswitch settings
- Direct replacement for traditional wall-mounted luminaires
- Water and vandal-proof as standard
- Emergency ready

Features

- High efficacy up to 140lm/W
- Three lumen packages and three-color temperatures to cater for diverse applications
- Choice of drivers: DALI with DC compatible, wireless with Interact ready
- Compatible emergency lighting kit (incl. self-test) available for self-installation
- IP65/IK10 as standard
- Optional motion detection, including daylight sensing, dimming and wireless grouping function with MDU


Application

- Offices
- Municipal Buildings
- Parking Garages
- Corridors
- Staircases
- Outdoor safety lighting

Warnings and Safety

- For outdoor operations; wall-mounted applications only and all cables should run indoors with a maximum distance of 10 meters

Dimensional drawing



CoreLine Wall-mounted

Product details



CoreLine Wall-mounted WL140V
Rim Black



CoreLine Wall-mounted WL140V
Rim Grey



CoreLine Wall-mounted WL140V
Wall-mounted Black



CoreLine Wall-mounted WL140V
Wall-mounted PSU



CoreLine Wall-mounted WL140V
Ceiling-mounted Grey



CoreLine Wall-mounted WL140V
Ceiling-mounted Black



CoreLine Wall-mounted WL140V
Wall-mounted White with Half-
moon Accessory



CoreLine Wall-mounted WL140V
Wall-mounted Grey with Half-
moon Accessory

CoreLine Wall-mounted

Product details



Coreline Wall-mounted WL140V
Top View (with screw locations)



CoreLine Wall-mounted WL140V
Wall-mounted Switchable Lumen
& CCT



CoreLine Wall-mounted WL140V
Half-moon Accessory Black



CoreLine Wall-mounted WL140V
Half-moon Accessory Grey



CoreLine Wall-mounted WL140V
Ceiling-mounted



CoreLine Wall-mounted WL140V
Wall-mounted PSR MDU



CoreLine Wall-mounted WL140V
Wall-mounted Grey



CoreLine Wall-mounted WL140V
Half-moon Accessory White

CoreLine Wall-mounted

Product details



Coreline Wall-mounted WL140V
Top View

General Information	
Driver included	Yes
Number of gear units	1 unit
Light Technical	
Color rendering index (CRI)	>80
Optic type	Symmetrical
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Mechanical and Housing	
Mech. impact protection code	IK10
Ingress protection code	IP65
Approval and Application	
CE mark	Yes
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Light source replaceable
911401848182	WL140V LED12_20S/827_830_840 PSU WH	Yes
911401848282	WL140V LED20_34S/827_830_840 PSU WH	Yes
911401873687	WL140V 14_24_40S/827_830_840 PSU WH	-
911401873787	WL140V 14_24_40S/827_830_840 PSU MDU WH	-
911401873887	WL140V 14_24_40S/827_830_840 PSR MDU WH	-
911401873987	WL140V 40S/827_830_840 PSED WH	-
911401874087	WL140V 40S/827_830_840 WIA WH	-
910505101534	WL140V LED12S/830 PSED WH	No
910505101535	WL140V LED12S/840 PSED WH	No
910505101538	WL140V LED20S/830 PSED WH	No
910505101539	WL140V LED20S/840 PSED WH	No
910505101542	WL140V LED34S/830 PSED WH	No
910505101543	WL140V LED34S/840 PSED WH	No
910505101546	WL140V LED20S/830 WIA WH	No
910505101547	WL140V LED20S/840 WIA WH	No
910505101548	WL140V LED34S/830 WIA WH	No
910505101549	WL140V LED34S/840 WIA WH	No
910505101550	WL140V LED12S/830 PSED ELB3 WH	No
910505101551	WL140V LED12S/840 PSED ELB3 WH	No
910505101552	WL140V LED12S/830 PSR ELB3 MDU WH	No
910505101553	WL140V LED12S/840 PSR ELB3 MDU WH	No
910505101554	WL140V LED20S/830 PSED ELB3 WH	No
910505101555	WL140V LED20S/840 PSED ELB3 WH	No
910505101556	WL140V LED20S/830 PSR ELB3 MDU WH	No
910505101557	WL140V LED20S/840 PSR ELB3 MDU WH	No
910505101558	WL140V LED34S/830 PSED ELB3 WH	No
910505101559	WL140V LED34S/840 PSED ELB3 WH	No
910505101560	WL140V LED34S/830 PSR ELB3 MDU WH	No
910505101561	WL140V LED34S/840 PSR ELB3 MDU WH	No
910505101562	WL140V LED20S/830 WIA ELB3 WH	No
910505101563	WL140V LED20S/840 WIA ELB3 WH	No
910505101564	WL140V LED34S/830 WIA ELB3 WH	No
910505101565	WL140V LED34S/840 WIA ELB3 WH	No
911401847482	WL140V LED12S/840 PSU WH	Yes
911401847582	WL140V LED20S/830 PSU WH	Yes
911401847682	WL140V LED20S/840 PSU WH	Yes
911401847782	WL140V LED34S/830 PSU WH	Yes

CoreLine Wall-mounted

Order Code	Full Product Name	Light source replaceable
911401847882	WL140V LED34S/840 PSU WH	Yes
911401847982	WL140V LED20S/830 PSU MDU WH	Yes
911401851582	WL140V LED12S/830 PSR MDU WH	Yes
911401851682	WL140V LED12S/840 PSR MDU WH	Yes
911401851782	WL140V LED20S/830 PSR MDU WH	Yes
911401851882	WL140V LED20S/840 PSR MDU WH	Yes
911401851982	WL140V LED34S/830 PSR MDU WH	Yes

Light Technical (1/2)

Order Code	Full Product Name	All-in Type	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
911401848182	WL140V LED12_20S/827_830_840 PSU WH	All-in, Multi Lumen	120 degree(s)	2700 K	100 lm/W
911401848282	WL140V LED20_34S/827_830_840 PSU WH	All-in, Multi Lumen	120 degree(s)	2700 K	100 lm/W
911401873687	WL140V 14_24_40S/827_830_840 PSU WH	All-in, Multi Color Temperature	-	2700 K	140 lm/W
911401873787	WL140V 14_24_40S/827_830_840 PSU MDU WH	All-in, Multi Color Temperature	-	2700 K	135 lm/W
911401873887	WL140V 14_24_40S/827_830_840 PSR MDU WH	All-in, Multi Color Temperature	-	2700 K	135 lm/W
911401873987	WL140V 40S/827_830_840 PSED WH	All-in, Multi Color Temperature	-	2700 K	140 lm/W
911401874087	WL140V 40S/827_830_840 WIA WH	All-in, Multi Color Temperature	-	2700 K	140 lm/W
910505101534	WL140V LED12S/830 PSED WH	-	120 degree(s)	3000 K	88 lm/W
910505101535	WL140V LED12S/840 PSED WH	-	120 degree(s)	4000 K	92 lm/W
910505101538	WL140V LED20S/830 PSED WH	-	120 degree(s)	3000 K	95 lm/W
910505101539	WL140V LED20S/840 PSED WH	-	120 degree(s)	4000 K	100 lm/W

Order Code	Full Product Name	All-in Type	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
910505101542	WL140V LED34S/830 PSED WH	-	120 degree(s)	3000 K	94 lm/W
910505101543	WL140V LED34S/840 PSED WH	-	120 degree(s)	4000 K	95 lm/W
910505101546	WL140V LED20S/830 WIA WH	-	120 degree(s)	3000 K	95 lm/W
910505101547	WL140V LED20S/840 WIA WH	-	120 degree(s)	4000 K	100 lm/W
910505101548	WL140V LED34S/830 WIA WH	-	120 degree(s)	3000 K	94 lm/W
910505101549	WL140V LED34S/840 WIA WH	-	120 degree(s)	4000 K	95 lm/W
910505101550	WL140V LED12S/830 PSED ELB3 WH	-	120 degree(s)	3000 K	72 lm/W
910505101551	WL140V LED12S/840 PSED ELB3 WH	-	120 degree(s)	4000 K	75 lm/W
910505101552	WL140V LED12S/830 PSR ELB3 MDU WH	-	120 degree(s)	3000 K	72 lm/W
910505101553	WL140V LED12S/840 PSR ELB3 MDU WH	-	120 degree(s)	4000 K	75 lm/W
910505101554	WL140V LED20S/830 PSED ELB3 WH	-	120 degree(s)	3000 K	84 lm/W
910505101555	WL140V LED20S/840 PSED ELB3 WH	-	120 degree(s)	4000 K	88 lm/W

CoreLine Wall-mounted

Order Code	Full Product		Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
	Name	All-in Type			
910505101556	WL140V LED20S/830 PSR ELB3 MDU WH	-	120 degree(s)	3000 K	73 lm/W
910505101557	WL140V LED20S/840 PSR ELB3 MDU WH	-	120 degree(s)	4000 K	77 lm/W
910505101558	WL140V LED34S/830 PSED ELB3 WH	-	120 degree(s)	3000 K	87 lm/W
910505101559	WL140V LED34S/840 PSED ELB3 WH	-	120 degree(s)	4000 K	88 lm/W
910505101560	WL140V LED34S/830 PSR ELB3 MDU WH	-	120 degree(s)	3000 K	76 lm/W
910505101561	WL140V LED34S/840 PSR ELB3 MDU WH	-	120 degree(s)	4000 K	80 lm/W
910505101562	WL140V LED20S/830 WIA ELB3 WH	-	120 degree(s)	3000 K	84 lm/W
910505101563	WL140V LED20S/840 WIA ELB3 WH	-	120 degree(s)	4000 K	88 lm/W
910505101564	WL140V LED34S/830 WIA ELB3 WH	-	120 degree(s)	3000 K	87 lm/W
910505101565	WL140V LED34S/840 WIA ELB3 WH	-	120 degree(s)	4000 K	88 lm/W

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux
911401848182	WL140V LED12_20S/827_830_840 PSU WH	1,200 lm
911401848282	WL140V LED20_34S/827_830_840 PSU WH	2,000 lm
911401873687	WL140V 14_24_40S/827_830_840 PSU WH	1,400 lm
911401873787	WL140V 14_24_40S/827_830_840 PSU MDU WH	1,400 lm
911401873887	WL140V 14_24_40S/827_830_840 PSR MDU WH	1,400 lm
911401873987	WL140V 40S/827_830_840 PSED WH	4,050 lm
911401874087	WL140V 40S/827_830_840 WIA WH	4,050 lm
910505101534	WL140V LED12S/830 PSED WH	1,200 lm
910505101535	WL140V LED12S/840 PSED WH	1,250 lm
910505101538	WL140V LED20S/830 PSED WH	2,100 lm
910505101539	WL140V LED20S/840 PSED WH	2,200 lm

Order Code	Full Product		Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
	Name	All-in Type			
911401847482	WL140V LED12S/840 PSU WH	-	120 degree(s)	4000 K	110 lm/W
911401847582	WL140V LED20S/830 PSU WH	-	120 degree(s)	3000 K	105 lm/W
911401847682	WL140V LED20S/840 PSU WH	-	120 degree(s)	4000 K	110 lm/W
911401847782	WL140V LED34S/830 PSU WH	-	120 degree(s)	3000 K	105 lm/W
911401847882	WL140V LED34S/840 PSU WH	-	120 degree(s)	4000 K	110 lm/W
911401847982	WL140V LED20S/830 PSU MDU WH	-	120 degree(s)	3000 K	95 lm/W
911401851582	WL140V LED12S/830 PSR MDU WH	-	120 degree(s)	3000 K	90 lm/W
911401851682	WL140V LED12S/840 PSR MDU WH	-	120 degree(s)	4000 K	95 lm/W
911401851782	WL140V LED20S/830 PSR MDU WH	-	120 degree(s)	3000 K	90 lm/W
911401851882	WL140V LED20S/840 PSR MDU WH	-	120 degree(s)	4000 K	95 lm/W
911401851982	WL140V LED34S/830 PSR MDU WH	-	120 degree(s)	3000 K	98 lm/W

Order Code	Full Product Name	Luminous Flux
910505101542	WL140V LED34S/830 PSED WH	3,350 lm
910505101543	WL140V LED34S/840 PSED WH	3,400 lm
910505101546	WL140V LED20S/830 WIA WH	2,100 lm
910505101547	WL140V LED20S/840 WIA WH	2,200 lm
910505101548	WL140V LED34S/830 WIA WH	3,350 lm
910505101549	WL140V LED34S/840 WIA WH	3,400 lm
910505101550	WL140V LED12S/830 PSED ELB3 WH	1,200 lm
910505101551	WL140V LED12S/840 PSED ELB3 WH	1,250 lm
910505101552	WL140V LED12S/830 PSR ELB3 MDU WH	1,200 lm
910505101553	WL140V LED12S/840 PSR ELB3 MDU WH	1,250 lm
910505101554	WL140V LED20S/830 PSED ELB3 WH	2,100 lm

CoreLine Wall-mounted

Order Code	Full Product Name	Luminous Flux
910505101555	WL140V LED20S/840 PSED ELB3 WH	2,200 lm
910505101556	WL140V LED20S/830 PSR ELB3 MDU WH	2,100 lm
910505101557	WL140V LED20S/840 PSR ELB3 MDU WH	2,200 lm
910505101558	WL140V LED34S/830 PSED ELB3 WH	3,350 lm
910505101559	WL140V LED34S/840 PSED ELB3 WH	3,400 lm
910505101560	WL140V LED34S/830 PSR ELB3 MDU WH	2,900 lm
910505101561	WL140V LED34S/840 PSR ELB3 MDU WH	3,100 lm
910505101562	WL140V LED20S/830 WIA ELB3 WH	2,100 lm
910505101563	WL140V LED20S/840 WIA ELB3 WH	2,200 lm
910505101564	WL140V LED34S/830 WIA ELB3 WH	3,350 lm
910505101565	WL140V LED34S/840 WIA ELB3 WH	3,400 lm

Order Code	Full Product Name	Luminous Flux
911401847482	WL140V LED12S/840 PSU WH	1,350 lm
911401847582	WL140V LED20S/830 PSU WH	2,100 lm
911401847682	WL140V LED20S/840 PSU WH	2,200 lm
911401847782	WL140V LED34S/830 PSU WH	3,400 lm
911401847882	WL140V LED34S/840 PSU WH	3,550 lm
911401847982	WL140V LED20S/830 PSU MDU WH	1,850 lm
911401851582	WL140V LED12S/830 PSR MDU WH	1,200 lm
911401851682	WL140V LED12S/840 PSR MDU WH	1,250 lm
911401851782	WL140V LED20S/830 PSR MDU WH	2,100 lm
911401851882	WL140V LED20S/840 PSR MDU WH	2,200 lm
911401851982	WL140V LED34S/830 PSR MDU WH	2,950 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Suitable for random switching
911401848182	WL140V LED12_20S/827_830_840 PSU WH	20 W	No
911401848282	WL140V LED20_34S/827_830_840 PSU WH	33 W	No
911401873687	WL140V 14_24_40S/827_830_840 PSU WH	29 W	No
911401873787	WL140V 14_24_40S/827_830_840 PSU MDU WH	30 W	No
911401873887	WL140V 14_24_40S/827_830_840 PSR MDU WH	30 W	No
911401873987	WL140V 40S/827_830_840 PSED WH	29 W	No
911401874087	WL140V 40S/827_830_840 WIA WH	29 W	No
910505101534	WL140V LED12S/830 PSED WH	13.5 W	No
910505101535	WL140V LED12S/840 PSED WH	13.5 W	No
910505101538	WL140V LED20S/830 PSED WH	22 W	No
910505101539	WL140V LED20S/840 PSED WH	22 W	No
910505101542	WL140V LED34S/830 PSED WH	35.5 W	No
910505101543	WL140V LED34S/840 PSED WH	35.5 W	No
910505101546	WL140V LED20S/830 WIA WH	22 W	No
910505101547	WL140V LED20S/840 WIA WH	22 W	No
910505101548	WL140V LED34S/830 WIA WH	35.5 W	No
910505101549	WL140V LED34S/840 WIA WH	35.5 W	No
910505101550	WL140V LED12S/830 PSED ELB3 WH	16.5 W	No
910505101551	WL140V LED12S/840 PSED ELB3 WH	16.5 W	No
910505101552	WL140V LED12S/830 PSR ELB3 MDU WH	16.5 W	Yes
910505101553	WL140V LED12S/840 PSR ELB3 MDU WH	16.5 W	Yes
910505101554	WL140V LED20S/830 PSED ELB3 WH	25 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
910505101555	WL140V LED20S/840 PSED ELB3 WH	25 W	No
910505101556	WL140V LED20S/830 PSR ELB3 MDU WH	28.5 W	Yes
910505101557	WL140V LED20S/840 PSR ELB3 MDU WH	28.5 W	Yes
910505101558	WL140V LED34S/830 PSED ELB3 WH	38.5 W	No
910505101559	WL140V LED34S/840 PSED ELB3 WH	38.5 W	No
910505101560	WL140V LED34S/830 PSR ELB3 MDU WH	38.5 W	Yes
910505101561	WL140V LED34S/840 PSR ELB3 MDU WH	38.5 W	Yes
910505101562	WL140V LED20S/830 WIA ELB3 WH	25 W	No
910505101563	WL140V LED20S/840 WIA ELB3 WH	25 W	No
910505101564	WL140V LED34S/830 WIA ELB3 WH	38.5 W	No
910505101565	WL140V LED34S/840 WIA ELB3 WH	38.5 W	No
911401847482	WL140V LED12S/840 PSU WH	12 W	No
911401847582	WL140V LED20S/830 PSU WH	20 W	No
911401847682	WL140V LED20S/840 PSU WH	20 W	No
911401847782	WL140V LED34S/830 PSU WH	32 W	No
911401847882	WL140V LED34S/840 PSU WH	32 W	No
911401847982	WL140V LED20S/830 PSU MDU WH	19 W	No
911401851582	WL140V LED12S/830 PSR MDU WH	13 W	No
911401851682	WL140V LED12S/840 PSR MDU WH	13 W	No
911401851782	WL140V LED20S/830 PSR MDU WH	23 W	No

CoreLine Wall-mounted

Order Code	Full Product Name	Power Consumption	Suitable for random switching
911401851882	WL140V LED20S/840 PSR MDU WH	23 W	No

Order Code	Full Product Name	Power Consumption	Suitable for random switching
911401851982	WL140V LED34S/830 PSR MDU WH	30 W	No

Controls and Dimming

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
911401848182	WL140V LED12_20S/827_830_840 PSU WH	No	-	Not applicable
911401848282	WL140V LED20_34S/827_830_840 PSU WH	No	-	Not applicable
911401873687	WL140V 14_24_40S/827_830_840 PSU WH	No	-	-
911401873787	WL140V 14_24_40S/827_830_840 PSU MDU WH	Yes	-	-
911401873887	WL140V 14_24_40S/827_830_840 PSR MDU WH	Yes	-	-
911401873987	WL140V 40S/827_830_840 PSED WH	Yes	-	-
911401874087	WL140V 40S/827_830_840 WIA WH	Yes	-	-
910505101534	WL140V LED12S/830 PSED WH	Yes	-	1%
910505101535	WL140V LED12S/840 PSED WH	Yes	-	1%
910505101538	WL140V LED20S/830 PSED WH	Yes	-	1%
910505101539	WL140V LED20S/840 PSED WH	Yes	-	1%
910505101542	WL140V LED34S/830 PSED WH	Yes	-	1%
910505101543	WL140V LED34S/840 PSED WH	Yes	-	1%
910505101546	WL140V LED20S/830 WIA WH	Yes	-	1%
910505101547	WL140V LED20S/840 WIA WH	Yes	-	1%
910505101548	WL140V LED34S/830 WIA WH	Yes	-	1%
910505101549	WL140V LED34S/840 WIA WH	Yes	-	1%
910505101550	WL140V LED12S/830 PSED ELB3 WH	Yes	-	1%
910505101551	WL140V LED12S/840 PSED ELB3 WH	Yes	-	1%
910505101552	WL140V LED12S/830 PSR ELB3 MDU WH	Yes	Programmable movement and light	10%

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
			sensor with wireless grouping	
910505101553	WL140V LED12S/840 PSR ELB3 MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%
910505101554	WL140V LED20S/830 PSED ELB3 WH	Yes	-	1%
910505101555	WL140V LED20S/840 PSED ELB3 WH	Yes	-	1%
910505101556	WL140V LED20S/830 PSR ELB3 MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%
910505101557	WL140V LED20S/840 PSR ELB3 MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%
910505101558	WL140V LED34S/830 PSED ELB3 WH	Yes	-	1%
910505101559	WL140V LED34S/840 PSED ELB3 WH	Yes	-	1%
910505101560	WL140V LED34S/830 PSR ELB3 MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%
910505101561	WL140V LED34S/840 PSR ELB3 MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%
910505101562	WL140V LED20S/830 WIA ELB3 WH	Yes	-	1%
910505101563	WL140V LED20S/840 WIA ELB3 WH	Yes	-	1%
910505101564	WL140V LED34S/830 WIA ELB3 WH	Yes	-	1%
910505101565	WL140V LED34S/840 WIA ELB3 WH	Yes	-	1%
911401847482	WL140V LED12S/840 PSU WH	No	-	Not applicable
911401847582	WL140V LED20S/830 PSU WH	No	-	Not applicable

CoreLine Wall-mounted

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
911401847682	WL140V LED20S/840 PSU WH	No	-	Not applicable
911401847782	WL140V LED34S/830 PSU WH	No	-	Not applicable
911401847882	WL140V LED34S/840 PSU WH	No	-	Not applicable
911401847982	WL140V LED20S/830 PSU MDU WH	Yes	Programmable movement and light sensor	Not applicable
911401851582	WL140V LED12S/830 PSR MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%
911401851682	WL140V LED12S/840 PSR MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%

Mechanical and Housing

Order Code	Full Product Name	Housing Color
911401848182	WL140V LED12_20S/827_830_840 PSU WH	White
911401848282	WL140V LED20_34S/827_830_840 PSU WH	White
911401873687	WL140V 14_24_40S/827_830_840 PSU WH	White RAL 9003
911401873787	WL140V 14_24_40S/827_830_840 PSU MDU WH	White RAL 9003
911401873887	WL140V 14_24_40S/827_830_840 PSR MDU WH	White RAL 9003
911401873987	WL140V 40S/827_830_840 PSED WH	White RAL 9003
911401874087	WL140V 40S/827_830_840 WIA WH	White RAL 9003
910505101534	WL140V LED12S/830 PSED WH	White
910505101535	WL140V LED12S/840 PSED WH	White
910505101538	WL140V LED20S/830 PSED WH	White
910505101539	WL140V LED20S/840 PSED WH	White
910505101542	WL140V LED34S/830 PSED WH	White
910505101543	WL140V LED34S/840 PSED WH	White
910505101546	WL140V LED20S/830 WIA WH	White
910505101547	WL140V LED20S/840 WIA WH	White
910505101548	WL140V LED34S/830 WIA WH	White
910505101549	WL140V LED34S/840 WIA WH	White
910505101550	WL140V LED12S/830 PSED ELB3 WH	White
910505101551	WL140V LED12S/840 PSED ELB3 WH	White
910505101552	WL140V LED12S/830 PSR ELB3 MDU WH	White
910505101553	WL140V LED12S/840 PSR ELB3 MDU WH	White
910505101554	WL140V LED20S/830 PSED ELB3 WH	White

Emergency Operation (1/2)

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
911401851782	WL140V LED20S/830 PSR MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%
911401851882	WL140V LED20S/840 PSR MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%
911401851982	WL140V LED34S/830 PSR MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%

Order Code	Full Product Name	Housing Color
910505101555	WL140V LED20S/840 PSED ELB3 WH	White
910505101556	WL140V LED20S/830 PSR ELB3 MDU WH	White
910505101557	WL140V LED20S/840 PSR ELB3 MDU WH	White
910505101558	WL140V LED34S/830 PSED ELB3 WH	White
910505101559	WL140V LED34S/840 PSED ELB3 WH	White
910505101560	WL140V LED34S/830 PSR ELB3 MDU WH	White
910505101561	WL140V LED34S/840 PSR ELB3 MDU WH	White
910505101562	WL140V LED20S/830 WIA ELB3 WH	White
910505101563	WL140V LED20S/840 WIA ELB3 WH	White
910505101564	WL140V LED34S/830 WIA ELB3 WH	White
910505101565	WL140V LED34S/840 WIA ELB3 WH	White
911401847482	WL140V LED12S/840 PSU WH	White
911401847582	WL140V LED20S/830 PSU WH	White
911401847682	WL140V LED20S/840 PSU WH	White
911401847782	WL140V LED34S/830 PSU WH	White
911401847882	WL140V LED34S/840 PSU WH	White
911401847982	WL140V LED20S/830 PSU MDU WH	White
911401851582	WL140V LED12S/830 PSR MDU WH	White
911401851682	WL140V LED12S/840 PSR MDU WH	White
911401851782	WL140V LED20S/830 PSR MDU WH	White
911401851882	WL140V LED20S/840 PSR MDU WH	White
911401851982	WL140V LED34S/830 PSR MDU WH	White

CoreLine Wall-mounted

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
911401848182	WL140V LED12_20S/ 827_830_840 PSU WH	-	-	-	-
911401848282	WL140V LED20_34S/ 827_830_840 PSU WH	-	-	-	-
911401873687	WL140V 14_24_40S/ 827_830_840 PSU WH	No	-	-	-
911401873787	WL140V 14_24_40S/ 827_830_840 PSU MDU WH	No	-	-	-
911401873887	WL140V 14_24_40S/ 827_830_840 PSR MDU WH	No	-	-	-
911401873987	WL140V 40S/ 827_830_840 PSED WH	Yes	DC operated central emergency lighting	-	-
911401874087	WL140V 40S/ 827_830_840 WIA WH	No	-	-	-
910505101534	WL140V LED12S/830 PSED WH	Yes	DC operated central emergency lighting	350 lm	-
910505101535	WL140V LED12S/840 PSED WH	Yes	DC operated central emergency lighting	350 lm	-
910505101538	WL140V LED20S/830 PSED WH	Yes	DC operated central emergency lighting	350 lm	-
910505101539	WL140V LED20S/840 PSED WH	Yes	DC operated central emergency lighting	350 lm	-
910505101542	WL140V LED34S/830 PSED WH	Yes	DC operated central emergency lighting	350 lm	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910505101543	WL140V LED34S/840 PSED WH	Yes	DC operated central emergency lighting	350 lm	-
910505101546	WL140V LED20S/830 WIA WH	-	-	-	-
910505101547	WL140V LED20S/840 WIA WH	-	-	-	-
910505101548	WL140V LED34S/830 WIA WH	-	-	-	-
910505101549	WL140V LED34S/840 WIA WH	-	-	-	-
910505101550	WL140V LED12S/830 PSED ELB3 WH	Yes	Emergency lighting 3 hours duration basic version	350 lm	Lithium
910505101551	WL140V LED12S/840 PSED ELB3 WH	Yes	Emergency lighting 3 hours duration basic version	350 lm	Lithium
910505101552	WL140V LED12S/830 PSR ELB3 MDU WH	No	Emergency lighting 3 hours duration basic version	350 lm	Lithium
910505101553	WL140V LED12S/840 PSR ELB3 MDU WH	No	Emergency lighting 3 hours duration basic version	350 lm	Lithium
910505101554	WL140V LED20S/830 PSED ELB3 WH	Yes	Emergency lighting 3 hours duration basic version	350 lm	Lithium
910505101555	WL140V LED20S/840 PSED ELB3 WH	Yes	Emergency lighting 3 hours duration basic version	350 lm	Lithium
910505101556	WL140V LED20S/830	No	Emergency lighting 3 hours	350 lm	Lithium

CoreLine Wall-mounted

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910505101557	PSR ELB3 MDU WH	No	duration	350 lm	Lithium
	WL140V		Emergency lighting 3		
	LED20S/840 PSR ELB3 MDU WH		hours duration basic version		
910505101558	WL140V	Yes	Emergency lighting 3	350 lm	Lithium
	LED34S/830		hours duration basic version		
	PSER ELB3 WH		hours duration basic version		
910505101559	WL140V	Yes	Emergency lighting 3	350 lm	Lithium
	LED34S/840		hours duration basic version		
	PSER ELB3 WH		hours duration basic version		
910505101560	WL140V	No	Emergency lighting 3	350 lm	Lithium
	LED34S/830		hours duration basic version		
	PSR ELB3 MDU WH		hours duration basic version		
910505101561	WL140V	No	Emergency lighting 3	350 lm	Lithium
	LED34S/840		hours duration basic version		
	PSR ELB3 MDU WH		hours duration basic version		
910505101562	WL140V	No	Emergency lighting 3	350 lm	Lithium
	LED20S/830		hours duration basic version		
	WIA ELB3 WH		hours duration basic version		
910505101563	WL140V	No	Emergency lighting 3	350 lm	Lithium
	LED20S/840		hours duration basic version		
	WIA ELB3 WH		hours duration basic version		
910505101564	WL140V	No	Emergency lighting 3	350 lm	Lithium
	LED34S/830		hours duration basic version		
	WIA ELB3 WH		hours duration basic version		

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910505101565	WL140V	No	Emergency lighting 3	350 lm	Lithium
	LED34S/840		hours duration basic version		
	WIA ELB3 WH		hours duration basic version		
911401847482	WL140V	-	-	-	-
	LED12S/840		-		
	PSU WH		-		
911401847582	WL140V	-	-	-	-
	LED20S/830		-		
	PSU WH		-		
911401847682	WL140V	-	-	-	-
	LED20S/840		-		
	PSU WH		-		
911401847782	WL140V	-	-	-	-
	LED34S/830		-		
	PSU WH		-		
911401847882	WL140V	-	-	-	-
	LED34S/840		-		
	PSU WH		-		
911401847982	WL140V	-	-	-	-
	LED20S/830		-		
	PSU MDU WH		-		
911401851582	WL140V	-	-	-	-
	LED12S/830 PSR		-		
	MDU WH		-		
911401851682	WL140V	-	-	-	-
	LED12S/840 PSR		-		
	MDU WH		-		
911401851782	WL140V	-	-	-	-
	LED20S/830		-		
	PSR MDU WH		-		
911401851882	WL140V	-	-	-	-
	LED20S/840		-		
	PSR MDU WH		-		
911401851982	WL140V	-	-	-	-
	LED34S/830		-		
	PSR MDU WH		-		

Emergency Operation (2/2)

CoreLine Wall-mounted

Order Code	Full Product Name	Power consumption during Central DC emergency mode	Rated duration of the emergency lighting (when fully charged)
911401848182	WL140V LED12_20S/827_830_840 PSU WH	-	-
911401848282	WL140V LED20_34S/827_830_840 PSU WH	-	-
911401873687	WL140V 14_24_40S/827_830_840 PSU WH	-	-
911401873787	WL140V 14_24_40S/827_830_840 PSU MDU WH	-	-
911401873887	WL140V 14_24_40S/827_830_840 PSR MDU WH	-	-
911401873987	WL140V 40S/827_830_840 PSED WH	-	-
911401874087	WL140V 40S/827_830_840 WIA WH	-	-
910505101534	WL140V LED12S/830 PSED WH	3 W	-
910505101535	WL140V LED12S/840 PSED WH	3 W	-
910505101538	WL140V LED20S/830 PSED WH	3 W	-
910505101539	WL140V LED20S/840 PSED WH	3 W	-
910505101542	WL140V LED34S/830 PSED WH	3 W	-
910505101543	WL140V LED34S/840 PSED WH	3 W	-
910505101546	WL140V LED20S/830 WIA WH	-	-
910505101547	WL140V LED20S/840 WIA WH	-	-
910505101548	WL140V LED34S/830 WIA WH	-	-
910505101549	WL140V LED34S/840 WIA WH	-	-
910505101550	WL140V LED12S/830 PSED ELB3 WH	3 W	3 hour(s)
910505101551	WL140V LED12S/840 PSED ELB3 WH	3 W	3 hour(s)
910505101552	WL140V LED12S/830 PSR ELB3 MDU WH	-	3 hour(s)
910505101553	WL140V LED12S/840 PSR ELB3 MDU WH	-	3 hour(s)
910505101554	WL140V LED20S/830 PSED ELB3 WH	3 W	3 hour(s)
910505101555	WL140V LED20S/840 PSED ELB3 WH	3 W	3 hour(s)
910505101556	WL140V LED20S/830 PSR ELB3 MDU WH	-	3 hour(s)

Order Code	Full Product Name	Power consumption during Central DC emergency mode	Rated duration of the emergency lighting (when fully charged)
910505101557	WL140V LED20S/840 PSR ELB3 MDU WH	-	3 hour(s)
910505101558	WL140V LED34S/830 PSED ELB3 WH	3 W	3 hour(s)
910505101559	WL140V LED34S/840 PSED ELB3 WH	3 W	3 hour(s)
910505101560	WL140V LED34S/830 PSR ELB3 MDU WH	-	3 hour(s)
910505101561	WL140V LED34S/840 PSR ELB3 MDU WH	-	3 hour(s)
910505101562	WL140V LED20S/830 WIA ELB3 WH	-	3 hour(s)
910505101563	WL140V LED20S/840 WIA ELB3 WH	-	3 hour(s)
910505101564	WL140V LED34S/830 WIA ELB3 WH	-	3 hour(s)
910505101565	WL140V LED34S/840 WIA ELB3 WH	-	3 hour(s)
911401847482	WL140V LED12S/840 PSU WH	-	-
911401847582	WL140V LED20S/830 PSU WH	-	-
911401847682	WL140V LED20S/840 PSU WH	-	-
911401847782	WL140V LED34S/830 PSU WH	-	-
911401847882	WL140V LED34S/840 PSU WH	-	-
911401847982	WL140V LED20S/830 PSU MDU WH	-	-
911401851582	WL140V LED12S/830 PSR MDU WH	-	-
911401851682	WL140V LED12S/840 PSR MDU WH	-	-
911401851782	WL140V LED20S/830 PSR MDU WH	-	-
911401851882	WL140V LED20S/840 PSR MDU WH	-	-
911401851982	WL140V LED34S/830 PSR MDU WH	-	-

Approval and Application (1/2)

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Flammability mark	Glow-wire test
911401848182	WL140V LED12_20S/827_830_840 PSU WH	-20 to +40 °C	ENEC mark	-	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Flammability mark	Glow-wire test
911401848282	WL140V LED20_34S/827_830_840 PSU WH	-20 to +40 °C	ENEC mark	-	Temperature 650 °C, duration 30 s

CoreLine Wall-mounted

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Flammability mark	Glow-wire test
911401873687	WL140V 14_24_40S/ 827_830_840 PSU WH	-20 to +40 °C	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401873787	WL140V 14_24_40S/ 827_830_840 PSU MDU WH	-20 to +40 °C	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401873887	WL140V 14_24_40S/ 827_830_840 PSR MDU WH	-20 to +40 °C	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401873987	WL140V 40S/ 827_830_840 PSED WH	-20 to +40 °C	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401874087	WL140V 40S/ 827_830_840 WIA WH	-20 to +40 °C	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
910505101534	WL140V LED12S/830 PSED WH	0 to +25 °C	-	-	Temperature 650 °C, duration 30 s
910505101535	WL140V LED12S/840 PSED WH	0 to +25 °C	-	-	Temperature 650 °C, duration 30 s
910505101538	WL140V LED20S/830 PSED WH	0 to +25 °C	-	-	Temperature 650 °C, duration 30 s
910505101539	WL140V LED20S/840 PSED WH	0 to +25 °C	-	-	Temperature 650 °C, duration 30 s
910505101542	WL140V LED34S/830 PSED WH	0 to +25 °C	-	-	Temperature 650 °C, duration 30 s
910505101543	WL140V LED34S/840 PSED WH	0 to +25 °C	-	-	Temperature 650 °C, duration 30 s
910505101546	WL140V LED20S/830 WIA WH	-20 to +35 °C	-	-	Temperature 650 °C, duration 30 s
910505101547	WL140V LED20S/840 WIA WH	-20 to +35 °C	-	-	Temperature 650 °C, duration 30 s
910505101548	WL140V LED34S/830 WIA WH	-20 to +35 °C	-	-	Temperature 650 °C, duration 30 s
910505101549	WL140V LED34S/840 WIA WH	-20 to +35 °C	-	-	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Flammability mark	Glow-wire test
910505101550	WL140V LED12S/830 PSED ELB3 WH	0 to +25 °C	-	-	Temperature 850 °C, duration 30 s
910505101551	WL140V LED12S/840 PSED ELB3 WH	0 to +25 °C	-	-	Temperature 850 °C, duration 30 s
910505101552	WL140V LED12S/830 PSR ELB3 MDU WH	0 to +25 °C	-	-	Temperature 850 °C, duration 30 s
910505101553	WL140V LED12S/840 PSR ELB3 MDU WH	0 to +25 °C	-	-	Temperature 850 °C, duration 30 s
910505101554	WL140V LED20S/830 PSED ELB3 WH	0 to +25 °C	-	-	Temperature 850 °C, duration 30 s
910505101555	WL140V LED20S/840 PSED ELB3 WH	0 to +25 °C	-	-	Temperature 850 °C, duration 30 s
910505101556	WL140V LED20S/830 PSR ELB3 MDU WH	0 to +25 °C	-	-	Temperature 850 °C, duration 30 s
910505101557	WL140V LED20S/840 PSR ELB3 MDU WH	0 to +25 °C	-	-	Temperature 850 °C, duration 30 s
910505101558	WL140V LED34S/830 PSED ELB3 WH	0 to +25 °C	-	-	Temperature 850 °C, duration 30 s
910505101559	WL140V LED34S/840 PSED ELB3 WH	0 to +25 °C	-	-	Temperature 850 °C, duration 30 s
910505101560	WL140V LED34S/830 PSR ELB3 MDU WH	0 to +25 °C	-	-	Temperature 850 °C, duration 30 s
910505101561	WL140V LED34S/840 PSR ELB3 MDU WH	0 to +25 °C	-	-	Temperature 850 °C, duration 30 s
910505101562	WL140V LED20S/830 WIA ELB3 WH	0 to +25 °C	-	-	Temperature 850 °C, duration 30 s
910505101563	WL140V LED20S/840 WIA ELB3 WH	0 to +25 °C	-	-	Temperature 850 °C, duration 30 s

CoreLine Wall-mounted

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Flammability mark	Glow-wire test
910505101564	WL140V	0 to +25 °C	-	-	Temperature
	LED34S/830				850 °C,
	WIA ELB3 WH				duration 30 s
910505101565	WL140V	0 to +25 °C	-	-	Temperature
	LED34S/840				850 °C,
	WIA ELB3 WH				duration 30 s
911401847482	WL140V	-20 to +40 °C	ENEC mark	-	Temperature
	LED12S/840				650 °C,
	PSU WH				duration 30 s
911401847582	WL140V	-20 to +40 °C	ENEC mark	-	Temperature
	LED20S/830				650 °C,
	PSU WH				duration 30 s
911401847682	WL140V	-20 to +40 °C	ENEC mark	-	Temperature
	LED20S/840				650 °C,
	PSU WH				duration 30 s
911401847782	WL140V	-20 to +40 °C	ENEC mark	-	Temperature
	LED34S/830				650 °C,
	PSU WH				duration 30 s
911401847882	WL140V	-20 to +40 °C	ENEC mark	-	Temperature
	LED34S/840				650 °C,
	PSU WH				duration 30 s

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Flammability mark	Glow-wire test
911401847982	WL140V	-20 to +40 °C	ENEC mark	-	Temperature
	LED20S/830				650 °C,
	PSU MDU WH				duration 30 s
911401851582	WL140V	-20 to +40 °C	ENEC mark	-	Temperature
	LED12S/830				650 °C,
	PSR MDU WH				duration 30 s
911401851682	WL140V	-20 to +40 °C	ENEC mark	-	Temperature
	LED12S/840				650 °C,
	PSR MDU WH				duration 30 s
911401851782	WL140V	-20 to +40 °C	ENEC mark	-	Temperature
	LED20S/830				650 °C,
	PSR MDU WH				duration 30 s
911401851882	WL140V	-20 to +40 °C	ENEC mark	-	Temperature
	LED20S/840				650 °C,
	PSR MDU WH				duration 30 s
911401851982	WL140V	-20 to +40 °C	ENEC mark	-	Temperature
	LED34S/830				650 °C,
	PSR MDU WH				duration 30 s

Approval and Application (2/2)

		Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
Order Code	Full Product Name		
911401848182	WL140V LED12_20S/827_830_840 PSU WH	1	1.6
911401848282	WL140V LED20_34S/827_830_840 PSU WH	1	1.6
911401873687	WL140V 14_24_40S/827_830_840 PSU WH	-	0.4
911401873787	WL140V 14_24_40S/827_830_840 PSU MDU WH	-	0.4
911401873887	WL140V 14_24_40S/827_830_840 PSR MDU WH	-	0.4
911401873987	WL140V 40S/827_830_840 PSED WH	-	0.4
911401874087	WL140V 40S/827_830_840 WIA WH	-	0.4
910505101534	WL140V LED12S/830 PSED WH	1	1.6
910505101535	WL140V LED12S/840 PSED WH	1	1.6
910505101538	WL140V LED20S/830 PSED WH	1	1.6
910505101539	WL140V LED20S/840 PSED WH	1	1.6
910505101542	WL140V LED34S/830 PSED WH	1	1.6
910505101543	WL140V LED34S/840 PSED WH	1	1.6
910505101546	WL140V LED20S/830 WIA WH	1	1.6

		Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
Order Code	Full Product Name		
910505101547	WL140V LED20S/840 WIA WH	1	1.6
910505101548	WL140V LED34S/830 WIA WH	1	1.6
910505101549	WL140V LED34S/840 WIA WH	1	1.6
910505101550	WL140V LED12S/830 PSED ELB3 WH	1	1.6
910505101551	WL140V LED12S/840 PSED ELB3 WH	1	1.6
910505101552	WL140V LED12S/830 PSR ELB3 MDU WH	1	1.6
910505101553	WL140V LED12S/840 PSR ELB3 MDU WH	1	1.6
910505101554	WL140V LED20S/830 PSED ELB3 WH	1	1.6
910505101555	WL140V LED20S/840 PSED ELB3 WH	1	1.6
910505101556	WL140V LED20S/830 PSR ELB3 MDU WH	1	1.6
910505101557	WL140V LED20S/840 PSR ELB3 MDU WH	1	1.6
910505101558	WL140V LED34S/830 PSED ELB3 WH	1	1.6

CoreLine Wall-mounted

Order Code	Full Product Name	Flickering value (PstLM) -	
		Flickering value	Stroboscopic
		as per EN 61000-3-3	effect visibility measure (SVM)
910505101559	WL140V LED34S/840 PSED ELB3 WH	1	1.6
910505101560	WL140V LED34S/830 PSR ELB3 MDU WH	1	1.6
910505101561	WL140V LED34S/840 PSR ELB3 MDU WH	1	1.6
910505101562	WL140V LED20S/830 WIA ELB3 WH	1	1.6
910505101563	WL140V LED20S/840 WIA ELB3 WH	1	1.6
910505101564	WL140V LED34S/830 WIA ELB3 WH	1	1.6
910505101565	WL140V LED34S/840 WIA ELB3 WH	1	1.6

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401848182	WL140V LED12_20S/827_830_840 PSU WH	(0.3818,0.3797) SDCM <5
911401848282	WL140V LED20_34S/827_830_840 PSU WH	(0.3818,0.3797) SDCM <5
911401873687	WL140V 14_24_40S/827_830_840 PSU WH	(0.46,0.42) SDCM<3; (0.43,0.40) SDCM<5; (0.38,0.38) SDCM<5
911401873787	WL140V 14_24_40S/827_830_840 PSU MDU WH	(0.46,0.42) SDCM<3; (0.43,0.40) SDCM<5; (0.38,0.38) SDCM<5
911401873887	WL140V 14_24_40S/827_830_840 PSR MDU WH	(0.46,0.42) SDCM<3; (0.43,0.40) SDCM<5; (0.38,0.38) SDCM<5
911401873987	WL140V 40S/827_830_840 PSED WH	(0.46,0.42) SDCM<3; (0.43,0.40) SDCM<5; (0.38,0.38) SDCM<5
911401874087	WL140V 40S/827_830_840 WIA WH	(0.46,0.42) SDCM<3; (0.43,0.40) SDCM<5; (0.38,0.38) SDCM<5
910505101534	WL140V LED12S/830 PSED WH	(0.4338,0.4030) SDCM <3
910505101535	WL140V LED12S/840 PSED WH	(0.3818,0.3797) SDCM <3
910505101538	WL140V LED20S/830 PSED WH	(0.4338,0.4030) SDCM <3
910505101539	WL140V LED20S/840 PSED WH	(0.3818,0.3797) SDCM <3
910505101542	WL140V LED34S/830 PSED WH	(0.4338,0.4030) SDCM <3
910505101543	WL140V LED34S/840 PSED WH	(0.3818,0.3797) SDCM <3
910505101546	WL140V LED20S/830 WIA WH	(0.4338,0.4030) SDCM <3
910505101547	WL140V LED20S/840 WIA WH	(0.3818,0.3797) SDCM <3
910505101548	WL140V LED34S/830 WIA WH	(0.4338,0.4030) SDCM <3
910505101549	WL140V LED34S/840 WIA WH	(0.3818,0.3797) SDCM <3
910505101550	WL140V LED12S/830 PSED ELB3 WH	(0.4338,0.4030) SDCM <3

Order Code	Full Product Name	Flickering value (PstLM) -	
		Flickering value	Stroboscopic
		as per EN 61000-3-3	effect visibility measure (SVM)
911401847482	WL140V LED12S/840 PSU WH	1	1.6
911401847582	WL140V LED20S/830 PSU WH	1	1.6
911401847682	WL140V LED20S/840 PSU WH	1	1.6
911401847782	WL140V LED34S/830 PSU WH	1	1.6
911401847882	WL140V LED34S/840 PSU WH	1	1.6
911401847982	WL140V LED20S/830 PSU MDU WH	1	1.6
911401851582	WL140V LED12S/830 PSR MDU WH	1	1.6
911401851682	WL140V LED12S/840 PSR MDU WH	1	1.6
911401851782	WL140V LED20S/830 PSR MDU WH	1	1.6
911401851882	WL140V LED20S/840 PSR MDU WH	1	1.6
911401851982	WL140V LED34S/830 PSR MDU WH	1	1.6

Order Code	Full Product Name	Initial chromaticity
910505101551	WL140V LED12S/840 PSED ELB3 WH	(0.3818,0.3797) SDCM <3
910505101552	WL140V LED12S/830 PSR ELB3 MDU WH	(0.4338,0.4030) SDCM <3
910505101553	WL140V LED12S/840 PSR ELB3 MDU WH	(0.3818,0.3797) SDCM <3
910505101554	WL140V LED20S/830 PSED ELB3 WH	(0.4338,0.4030) SDCM <3
910505101555	WL140V LED20S/840 PSED ELB3 WH	(0.3818,0.3797) SDCM <3
910505101556	WL140V LED20S/830 PSR ELB3 MDU WH	(0.4338,0.4030) SDCM <3
910505101557	WL140V LED20S/840 PSR ELB3 MDU WH	(0.3818,0.3797) SDCM <3
910505101558	WL140V LED34S/830 PSED ELB3 WH	(0.4338,0.4030) SDCM <3
910505101559	WL140V LED34S/840 PSED ELB3 WH	(0.3818,0.3797) SDCM <3
910505101560	WL140V LED34S/830 PSR ELB3 MDU WH	(0.4338,0.4030) SDCM <3
910505101561	WL140V LED34S/840 PSR ELB3 MDU WH	(0.3818,0.3797) SDCM <3
910505101562	WL140V LED20S/830 WIA ELB3 WH	(0.4338,0.4030) SDCM <3
910505101563	WL140V LED20S/840 WIA ELB3 WH	(0.3818,0.3797) SDCM <3
910505101564	WL140V LED34S/830 WIA ELB3 WH	(0.4338,0.4030) SDCM <3
910505101565	WL140V LED34S/840 WIA ELB3 WH	(0.3818,0.3797) SDCM <3
911401847482	WL140V LED12S/840 PSU WH	(0.3818,0.3797) SDCM <3
911401847582	WL140V LED20S/830 PSU WH	(0.4338,0.4030) SDCM <3
911401847682	WL140V LED20S/840 PSU WH	(0.3818,0.3797) SDCM <3
911401847782	WL140V LED34S/830 PSU WH	(0.4338,0.4030) SDCM <3
911401847882	WL140V LED34S/840 PSU WH	(0.3818,0.3797) SDCM <3
911401847982	WL140V LED20S/830 PSU MDU WH	(0.4338,0.4030) SDCM <3
911401851582	WL140V LED12S/830 PSR MDU WH	(0.4338,0.4030) SDCM <3
911401851682	WL140V LED12S/840 PSR MDU WH	(0.3818,0.3797) SDCM <3
911401851782	WL140V LED20S/830 PSR MDU WH	(0.4338,0.4030) SDCM <3

CoreLine Wall-mounted

Order Code	Full Product Name	Initial chromaticity
911401851882	WL140V LED20S/840 PSR MDU WH	(0.3818,0.3797) SDCM <3


Order Code	Full Product Name	Initial chromaticity
911401851982	WL140V LED34S/830 PSR MDU WH	(0.4338,0.4030) SDCM <3

Product Data


Order Code	Full Product Name	Product family code
911401848182	WL140V LED12_20S/827_830_840 PSU WH	-
911401848282	WL140V LED20_34S/827_830_840 PSU WH	-
911401873687	WL140V 14_24_40S/827_830_840 PSU WH	-
911401873787	WL140V 14_24_40S/827_830_840 PSU MDU WH	-
911401873887	WL140V 14_24_40S/827_830_840 PSR MDU WH	-
911401873987	WL140V 40S/827_830_840 PSED WH	-
911401874087	WL140V 40S/827_830_840 WIA WH	-
910505101534	WL140V LED12S/830 PSED WH	WL140V
910505101535	WL140V LED12S/840 PSED WH	WL140V
910505101538	WL140V LED20S/830 PSED WH	WL140V
910505101539	WL140V LED20S/840 PSED WH	WL140V
910505101542	WL140V LED34S/830 PSED WH	WL140V
910505101543	WL140V LED34S/840 PSED WH	WL140V
910505101546	WL140V LED20S/830 WIA WH	WL140V
910505101547	WL140V LED20S/840 WIA WH	WL140V
910505101548	WL140V LED34S/830 WIA WH	WL140V
910505101549	WL140V LED34S/840 WIA WH	WL140V
910505101550	WL140V LED12S/830 PSED ELB3 WH	WL140V
910505101551	WL140V LED12S/840 PSED ELB3 WH	WL140V
910505101552	WL140V LED12S/830 PSR ELB3 MDU WH	WL140V
910505101553	WL140V LED12S/840 PSR ELB3 MDU WH	WL140V
910505101554	WL140V LED20S/830 PSED ELB3 WH	WL140V

Order Code	Full Product Name	Product family code
910505101555	WL140V LED20S/840 PSED ELB3 WH	WL140V
910505101556	WL140V LED20S/830 PSR ELB3 MDU WH	WL140V
910505101557	WL140V LED20S/840 PSR ELB3 MDU WH	WL140V
910505101558	WL140V LED34S/830 PSED ELB3 WH	WL140V
910505101559	WL140V LED34S/840 PSED ELB3 WH	WL140V
910505101560	WL140V LED34S/830 PSR ELB3 MDU WH	WL140V
910505101561	WL140V LED34S/840 PSR ELB3 MDU WH	WL140V
910505101562	WL140V LED20S/830 WIA ELB3 WH	WL140V
910505101563	WL140V LED20S/840 WIA ELB3 WH	WL140V
910505101564	WL140V LED34S/830 WIA ELB3 WH	WL140V
910505101565	WL140V LED34S/840 WIA ELB3 WH	WL140V
911401847482	WL140V LED12S/840 PSU WH	-
911401847582	WL140V LED20S/830 PSU WH	-
911401847682	WL140V LED20S/840 PSU WH	-
911401847782	WL140V LED34S/830 PSU WH	-
911401847882	WL140V LED34S/840 PSU WH	-
911401847982	WL140V LED20S/830 PSU MDU WH	-
911401851582	WL140V LED12S/830 PSR MDU WH	-
911401851682	WL140V LED12S/840 PSR MDU WH	-
911401851782	WL140V LED20S/830 PSR MDU WH	-
911401851882	WL140V LED20S/840 PSR MDU WH	-
911401851982	WL140V LED34S/830 PSR MDU WH	-


Polar Wide Diagrams



Polar Normal (separate) - WL140VI - 910505101550




Polar Normal (separate) - WL140VI - 910505101553




Polar Normal (separate) - WL140VI - 910505101548


Polar Wide Diagrams




Polar Normal (separate) - WL140VI - 910505101563




Polar Normal (separate) - WL140VI - 910505101565




Polar Normal (separate) - WL140VI - 910505101546




Polar Normal (separate) - WL140VI - 910505101562




Polar Normal (separate) - WL140VI - 910505101539




Polar Normal (separate) - WL140VI - 910505101554



Polar Normal (separate) - WL140VI - 910505101561




Polar Normal (separate) - WL140VI - 910505101543




Polar Normal (separate) - WL140VI - 910505101552

CoreLine Wall-mounted


Polar Wide Diagrams




Polar Normal (separate) - WL140VI - 910505101533




Polar Normal (separate) - WL140VI - 910505101539




Polar Normal (separate) - WL140VI - 910505101555




Polar Normal (separate) - WL140VI - 910505101534




Polar Normal (separate) - WL140VI - 910505101551




Polar Normal (separate) - WL140VI - 910505101564



Polar Normal (separate) - WL140VI - 910505101560




Polar Normal (separate) - WL140VI - 910505101547




Polar Normal (separate) - WL140VI - 910505101549

CoreLine Wall-mounted


Polar Wide Diagrams




Polar Normal (separate) - WL140VI - 910505101538




Polar Normal (separate) - WL140VI - 910505101542




Polar Normal (separate) - WL140VI - 910505101557




Polar Normal (separate) - WL140VI - 910505101556




Polar Normal (separate) - WL140VI - 910505101558




Polar Normal (separate) - null - 911401874087




Polar Normal (separate) - null - 911401873787



Polar Normal (separate) - null - 911401873887






Polar Normal (separate) - null - 911401873987



Polar Normal (separate) - null - 911401873687

CoreLine Wall-mounted




Polar Wide Diagrams



Polar Normal (separate) - null - 911401851882

Polar Normal (separate) - null - 91140184282




Polar Normal (separate) - null - 911401847482



Polar Normal (separate) - null - 911401847582

Polar Normal (separate) - null - 911401847682




Polar Normal (separate) - null - 911401847782



Polar Normal (separate) - null - 911401847882

Polar Normal (separate) - null - 911401847982

Polar Normal (separate) - null - 911401848182




Polar Normal (separate) - null - 911401851582

Polar Normal (separate) - null - 911401851682

Polar Normal (separate) - null - 911401851782

CoreLine Wall-mounted

Polar Wide Diagrams



Polar Normal (separate) - null - 911401851982

