



CoreLine wall-mounted – For every project, where light really matters. Suits your specific application.

CoreLine Wall-mounted

CoreLine wall-mounted solutions deliver on the CoreLine promise of innovative, easy-to-install and high-quality luminaires. These circular-shaped, surface-mounted luminaires are suitable for both ceiling and wall installations and are easy to apply in circulation areas such as corridors, hallways and staircases. The modern, unobtrusive design, combined with a homogeneous light distribution, ensures this luminaire will blend into the architecture of most buildings. All-in features provide up to three lumen packages and three color temperature options in one luminaire. Installers can easily fit the luminaire according to the application need on site. And thanks to the push-in connectors, installation of the CoreLine WL140V is fast and straightforward. This family includes Interact ready luminaires with integrated wireless communications, ready for use with Interact gateways, sensors and software.

CoreLine Wall-mounted

Benefits

- Delivers the right lighting settings for various applications
- Easy installation with push-in connectors and through wiring possibility
- Slim and unobtrusive design in black or grey, plus half-moon (eye-lid) accessories
- One product serves multi-functional purposes with dipswitch settings
- Direct replacement for traditional wall-mounted luminaires
- Water and vandal-proof as standard
- Emergency ready

Features

- High efficacy up to 140lm/W
- Three lumen packages and three-color temperatures to cater for diverse applications
- Choice of drivers: DALI with DC compatible, wireless with Interact ready
- Compatible emergency lighting kit (incl. self-test) available for self-installation
- IP65/IK10 as standard
- Optional motion detection, including daylight sensing, dimming and wireless grouping function with MDU


Application

- Offices
- Municipal Buildings
- Parking Garages
- Corridors
- Staircases
- Outdoor safety lighting

Warnings and Safety

- For outdoor operations; wall-mounted applications only and all cables should run indoors with a maximum distance of 10 meters

Dimensional drawing



CoreLine Wall-mounted

Product details



CoreLine Wall-mounted WL140V
Rim Black



CoreLine Wall-mounted WL140V
Rim Grey



CoreLine Wall-mounted WL140V
Wall-mounted Black



CoreLine Wall-mounted WL140V
Wall-mounted PSU



CoreLine Wall-mounted WL140V
Ceiling-mounted Grey



CoreLine Wall-mounted WL140V
Ceiling-mounted Black



CoreLine Wall-mounted WL140V
Wall-mounted White with Half-
moon Accessory



CoreLine Wall-mounted WL140V
Wall-mounted Grey with Half-
moon Accessory

CoreLine Wall-mounted

Product details



Coreline Wall-mounted WL140V
Top View (with screw locations)



CoreLine Wall-mounted WL140V
Wall-mounted Switchable Lumen
& CCT



CoreLine Wall-mounted WL140V
Half-moon Accessory Black



CoreLine Wall-mounted WL140V
Half-moon Accessory Grey



CoreLine Wall-mounted WL140V
Ceiling-mounted



CoreLine Wall-mounted WL140V
Wall-mounted PSR MDU



CoreLine Wall-mounted WL140V
Wall-mounted Grey



CoreLine Wall-mounted WL140V
Half-moon Accessory White

CoreLine Wall-mounted

Product details



Coreline Wall-mounted WL140V
Top View

General Information	
Driver included	Yes
Number of gear units	1 unit
Light Technical	
Color rendering index (CRI)	>80
Optic type	Symmetrical
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Suitable for random switching	No
Mechanical and Housing	
Mech. impact protection code	IK10
Ingress protection code	IP65
Approval and Application	
CE mark	Yes
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Light source replaceable
911401848182	WL140V LED12_20S/827_830_840 PSU WH	Yes
911401848282	WL140V LED20_34S/827_830_840 PSU WH	Yes
911401873687	WL140V 14_24_40S/827_830_840 PSU WH	-
911401873787	WL140V 14_24_40S/827_830_840 PSU MDU WH	-
911401873887	WL140V 14_24_40S/827_830_840 PSR MDU WH	-
911401873987	WL140V 40S/827_830_840 PSED WH	-
911401874087	WL140V 40S/827_830_840 WIA WH	-
910505101539	WL140V LED20S/840 PSED WH	No
911401847382	WL140V LED12S/830 PSU WH	Yes
911401847482	WL140V LED12S/840 PSU WH	Yes
911401847582	WL140V LED20S/830 PSU WH	Yes
911401847682	WL140V LED20S/840 PSU WH	Yes
911401847782	WL140V LED34S/830 PSU WH	Yes
911401847882	WL140V LED34S/840 PSU WH	Yes
911401847982	WL140V LED20S/830 PSU MDU WH	Yes
911401848082	WL140V LED20S/840 PSU MDU WH	Yes
911401851582	WL140V LED12S/830 PSR MDU WH	Yes
911401851682	WL140V LED12S/840 PSR MDU WH	Yes
911401851782	WL140V LED20S/830 PSR MDU WH	Yes
911401851882	WL140V LED20S/840 PSR MDU WH	Yes
911401851982	WL140V LED34S/830 PSR MDU WH	Yes
911401852082	WL140V LED34S/840 PSR MDU WH	Yes

Light Technical (1/2)

Order Code	Full Product		Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
	Name	All-in Type			
911401848182	WL140V LED12_20S/827_830_840 PSU WH	All-in, Multi Lumen	120 degree(s)	2700 K	100 lm/W
911401848282	WL140V LED20_34S/	All-in, Multi Lumen	120 degree(s)	2700 K	100 lm/W

Order Code	Full Product		Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
	Name	All-in Type			
	827_830_840 PSU WH				
911401873687	WL140V 14_24_40S/827_830_840 PSU WH	All-in, Multi Color Temperature	-	2700 K	140 lm/W

CoreLine Wall-mounted

Order Code	Full Product Name	All-in Type	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
911401873787	WL140V 14_24_40S/827_830_840 PSU MDU WH	All-in, Multi Color Temperature	-	2700 K	135 lm/W
911401873887	WL140V 14_24_40S/827_830_840 PSR MDU WH	All-in, Multi Color Temperature	-	2700 K	135 lm/W
911401873987	WL140V 40S/827_830_840 PSED WH	All-in, Multi Color Temperature	-	2700 K	140 lm/W
911401874087	WL140V 40S/827_830_840 WIA WH	All-in, Multi Color Temperature	-	2700 K	140 lm/W
910505101539	WL140V LED20S/840 PSED WH	-	120 degree(s)	4000 K	100 lm/W
911401847382	WL140V LED12S/830 PSU WH	-	120 degree(s)	3000 K	105 lm/W
911401847482	WL140V LED12S/840 PSU WH	-	120 degree(s)	4000 K	110 lm/W
911401847582	WL140V LED20S/830 PSU WH	-	120 degree(s)	3000 K	105 lm/W
911401847682	WL140V LED20S/840 PSU WH	-	120 degree(s)	4000 K	110 lm/W
911401847782	WL140V LED34S/830 PSU WH	-	120 degree(s)	3000 K	105 lm/W

Order Code	Full Product Name	All-in Type	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
911401847882	WL140V LED34S/840 PSU WH	-	120 degree(s)	4000 K	110 lm/W
911401847982	WL140V LED20S/830 PSU MDU WH	-	120 degree(s)	3000 K	95 lm/W
911401848082	WL140V LED20S/840 PSU MDU WH	-	120 degree(s)	4000 K	100 lm/W
911401851582	WL140V LED12S/830 PSR MDU WH	-	120 degree(s)	3000 K	90 lm/W
911401851682	WL140V LED12S/840 PSR MDU WH	-	120 degree(s)	4000 K	95 lm/W
911401851782	WL140V LED20S/830 PSR MDU WH	-	120 degree(s)	3000 K	90 lm/W
911401851882	WL140V LED20S/840 PSR MDU WH	-	120 degree(s)	4000 K	95 lm/W
911401851982	WL140V LED34S/830 PSR MDU WH	-	120 degree(s)	3000 K	98 lm/W
911401852082	WL140V LED34S/840 PSR MDU WH	-	120 degree(s)	4000 K	103 lm/W

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux
911401848182	WL140V LED12_20S/827_830_840 PSU WH	1,200 lm
911401848282	WL140V LED20_34S/827_830_840 PSU WH	2,000 lm
911401873687	WL140V 14_24_40S/827_830_840 PSU WH	1,400 lm
911401873787	WL140V 14_24_40S/827_830_840 PSU MDU WH	1,400 lm
911401873887	WL140V 14_24_40S/827_830_840 PSR MDU WH	1,400 lm
911401873987	WL140V 40S/827_830_840 PSED WH	4,050 lm
911401874087	WL140V 40S/827_830_840 WIA WH	4,050 lm
910505101539	WL140V LED20S/840 PSED WH	2,200 lm
911401847382	WL140V LED12S/830 PSU WH	1,275 lm
911401847482	WL140V LED12S/840 PSU WH	1,350 lm
911401847582	WL140V LED20S/830 PSU WH	2,100 lm

Order Code	Full Product Name	Luminous Flux
911401847682	WL140V LED20S/840 PSU WH	2,200 lm
911401847782	WL140V LED34S/830 PSU WH	3,400 lm
911401847882	WL140V LED34S/840 PSU WH	3,550 lm
911401847982	WL140V LED20S/830 PSU MDU WH	1,850 lm
911401848082	WL140V LED20S/840 PSU MDU WH	1,950 lm
911401851582	WL140V LED12S/830 PSR MDU WH	1,200 lm
911401851682	WL140V LED12S/840 PSR MDU WH	1,250 lm
911401851782	WL140V LED20S/830 PSR MDU WH	2,100 lm
911401851882	WL140V LED20S/840 PSR MDU WH	2,200 lm
911401851982	WL140V LED34S/830 PSR MDU WH	2,950 lm
911401852082	WL140V LED34S/840 PSR MDU WH	3,100 lm

Operating and Electrical

CoreLine Wall-mounted

Order Code	Full Product Name	Power Consumption
911401848182	WL140V LED12_20S/827_830_840 PSU WH	20 W
911401848282	WL140V LED20_34S/827_830_840 PSU WH	33 W
911401873687	WL140V 14_24_40S/827_830_840 PSU WH	29 W
911401873787	WL140V 14_24_40S/827_830_840 PSU MDU WH	30 W
911401873887	WL140V 14_24_40S/827_830_840 PSR MDU WH	30 W
911401873987	WL140V 40S/827_830_840 PSED WH	29 W
911401874087	WL140V 40S/827_830_840 WIA WH	29 W
910505101539	WL140V LED20S/840 PSED WH	22 W
911401847382	WL140V LED12S/830 PSU WH	12 W
911401847482	WL140V LED12S/840 PSU WH	12 W
911401847582	WL140V LED20S/830 PSU WH	20 W

Order Code	Full Product Name	Power Consumption
911401847682	WL140V LED20S/840 PSU WH	20 W
911401847782	WL140V LED34S/830 PSU WH	32 W
911401847882	WL140V LED34S/840 PSU WH	32 W
911401847982	WL140V LED20S/830 PSU MDU WH	19 W
911401848082	WL140V LED20S/840 PSU MDU WH	19 W
911401851582	WL140V LED12S/830 PSR MDU WH	13 W
911401851682	WL140V LED12S/840 PSR MDU WH	13 W
911401851782	WL140V LED20S/830 PSR MDU WH	23 W
911401851882	WL140V LED20S/840 PSR MDU WH	23 W
911401851982	WL140V LED34S/830 PSR MDU WH	30 W
911401852082	WL140V LED34S/840 PSR MDU WH	30 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
911401848182	WL140V LED12_20S/827_830_840 PSU WH	No	-	Not applicable
911401848282	WL140V LED20_34S/827_830_840 PSU WH	No	-	Not applicable
911401873687	WL140V 14_24_40S/827_830_840 PSU WH	No	-	-
911401873787	WL140V 14_24_40S/827_830_840 PSU MDU WH	Yes	-	-
911401873887	WL140V 14_24_40S/827_830_840 PSR MDU WH	Yes	-	-
911401873987	WL140V 40S/827_830_840 PSED WH	Yes	-	-
911401874087	WL140V 40S/827_830_840 WIA WH	Yes	-	-
910505101539	WL140V LED20S/840 PSED WH	Yes	-	1%
911401847382	WL140V LED12S/830 PSU WH	No	-	Not applicable
911401847482	WL140V LED12S/840 PSU WH	No	-	Not applicable
911401847582	WL140V LED20S/830 PSU WH	No	-	Not applicable
911401847682	WL140V LED20S/840 PSU WH	No	-	Not applicable
911401847782	WL140V LED34S/830 PSU WH	No	-	Not applicable
911401847882	WL140V LED34S/840 PSU WH	No	-	Not applicable

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
911401847982	WL140V LED20S/830 PSU MDU WH	Yes	Programmable movement and light sensor	Not applicable
911401848082	WL140V LED20S/840 PSU MDU WH	Yes	Programmable movement and light sensor	Not applicable
911401851582	WL140V LED12S/830 PSR MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%
911401851682	WL140V LED12S/840 PSR MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%
911401851782	WL140V LED20S/830 PSR MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%
911401851882	WL140V LED20S/840 PSR MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%
911401851982	WL140V LED34S/830 PSR MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%
911401852082	WL140V LED34S/840 PSR MDU WH	Yes	Programmable movement and light sensor with wireless grouping	10%

Mechanical and Housing

CoreLine Wall-mounted

Order Code	Full Product Name	Housing Color
911401848182	WL140V LED12_20S/827_830_840 PSU WH	White
911401848282	WL140V LED20_34S/827_830_840 PSU WH	White
911401873687	WL140V 14_24_40S/827_830_840 PSU WH	White RAL 9003
911401873787	WL140V 14_24_40S/827_830_840 PSU MDU WH	White RAL 9003
911401873887	WL140V 14_24_40S/827_830_840 PSR MDU WH	White RAL 9003
911401873987	WL140V 40S/827_830_840 PSED WH	White RAL 9003
911401874087	WL140V 40S/827_830_840 WIA WH	White RAL 9003
910505101539	WL140V LED20S/840 PSED WH	White
911401847382	WL140V LED12S/830 PSU WH	White
911401847482	WL140V LED12S/840 PSU WH	White
911401847582	WL140V LED20S/830 PSU WH	White

Order Code	Full Product Name	Housing Color
911401847682	WL140V LED20S/840 PSU WH	White
911401847782	WL140V LED34S/830 PSU WH	White
911401847882	WL140V LED34S/840 PSU WH	White
911401847982	WL140V LED20S/830 PSU MDU WH	White
911401848082	WL140V LED20S/840 PSU MDU WH	White
911401851582	WL140V LED12S/830 PSR MDU WH	White
911401851682	WL140V LED12S/840 PSR MDU WH	White
911401851782	WL140V LED20S/830 PSR MDU WH	White
911401851882	WL140V LED20S/840 PSR MDU WH	White
911401851982	WL140V LED34S/830 PSR MDU WH	White
911401852082	WL140V LED34S/840 PSR MDU WH	White

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Power consumption during Central DC emergency mode
911401848182	WL140V LED12_20S/827_830_840 PSU WH	-	-	-	-
911401848282	WL140V LED20_34S/827_830_840 PSU WH	-	-	-	-
911401873687	WL140V 14_24_40S/827_830_840 PSU WH	No	-	-	-
911401873787	WL140V 14_24_40S/827_830_840 PSU MDU WH	No	-	-	-
911401873887	WL140V 14_24_40S/827_830_840 PSR MDU WH	No	-	-	-
911401873987	WL140V 40S/827_830_840 PSED WH	Yes	DC operated central emergency lighting	-	-
911401874087	WL140V 40S/827_830_840 WIA WH	No	-	-	-
910505101539	WL140V LED20S/840 PSED WH	Yes	DC operated central	350 lm	3 W

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Power consumption during Central DC emergency mode
			emergency lighting		
911401847382	WL140V LED12S/830 PSU WH	-	-	-	-
911401847482	WL140V LED12S/840 PSU WH	-	-	-	-
911401847582	WL140V LED20S/830 PSU WH	-	-	-	-
911401847682	WL140V LED20S/840 PSU WH	-	-	-	-
911401847782	WL140V LED34S/830 PSU WH	-	-	-	-
911401847882	WL140V LED34S/840 PSU WH	-	-	-	-
911401847982	WL140V LED20S/830 PSU MDU WH	-	-	-	-
911401848082	WL140V LED20S/840 PSU MDU WH	-	-	-	-
911401851582	WL140V LED12S/830 PSR MDU WH	-	-	-	-
911401851682	WL140V LED12S/840 PSR MDU WH	-	-	-	-

CoreLine Wall-mounted

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Power consumption during Central DC emergency mode
911401851782	WL140V LED20S/830 PSR MDU WH	-	-	-	-
911401851882	WL140V LED20S/840 PSR MDU WH	-	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Power consumption during Central DC emergency mode
911401851982	WL140V LED34S/830 PSR MDU WH	-	-	-	-
911401852082	WL140V LED34S/840 PSR MDU WH	-	-	-	-

Approval and Application (1/2)

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3
911401848182	WL140V LED12_20S/ 827_830_840 PSU WH	-20 to +40 °C	ENEC mark	-	1
911401848282	WL140V LED20_34S/ 827_830_840 PSU WH	-20 to +40 °C	ENEC mark	-	1
911401873687	WL140V 14_24_40S/ 827_830_840 PSU WH	-20 to +40 °C	ENEC mark	For mounting on normally flammable surfaces	-
911401873787	WL140V 14_24_40S/ 827_830_840 PSU MDU WH	-20 to +40 °C	ENEC mark	For mounting on normally flammable surfaces	-
911401873887	WL140V 14_24_40S/ 827_830_840 PSR MDU WH	-20 to +40 °C	ENEC mark	For mounting on normally flammable surfaces	-
911401873987	WL140V 40S/ 827_830_840 PSED WH	-20 to +40 °C	ENEC mark	For mounting on normally flammable surfaces	-
911401874087	WL140V 40S/ 827_830_840 WIA WH	-20 to +40 °C	ENEC mark	For mounting on normally flammable surfaces	-
910505101539	WL140V LED20S/840 PSED WH	0 to +25 °C	-	-	1

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3
911401847382	WL140V LED12S/830 PSU WH	-20 to +40 °C	ENEC mark	-	1
911401847482	WL140V LED12S/840 PSU WH	-20 to +40 °C	ENEC mark	-	1
911401847582	WL140V LED20S/830 PSU WH	-20 to +40 °C	ENEC mark	-	1
911401847682	WL140V LED20S/840 PSU WH	-20 to +40 °C	ENEC mark	-	1
911401847782	WL140V LED34S/830 PSU WH	-20 to +40 °C	ENEC mark	-	1
911401847882	WL140V LED34S/840 PSU WH	-20 to +40 °C	ENEC mark	-	1
911401847982	WL140V LED20S/830 PSU MDU WH	-20 to +40 °C	ENEC mark	-	1
911401848082	WL140V LED20S/840 PSU MDU WH	-20 to +40 °C	ENEC mark	-	1
911401851582	WL140V LED12S/830 PSR MDU WH	-20 to +40 °C	ENEC mark	-	1
911401851682	WL140V LED12S/840 PSR MDU WH	-20 to +40 °C	ENEC mark	-	1

CoreLine Wall-mounted

					Flickering value (PstLM) - Flickering value as per EN 61000-3-3
Order Code	Full Product Name	Ambient temperature range	ENEC mark	Flammability mark	
911401851782	WL140V	-20 to +40 °C	ENEC	-	1
	LED20S/830		mark		
	PSR MDU WH				
911401851882	WL140V	-20 to +40 °C	ENEC	-	1
	LED20S/840		mark		
	PSR MDU WH				

					Flickering value (PstLM) - Flickering value as per EN 61000-3-3
Order Code	Full Product Name	Ambient temperature range	ENEC mark	Flammability mark	
911401851982	WL140V	-20 to +40 °C	ENEC	–	1
	LED34S/830		mark		
	PSR MDU WH				
911401852082	WL140V	-20 to +40 °C	ENEC	–	1
	LED34S/840		mark		
	PSR MDU WH				

Approval and Application (2/2)

Order Code	Full Product Name	Stroboscopic effect visibility measure (SVM)
911401848182	WL140V LED12_20S/827_830_840 PSU WH	1.6
911401848282	WL140V LED20_34S/827_830_840 PSU WH	1.6
911401873687	WL140V 14_24_40S/827_830_840 PSU WH	0.4
911401873787	WL140V 14_24_40S/827_830_840 PSU MDU WH	0.4
911401873887	WL140V 14_24_40S/827_830_840 PSR MDU WH	0.4
911401873987	WL140V 40S/827_830_840 PSED WH	0.4
911401874087	WL140V 40S/827_830_840 WIA WH	0.4
910505101539	WL140V LED20S/840 PSED WH	1.6
911401847382	WL140V LED12S/830 PSU WH	1.6
911401847482	WL140V LED12S/840 PSU WH	1.6
911401847582	WL140V LED20S/830 PSU WH	1.6

Order Code	Full Product Name	Stroboscopic effect visibility measure (SVM)
911401847682	WL140V LED20S/840 PSU WH	1.6
911401847782	WL140V LED34S/830 PSU WH	1.6
911401847882	WL140V LED34S/840 PSU WH	1.6
911401847982	WL140V LED20S/830 PSU MDU WH	1.6
911401848082	WL140V LED20S/840 PSU MDU WH	1.6
911401851582	WL140V LED12S/830 PSR MDU WH	1.6
911401851682	WL140V LED12S/840 PSR MDU WH	1.6
911401851782	WL140V LED20S/830 PSR MDU WH	1.6
911401851882	WL140V LED20S/840 PSR MDU WH	1.6
911401851982	WL140V LED34S/830 PSR MDU WH	1.6
911401852082	WL140V LED34S/840 PSR MDU WH	1.6

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401848182	WL140V LED12_20S/827_830_840	(0.3818,0.3797) SDCM <5
	PSU WH	
911401848282	WL140V LED20_34S/827_830_840	(0.3818,0.3797) SDCM <5
	PSU WH	
911401873687	WL140V 14_24_40S/827_830_840	(0.46,0.42) SDCM<3; (0.43,0.40) SDCM<5; (0.38,0.38) SDCM<5
	PSU WH	
911401873787	WL140V 14_24_40S/827_830_840	(0.46,0.42) SDCM<3; (0.43,0.40) SDCM<5; (0.38,0.38) SDCM<5
	PSU MDU WH	
911401873887	WL140V 14_24_40S/827_830_840	(0.46,0.42) SDCM<3; (0.43,0.40) SDCM<5; (0.38,0.38) SDCM<5
	PSR MDU WH	
911401873987	WL140V 40S/827_830_840 PSED WH	(0.46,0.42) SDCM<3; (0.43,0.40) SDCM<5; (0.38,0.38) SDCM<5
911401874087	WL140V 40S/827_830_840 WIA WH	(0.46,0.42) SDCM<3; (0.43,0.40) SDCM<5; (0.38,0.38) SDCM<5
910505101539	WL140V LED20S/840 PSED WH	(0.3818,0.3797) SDCM <3




Order Code	Full Product Name	Initial chromaticity
911401847382	WL140V LED12S/830 PSU WH	(0.4338,0.4030) SDCM <3
911401847482	WL140V LED12S/840 PSU WH	(0.3818,0.3797) SDCM <3
911401847582	WL140V LED20S/830 PSU WH	(0.4338,0.4030) SDCM <3
911401847682	WL140V LED20S/840 PSU WH	(0.3818,0.3797) SDCM <3
911401847782	WL140V LED34S/830 PSU WH	(0.4338,0.4030) SDCM <3
911401847882	WL140V LED34S/840 PSU WH	(0.3818,0.3797) SDCM <3
911401847982	WL140V LED20S/830 PSU MDU WH	(0.4338,0.4030) SDCM <3
911401848082	WL140V LED20S/840 PSU MDU WH	(0.3818,0.3797) SDCM <3
911401851582	WL140V LED12S/830 PSR MDU WH	(0.4338,0.4030) SDCM <3
911401851682	WL140V LED12S/840 PSR MDU WH	(0.3818,0.3797) SDCM <3
911401851782	WL140V LED20S/830 PSR MDU WH	(0.4338,0.4030) SDCM <3
911401851882	WL140V LED20S/840 PSR MDU WH	(0.3818,0.3797) SDCM <3
911401851982	WL140V LED34S/830 PSR MDU WH	(0.4338,0.4030) SDCM <3
911401852082	WL140V LED34S/840 PSR MDU WH	(0.3818,0.3797) SDCM <3

Product Data

CoreLine Wall-mounted

Order Code	Full Product Name	Product family code	Order Code	Full Product Name	Product family code
911401848182	WL140V LED12_20S/827_830_840 PSU WH	-	911401847682	WL140V LED20S/840 PSU WH	-
911401848282	WL140V LED20_34S/827_830_840 PSU WH	-	911401847782	WL140V LED34S/830 PSU WH	-
911401873687	WL140V 14_24_40S/827_830_840 PSU WH	-	911401847882	WL140V LED34S/840 PSU WH	-
911401873787	WL140V 14_24_40S/827_830_840 PSU MDU WH	-	911401847982	WL140V LED20S/830 PSU MDU WH	-
911401873887	WL140V 14_24_40S/827_830_840 PSR MDU WH	-	911401848082	WL140V LED20S/840 PSU MDU WH	-
911401873987	WL140V 40S/827_830_840 PSED WH	-	911401851582	WL140V LED12S/830 PSR MDU WH	-
911401874087	WL140V 40S/827_830_840 WIA WH	-	911401851682	WL140V LED12S/840 PSR MDU WH	-
910505101539	WL140V LED20S/840 PSED WH	WL140V	911401851782	WL140V LED20S/830 PSR MDU WH	-
911401847382	WL140V LED12S/830 PSU WH	-	911401851882	WL140V LED20S/840 PSR MDU WH	-
911401847482	WL140V LED12S/840 PSU WH	-	911401851982	WL140V LED34S/830 PSR MDU WH	-
911401847582	WL140V LED20S/830 PSU WH	-	911401852082	WL140V LED34S/840 PSR MDU WH	-



Polar Wide Diagrams



Polar Normal (separate) - WL140VI - 910505101539




Polar Normal (separate) - null - 911401874087

Polar Normal (separate) - null - 911401873787



Polar Normal (separate) - null - 911401873887

Polar Normal (separate) - null - 911401873987






Polar Normal (separate) - null - 911401873687

Polar Normal (separate) - null - 911401851882

Polar Normal (separate) - null - 911401852082

CoreLine Wall-mounted




Polar Wide Diagrams



Polar Normal (separate) - null - 911401848282

Polar Normal (separate) - null - 911401847382




Polar Normal (separate) - null - 911401847482



Polar Normal (separate) - null - 911401847582

Polar Normal (separate) - null - 911401847682




Polar Normal (separate) - null - 911401847782



Polar Normal (separate) - null - 911401847882

Polar Normal (separate) - null - 911401847982

Polar Normal (separate) - null - 911401848082





Polar Normal (separate) - null - 911401848182

Polar Normal (separate) - null - 911401851582

Polar Normal (separate) - null - 911401851682

CoreLine Wall-mounted

Polar Wide Diagrams



Polar Normal (separate) - null - 911401851782

Polar Normal (separate) - null - 911401851982

