



CoreLine Wall-mounted – the clear choice for LED

CoreLine Wall-mounted

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Wall-mounted range of LED products can be used to replace traditional wall-mounted luminaires incorporating compact fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Benefits

- Up to 55% energy savings compared with luminaires with PL-C lamps
- Up to 55% energy savings compared with luminaires with PL-C lamps
- Direct replacement for traditional wall-mounted luminaires
- Direct replacement for traditional wall-mounted luminaires
- Complete range covering all application requirements in one product (light levels, IP65, IK10, certified emergency lighting, built-in controls)
- Complete range covering all application requirements in one product (light levels, IP65, IK10, certified emergency lighting, built-in controls)

CoreLine Wall-mounted

Features

- Unobtrusive design
- Unobtrusive design
- Three lumen packages replacing traditional wall-mounted luminaires with 1x18 W / 2x18 W / 2x26 W PL-C
- Three lumen packages replacing traditional wall-mounted luminaires with 1x18 W / 2x18 W / 2x26 W PL-C
- Water- and vandal-proof as standard
- Water- and vandal-proof as standard
- Phase-cut dimming as standard
- Phase-cut dimming as standard
- Frosted diffuser ensuring homogeneous light effect and visual comfort
- Frosted diffuser ensuring homogeneous light effect and visual comfort
- Optional emergency lighting
- Optional emergency lighting
- Optional on/off movement detection or programmed 100%-10%-0% corridor dimming functionality
- Optional on/off movement detection or programmed 100%-10%-0% corridor dimming functionality

Application

- Corridors
- Corridors
- Staircases
- Staircases
- Public entrance areas
- Public entrance areas
- Bathrooms
- Bathrooms
- Emergency exits
- Emergency exits
- Parking garages
- Parking garages
- Outdoor safety lighting
- Outdoor safety lighting

Warnings and Safety

- For outdoor operations; wall-mounted applications only and all cables should run indoors with a maximum distance of 10 meters


Versions



CoreLine Wall-mounted WL140V
Wall-mounted

CoreLine Wall-mounted

Dimensional drawing



Product details



CoreLine Wall-mounted WL140V
Rim Black



CoreLine Wall-mounted WL140V
Rim Grey



CoreLine Wall-mounted WL140V
Wall-mounted Black



CoreLine Wall-mounted WL140V
Wall-mounted PSU



CoreLine Wall-mounted WL140V
Ceiling-mounted Grey



CoreLine Wall-mounted WL140V
Ceiling-mounted Black

CoreLine Wall-mounted

Product details



CoreLine Wall-mounted WL140V
Wall-mounted White with Half-
moon Accessory



CoreLine Wall-mounted WL140V
Wall-mounted Grey with Half-
moon Accessory



Coreline Wall-mounted WL140V
Top View (with screw locations)



CoreLine Wall-mounted WL140V
Wall-mounted Switchable Lumen
& CCT



CoreLine Wall-mounted WL140V
Half-moon Accessory Black



CoreLine Wall-mounted WL140V
Half-moon Accessory Grey



CoreLine Wall-mounted WL140V
Ceiling-mounted



CoreLine Wall-mounted WL140V
Wall-mounted PSR MDU

CoreLine Wall-mounted

Product details



CoreLine Wall-mounted WL140V
Wall-mounted Grey




CoreLine Wall-mounted WL140V
Half-moon Accessory White



Coreline Wall-mounted WL140V
Top View

Polar Wide Diagrams



Polar Normal (separate) - null - 911401847682

