



# CoreLine Waterproof – the clear choice for LED

## CoreLine Waterproof

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Waterproof range of LED products can be used to replace traditional waterproof luminaires with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch.

### Benefits

- Up to 50% energy savings compared with TL-D
- Reliable LED technology – maintenance-free
- Direct replacement for conventional waterproof luminaires in terms of light performance, installation flexibility and length

### Features

- Reliable integrated LED technology, ensuring maintenance-free installation and a long lifetime
- Can be used to replace traditional waterproof luminaires ranging from 18 to 58 W TL-D
- Wide-beam light distribution
- Diffuser with optical element ensures visual comfort
- Ceiling-mounted bracket and suspension hooks included; installation can be made vandal-proof by additional screw fixation of mounting brackets

### Application




- Parking garages
- Warehouses
- General lighting

# CoreLine Waterproof

## Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

## Dimensional drawing



## Product details



CoreLine Waterproof WT120C G2  
PCU-7DPP



CoreLine Waterproof WT120C G2  
PCU-3DPP



CoreLine Waterproof WT120C G2  
PCU-10DPP



CoreLine Waterproof WT120C G2  
PCU-9DPP

CoreLine Waterproof


Product details



CoreLine Waterproof WT120C G2  
PCU-12DPP



CoreLine waterproof G2 (WT120C  
G2),MDU, Motion Detection Unit




CoreLine Waterproof WT120C G2  
PCU-2DPP



CoreLine Waterproof WT120C G2  
PCU-13DPP



CoreLine Waterproof WT120C G2  
PCU-8DPP



CoreLine waterproof G2 (WT120C  
G2),MDU, Motion Detection Unit



CoreLine Waterproof WT120C G2  
PCU-11DPP



CoreLine waterproof G2 (WT120C  
G2),Emergency lighting, TrustSight

| General Information                                             |                                           |
|-----------------------------------------------------------------|-------------------------------------------|
| Driver included                                                 | Yes                                       |
| Light source replaceable                                        | No                                        |
| Number of gear units                                            | 1 unit                                    |
| Service tag                                                     | Yes                                       |
| Light Technical                                                 |                                           |
| Color rendering index (CRI)                                     | >80                                       |
| Operating and Electrical                                        |                                           |
| Protection class IEC                                            | Safety class I                            |
| Input Voltage                                                   | 220 to 240 V                              |
| Line Frequency                                                  | 50 or 60 Hz                               |
| Mechanical and Housing                                          |                                           |
| Housing Color                                                   | Gray                                      |
| Mech. impact protection code                                    | IK08                                      |
| Ingress protection code                                         | IP65                                      |
| Approval and Application                                        |                                           |
| CE mark                                                         | Yes                                       |
| ENEC mark                                                       | ENEC mark                                 |
| Flammability mark                                               | For mounting on easily flammable surfaces |
| Glow-wire test                                                  | Temperature 850 °C, duration 30 s         |
| Flickering value (PstLM) - Flickering value as per EN 61000-3-3 | 1                                         |
| Stroboscopic effect visibility measure (SVM)                    | 1.6                                       |
| Initial Performance (IEC Compliant)                             |                                           |
| Luminous flux tolerance                                         | +/-10%                                    |

General Information

| Order Code | Full Product Name                      | Lamp family code |
|------------|----------------------------------------|------------------|
| 91685800   | WT120C G2 LED27S/840 PSU TW3 L1200     | LED27S           |
| 96248700   | WT120C G2 LED27S/840 PSU MDU L1200     | LED27S           |
| 96249400   | WT120C G2 LED27S/840 PSU MDU TW3 L1200 | LED27S           |
| 85418000   | WT120C G2 LED27S/840 PSU ELB3 L1200    | LED27S           |
| 88307500   | WT120C G2 LED27S/840 PSD L1200         | LED27S           |
| 88311200   | WT120C G2 LED27S/840 PSD ELB3 L1200    | LED27S           |
| 91687200   | WT120C G2 LED40S/840 PSU TW3 L1200     | LED40S           |
| 96257900   | WT120C G2 LED40S/840 PSU MDU TW3 L1200 | LED40S           |
| 16316700   | WT120C G2 LED40S/840 PSU WEC L1200     | LED40S           |
| 16317400   | WT120C G2 LED40S/840 PSU TW1 WEC L1200 | LED40S           |
| 88309900   | WT120C G2 LED40S/840 PSD L1200         | LED40S           |
| 85419700   | WT120C G2 LED40S/840 PSU ELB3 L1200    | LED40S           |
| 88312900   | WT120C G2 LED40S/840 PSD ELB3 L1200    | LED40S           |
| 84046600   | WT120C G2 LED27S/840 PSU L1200         | -                |
| 84048099   | WT120C G2 LED40S/840 PSU L1200         | -                |
| 36933499   | WT120C G2 LED40S/865 PSU L1200         | -                |
| 34976399   | WT120C G2 LED18S/840 PSU PCO L600      | -                |
| 34977099   | WT120C G2 LED25S/840 PSU PCO L1200     | -                |
| 34978799   | WT120C G2 LED31S/840 PSU PCO L1500     | -                |
| 34979499   | WT120C G2 LED37S/840 PSU PCO L1200     | -                |
| 34980099   | WT120C G2 LED57S/840 PSU PCO L1500     | -                |
| 34981799   | WT120C G2 LED75S/840 PSU PCO L1500     | -                |
| 96244900   | WT120C G2 LED19S/840 PSU MDU L600      | LED27S           |
| 88306800   | WT120C G2 LED19S/840 PSD L600          | LED19S           |
| 84045900   | WT120C G2 LED19S/840 PSU L600          | -                |
| 91686500   | WT120C G2 LED34S/840 PSU TW3 L1500     | LED34S           |
| 96267800   | WT120C G2 LED34S/840 PSU MDU L1500     | LED34S           |
| 96268500   | WT120C G2 LED34S/840 PSU MDU TW3 L1500 | LED34S           |
| 88308200   | WT120C G2 LED34S/840 PSD L1500         | LED34S           |
| 85420300   | WT120C G2 LED34S/840 PSU ELB3 L1500    | LED34S           |
| 88313600   | WT120C G2 LED34S/840 PSD ELB3 L1500    | LED34S           |
| 91688900   | WT120C G2 LED60S/840 PSU TW3 L1500     | LED60S           |
| 96275300   | WT120C G2 LED60S/840 PSU MDU L1500     | LED60S           |
| 96276000   | WT120C G2 LED60S/840 PSU MDU TW3 L1500 | LED60S           |
| 16318100   | WT120C G2 LED60S/840 PSU WEC L1500     | LED60S           |
| 16319800   | WT120C G2 LED60S/840 PSU TW1 WEC L1500 | LED60S           |
| 88310500   | WT120C G2 LED60S/840 PSD L1500         | LED60S           |
| 85421000   | WT120C G2 LED60S/840 PSU ELB3 L1500    | LED60S           |
| 88314300   | WT120C G2 LED60S/840 PSD ELB3 L1500    | LED60S           |
| 40930200   | WT120C G2 LED80S/840 PSU TW3 L1500     | LED80S           |
| 96286900   | WT120C G2 LED80S/840 PSU MDU L1500     | LED80S           |
| 40929600   | WT120C G2 LED80S/840 PSD L1500         | LED80S           |
| 40931900   | WT120C G2 LED80S/840 PSU L1500 ELB3    | LED80S           |
| 97578400   | WT120C G2 LED65S/840 WIA L1500         | -                |
| 84047399   | WT120C G2 LED34S/840 PSU L1500         | -                |
| 84049700   | WT120C G2 LED60S/840 PSU L1500         | -                |
| 40928900   | WT120C G2 LED80S/840 PSU L1500         | -                |
| 36934199   | WT120C G2 LED34S/865 PSU L1500         | -                |
| 36935899   | WT120C G2 LED60S/865 PSU L1500         | -                |

Light Technical

CoreLine Waterproof

| Order Code | Full Product Name                            | Correlated Color Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux | Optic type |
|------------|----------------------------------------------|------------------------------------|---------------------------------|---------------|------------|
|            |                                              |                                    |                                 |               |            |
| 91685800   | WT120C G2<br>LED27S/840 PSU<br>TW3 L1200     | 4000 K                             | 126 lm/W                        | 2,700 lm      | Wide beam  |
| 96248700   | WT120C G2<br>LED27S/840 PSU<br>MDU L1200     | 4000 K                             | 123 lm/W                        | 2,700 lm      | Wide beam  |
| 96249400   | WT120C G2<br>LED27S/840 PSU<br>MDU TW3 L1200 | 4000 K                             | 123 lm/W                        | 2,700 lm      | Wide beam  |
| 85418000   | WT120C G2<br>LED27S/840 PSU<br>ELB3 L1200    | 4000 K                             | 104 lm/W                        | 2,700 lm      | Wide beam  |
| 88307500   | WT120C G2<br>LED27S/840 PSD<br>L1200         | 4000 K                             | 123 lm/W                        | 2,700 lm      | Wide beam  |
| 88311200   | WT120C G2<br>LED27S/840 PSD<br>ELB3 L1200    | 4000 K                             | 100 lm/W                        | 2,700 lm      | Wide beam  |
| 91687200   | WT120C G2<br>LED40S/840 PSU<br>TW3 L1200     | 4000 K                             | 133 lm/W                        | 4,000 lm      | Wide beam  |
| 96257900   | WT120C G2<br>LED40S/840 PSU<br>MDU TW3 L1200 | 4000 K                             | 133 lm/W                        | 4,000 lm      | Wide beam  |
| 16316700   | WT120C G2<br>LED40S/840 PSU<br>WEC L1200     | 4000 K                             | 138 lm/W                        | 4,000 lm      | Wide beam  |
| 16317400   | WT120C G2<br>LED40S/840 PSU<br>TW1 WEC L1200 | 4000 K                             | 136 lm/W                        | 4,000 lm      | Wide beam  |
| 88309900   | WT120C G2<br>LED40S/840 PSD<br>L1200         | 4000 K                             | 131 lm/W                        | 4,000 lm      | Wide beam  |
| 85419700   | WT120C G2<br>LED40S/840 PSU<br>ELB3 L1200    | 4000 K                             | 121 lm/W                        | 4,000 lm      | Wide beam  |
| 88312900   | WT120C G2<br>LED40S/840 PSD<br>ELB3 L1200    | 4000 K                             | 113 lm/W                        | 4,000 lm      | Wide beam  |
| 84046600   | WT120C G2<br>LED27S/840 PSU<br>L1200         | 4000 K                             | 132 lm/W                        | 2,700 lm      | Wide beam  |
| 84048099   | WT120C G2<br>LED40S/840 PSU<br>L1200         | 4000 K                             | 140 lm/W                        | 4,000 lm      | Wide beam  |
| 36933499   | WT120C G2<br>LED40S/865 PSU<br>L1200         | 6500 K                             | 140 lm/W                        | 4,000 lm      | Wide beam  |

| Order Code | Full Product Name                            | Correlated Color Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux | Optic type     |
|------------|----------------------------------------------|------------------------------------|---------------------------------|---------------|----------------|
|            |                                              |                                    |                                 |               |                |
| 34976399   | WT120C G2<br>LED18S/840 PSU<br>PCO L600      | 4000 K                             | 121 lm/W                        | 1,800 lm      | Very wide beam |
| 34977099   | WT120C G2<br>LED25S/840 PSU<br>PCO L1200     | 4000 K                             | 122 lm/W                        | 2,500 lm      | Very wide beam |
| 34978799   | WT120C G2<br>LED31S/840 PSU<br>PCO L1500     | 4000 K                             | 128 lm/W                        | 3,100 lm      | Very wide beam |
| 34979499   | WT120C G2<br>LED37S/840 PSU<br>PCO L1200     | 4000 K                             | 130 lm/W                        | 3,700 lm      | Very wide beam |
| 34980099   | WT120C G2<br>LED57S/840 PSU<br>PCO L1500     | 4000 K                             | 133 lm/W                        | 5,700 lm      | Very wide beam |
| 34981799   | WT120C G2<br>LED75S/840 PSU<br>PCO L1500     | 4000 K                             | 131 lm/W                        | 7,500 lm      | Very wide beam |
| 96244900   | WT120C G2<br>LED19S/840 PSU<br>MDU L600      | 4000 K                             | 116 lm/W                        | 1,900 lm      | Wide beam      |
| 88306800   | WT120C G2<br>LED19S/840 PSD<br>L600          | 4000 K                             | 115 lm/W                        | 1,900 lm      | Wide beam      |
| 84045900   | WT120C G2<br>LED19S/840 PSU<br>L600          | 4000 K                             | 127 lm/W                        | 1,900 lm      | Wide beam      |
| 91686500   | WT120C G2<br>LED34S/840 PSU<br>TW3 L1500     | 4000 K                             | 133 lm/W                        | 3,400 lm      | Wide beam      |
| 96267800   | WT120C G2<br>LED34S/840 PSU<br>MDU L1500     | 4000 K                             | 131 lm/W                        | 3,400 lm      | Wide beam      |
| 96268500   | WT120C G2<br>LED34S/840 PSU<br>MDU TW3 L1500 | 4000 K                             | 131 lm/W                        | 3,400 lm      | Wide beam      |
| 88308200   | WT120C G2<br>LED34S/840 PSD<br>L1500         | 4000 K                             | 131 lm/W                        | 3,400 lm      | Wide beam      |
| 85420300   | WT120C G2<br>LED34S/840 PSU<br>ELB3 L1500    | 4000 K                             | 113 lm/W                        | 3,400 lm      | Wide beam      |
| 88313600   | WT120C G2<br>LED34S/840 PSD<br>ELB3 L1500    | 4000 K                             | 110 lm/W                        | 3,400 lm      | Wide beam      |
| 91688900   | WT120C G2<br>LED60S/840 PSU<br>TW3 L1500     | 4000 K                             | 135 lm/W                        | 6,000 lm      | Wide beam      |

CoreLine Waterproof

| Order Code | Full Product Name                      | Correlated Color Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux | Optic type |
|------------|----------------------------------------|------------------------------------|---------------------------------|---------------|------------|
|            |                                        |                                    |                                 |               |            |
| 96275300   | WT120C G2 LED60S/840 PSU MDU L1500     | 4000 K                             | 133 lm/W                        | 6,000 lm      | Wide beam  |
| 96276000   | WT120C G2 LED60S/840 PSU MDU TW3 L1500 | 4000 K                             | 133 lm/W                        | 6,000 lm      | Wide beam  |
| 16318100   | WT120C G2 LED60S/840 PSU WEC L1500     | 4000 K                             | 135 lm/W                        | 6,000 lm      | Wide beam  |
| 16319800   | WT120C G2 LED60S/840 PSU TW1 WEC L1500 | 4000 K                             | 136 lm/W                        | 6,000 lm      | Wide beam  |
| 88310500   | WT120C G2 LED60S/840 PSD L1500         | 4000 K                             | 133 lm/W                        | 6,000 lm      | Wide beam  |
| 85421000   | WT120C G2 LED60S/840 PSU ELB3 L1500    | 4000 K                             | 121 lm/W                        | 6,000 lm      | Wide beam  |
| 88314300   | WT120C G2 LED60S/840 PSD ELB3 L1500    | 4000 K                             | 121 lm/W                        | 6,000 lm      | Wide beam  |
| 40930200   | WT120C G2 LED80S/840 PSU TW3 L1500     | 4000 K                             | 133 lm/W                        | 8,000 lm      | Wide beam  |
| 96286900   | WT120C G2 LED80S/840 PSU MDU L1500     | 4000 K                             | 131 lm/W                        | 8,000 lm      | Wide beam  |

| Order Code | Full Product Name                   | Correlated Color Temperature (Nom) | Luminous Efficacy (rated) (Nom) | Luminous Flux | Optic type |
|------------|-------------------------------------|------------------------------------|---------------------------------|---------------|------------|
|            |                                     |                                    |                                 |               |            |
| 40929600   | WT120C G2 LED80S/840 PSD L1500      | 4000 K                             | 129 lm/W                        | 8,000 lm      | Wide beam  |
| 40931900   | WT120C G2 LED80S/840 PSU L1500 ELB3 | 4000 K                             | 126 lm/W                        | 8,000 lm      | Wide beam  |
| 97578400   | WT120C G2 LED65S/840 WIA L1500      | 4000 K                             | 144 lm/W                        | 6,500 lm      | Wide beam  |
| 84047399   | WT120C G2 LED34S/840 PSU L1500      | 4000 K                             | 140 lm/W                        | 3,400 lm      | Wide beam  |
| 84049700   | WT120C G2 LED60S/840 PSU L1500      | 4000 K                             | 140 lm/W                        | 6,000 lm      | Wide beam  |
| 40928900   | WT120C G2 LED80S/840 PSU L1500      | 4000 K                             | 140 lm/W                        | 8,000 lm      | Wide beam  |
| 36934199   | WT120C G2 LED34S/865 PSU L1500      | 6500 K                             | 139 lm/W                        | 3,400 lm      | Wide beam  |
| 36935899   | WT120C G2 LED60S/865 PSU L1500      | 6500 K                             | 140 lm/W                        | 6,000 lm      | Wide beam  |

Operating and Electrical

| Order Code | Full Product Name                      | Power Consumption | Suitable for random switching |
|------------|----------------------------------------|-------------------|-------------------------------|
| 91685800   | WT120C G2 LED27S/840 PSU TW3 L1200     | 21.5 W            | Not applicable                |
| 96248700   | WT120C G2 LED27S/840 PSU MDU L1200     | 22 W              | Yes                           |
| 96249400   | WT120C G2 LED27S/840 PSU MDU TW3 L1200 | 22 W              | Yes                           |
| 85418000   | WT120C G2 LED27S/840 PSU ELB3 L1200    | 26 W              | Not applicable                |
| 88307500   | WT120C G2 LED27S/840 PSD L1200         | 22 W              | Not applicable                |
| 88311200   | WT120C G2 LED27S/840 PSD ELB3 L1200    | 27 W              | Not applicable                |
| 91687200   | WT120C G2 LED40S/840 PSU TW3 L1200     | 30 W              | Not applicable                |
| 96257900   | WT120C G2 LED40S/840 PSU MDU TW3 L1200 | 30 W              | Yes                           |

| Order Code | Full Product Name                      | Power Consumption | Suitable for random switching |
|------------|----------------------------------------|-------------------|-------------------------------|
| 16316700   | WT120C G2 LED40S/840 PSU WEC L1200     | 29 W              | Not applicable                |
| 16317400   | WT120C G2 LED40S/840 PSU TW1 WEC L1200 | 29.5 W            | Not applicable                |
| 88309900   | WT120C G2 LED40S/840 PSD L1200         | 30.5 W            | Not applicable                |
| 85419700   | WT120C G2 LED40S/840 PSU ELB3 L1200    | 33 W              | Not applicable                |
| 88312900   | WT120C G2 LED40S/840 PSD ELB3 L1200    | 35.5 W            | Not applicable                |
| 84046600   | WT120C G2 LED27S/840 PSU L1200         | 20.5 W            | Not applicable                |
| 84048099   | WT120C G2 LED40S/840 PSU L1200         | 28.6 W            | Not applicable                |
| 36933499   | WT120C G2 LED40S/865 PSU L1200         | 28.5 W            | Not applicable                |

CoreLine Waterproof

| Order Code | Full Product Name                      | Power Consumption | Suitable for random switching |  |
|------------|----------------------------------------|-------------------|-------------------------------|--|
| 34976399   | WT120C G2 LED18S/840 PSU PCO L600      | 15 W              | Not applicable                |  |
| 34977099   | WT120C G2 LED25S/840 PSU PCO L1200     | 20.5 W            | Not applicable                |  |
| 34978799   | WT120C G2 LED31S/840 PSU PCO L1500     | 24.3 W            | Not applicable                |  |
| 34979499   | WT120C G2 LED37S/840 PSU PCO L1200     | 28.6 W            | Not applicable                |  |
| 34980099   | WT120C G2 LED57S/840 PSU PCO L1500     | 42.9 W            | Not applicable                |  |
| 34981799   | WT120C G2 LED75S/840 PSU PCO L1500     | 57.1 W            | Not applicable                |  |
| 96244900   | WT120C G2 LED19S/840 PSU MDU L600      | 16.4 W            | Yes                           |  |
| 88306800   | WT120C G2 LED19S/840 PSD L600          | 16.5 W            | Not applicable                |  |
| 84045900   | WT120C G2 LED19S/840 PSU L600          | 15 W              | Not applicable                |  |
| 91686500   | WT120C G2 LED34S/840 PSU TW3 L1500     | 25.5 W            | Not applicable                |  |
| 96267800   | WT120C G2 LED34S/840 PSU MDU L1500     | 26 W              | Yes                           |  |
| 96268500   | WT120C G2 LED34S/840 PSU MDU TW3 L1500 | 26 W              | Yes                           |  |
| 88308200   | WT120C G2 LED34S/840 PSD L1500         | 26 W              | Not applicable                |  |
| 85420300   | WT120C G2 LED34S/840 PSU ELB3 L1500    | 30 W              | Not applicable                |  |
| 88313600   | WT120C G2 LED34S/840 PSD ELB3 L1500    | 31 W              | Not applicable                |  |
| 91688900   | WT120C G2 LED60S/840 PSU TW3 L1500     | 44.5 W            | Not applicable                |  |
| 96275300   | WT120C G2 LED60S/840 PSU MDU L1500     | 45 W              | Yes                           |  |

Controls and Dimming

| Order Code | Full Product Name                      | Dimmable | Embedded control                   | Maximum dim level |
|------------|----------------------------------------|----------|------------------------------------|-------------------|
| 91685800   | WT120C G2 LED27S/840 PSU TW3 L1200     | No       | -                                  | Not applicable    |
| 96248700   | WT120C G2 LED27S/840 PSU MDU L1200     | Yes      | Movement and light sensor (On/Off) | Not applicable    |
| 96249400   | WT120C G2 LED27S/840 PSU MDU TW3 L1200 | Yes      | Movement and light sensor (On/Off) | Not applicable    |
| 85418000   | WT120C G2 LED27S/840 PSU ELB3 L1200    | No       | -                                  | Not applicable    |

| Order Code | Full Product Name                      | Power Consumption | Suitable for random switching |  |
|------------|----------------------------------------|-------------------|-------------------------------|--|
| 96276000   | WT120C G2 LED60S/840 PSU MDU TW3 L1500 | 45 W              | Yes                           |  |
| 16318100   | WT120C G2 LED60S/840 PSU WEC L1500     | 44.5 W            | Not applicable                |  |
| 16319800   | WT120C G2 LED60S/840 PSU TW1 WEC L1500 | 44 W              | Not applicable                |  |
| 88310500   | WT120C G2 LED60S/840 PSD L1500         | 45 W              | Not applicable                |  |
| 85421000   | WT120C G2 LED60S/840 PSU ELB3 L1500    | 49.5 W            | Not applicable                |  |
| 88314300   | WT120C G2 LED60S/840 PSD ELB3 L1500    | 49.5 W            | Not applicable                |  |
| 40930200   | WT120C G2 LED80S/840 PSU TW3 L1500     | 60 W              | Not applicable                |  |
| 96286900   | WT120C G2 LED80S/840 PSU MDU L1500     | 61 W              | Yes                           |  |
| 40929600   | WT120C G2 LED80S/840 PSD L1500         | 62 W              | Not applicable                |  |
| 40931900   | WT120C G2 LED80S/840 PSU L1500 ELB3    | 63.5 W            | Not applicable                |  |
| 97578400   | WT120C G2 LED65S/840 WIA L1500         | 45 W              | Not applicable                |  |
| 84047399   | WT120C G2 LED34S/840 PSU L1500         | 24.3 W            | Not applicable                |  |
| 84049700   | WT120C G2 LED60S/840 PSU L1500         | 42.9 W            | Not applicable                |  |
| 40928900   | WT120C G2 LED80S/840 PSU L1500         | 57.1 W            | Not applicable                |  |
| 36934199   | WT120C G2 LED34S/865 PSU L1500         | 24.5 W            | Not applicable                |  |
| 36935899   | WT120C G2 LED60S/865 PSU L1500         | 43 W              | Not applicable                |  |

| Order Code | Full Product Name                      | Dimmable | Embedded control                   | Maximum dim level |
|------------|----------------------------------------|----------|------------------------------------|-------------------|
| 88307500   | WT120C G2 LED27S/840 PSD L1200         | Yes      | -                                  | 1%                |
| 88311200   | WT120C G2 LED27S/840 PSD ELB3 L1200    | Yes      | -                                  | 1%                |
| 91687200   | WT120C G2 LED40S/840 PSU TW3 L1200     | No       | -                                  | Not applicable    |
| 96257900   | WT120C G2 LED40S/840 PSU MDU TW3 L1200 | Yes      | Movement and light sensor (On/Off) | Not applicable    |
| 16316700   | WT120C G2 LED40S/840 PSU WEC L1200     | No       | -                                  | Not applicable    |

## CoreLine Waterproof

| Order Code | Full Product Name                      | Dimmable | Embedded control                   | Maximum dim level |
|------------|----------------------------------------|----------|------------------------------------|-------------------|
| 16317400   | WT120C G2 LED40S/840 PSU TW1 WEC L1200 | No       | -                                  | Not applicable    |
| 88309900   | WT120C G2 LED40S/840 PSD L1200         | Yes      | -                                  | 1%                |
| 85419700   | WT120C G2 LED40S/840 PSU ELB3 L1200    | No       | -                                  | Not applicable    |
| 88312900   | WT120C G2 LED40S/840 PSD ELB3 L1200    | Yes      | -                                  | 1%                |
| 84046600   | WT120C G2 LED27S/840 PSU L1200         | No       | -                                  | Not applicable    |
| 84048099   | WT120C G2 LED40S/840 PSU L1200         | No       | -                                  | Not applicable    |
| 36933499   | WT120C G2 LED40S/865 PSU L1200         | No       | -                                  | Not applicable    |
| 34976399   | WT120C G2 LED18S/840 PSU PCO L600      | No       | -                                  | Not applicable    |
| 34977099   | WT120C G2 LED25S/840 PSU PCO L1200     | No       | -                                  | Not applicable    |
| 34978799   | WT120C G2 LED31S/840 PSU PCO L1500     | No       | -                                  | Not applicable    |
| 34979499   | WT120C G2 LED37S/840 PSU PCO L1200     | No       | -                                  | Not applicable    |
| 34980099   | WT120C G2 LED57S/840 PSU PCO L1500     | No       | -                                  | Not applicable    |
| 34981799   | WT120C G2 LED75S/840 PSU PCO L1500     | No       | -                                  | Not applicable    |
| 96244900   | WT120C G2 LED19S/840 PSU MDU L600      | Yes      | Movement and light sensor (On/Off) | Not applicable    |
| 88306800   | WT120C G2 LED19S/840 PSD L600          | Yes      | -                                  | 1%                |
| 84045900   | WT120C G2 LED19S/840 PSU L600          | No       | -                                  | Not applicable    |
| 91686500   | WT120C G2 LED34S/840 PSU TW3 L1500     | No       | -                                  | Not applicable    |
| 96267800   | WT120C G2 LED34S/840 PSU MDU L1500     | Yes      | Movement and light sensor (On/Off) | Not applicable    |
| 96268500   | WT120C G2 LED34S/840 PSU MDU TW3 L1500 | Yes      | Movement and light sensor (On/Off) | Not applicable    |
| 88308200   | WT120C G2 LED34S/840 PSD L1500         | Yes      | -                                  | 1%                |

| Order Code | Full Product Name                      | Dimmable | Embedded control                   | Maximum dim level |
|------------|----------------------------------------|----------|------------------------------------|-------------------|
| 85420300   | WT120C G2 LED34S/840 PSU ELB3 L1500    | No       | -                                  | Not applicable    |
| 88313600   | WT120C G2 LED34S/840 PSD ELB3 L1500    | Yes      | -                                  | 1%                |
| 91688900   | WT120C G2 LED60S/840 PSU TW3 L1500     | No       | -                                  | Not applicable    |
| 96275300   | WT120C G2 LED60S/840 PSU MDU L1500     | Yes      | Movement and light sensor (On/Off) | Not applicable    |
| 96276000   | WT120C G2 LED60S/840 PSU MDU TW3 L1500 | Yes      | Movement and light sensor (On/Off) | Not applicable    |
| 16318100   | WT120C G2 LED60S/840 PSU WEC L1500     | No       | -                                  | Not applicable    |
| 16319800   | WT120C G2 LED60S/840 PSU TW1 WEC L1500 | No       | -                                  | Not applicable    |
| 88310500   | WT120C G2 LED60S/840 PSD L1500         | Yes      | -                                  | 1%                |
| 85421000   | WT120C G2 LED60S/840 PSU ELB3 L1500    | No       | -                                  | Not applicable    |
| 88314300   | WT120C G2 LED60S/840 PSD ELB3 L1500    | Yes      | -                                  | 1%                |
| 40930200   | WT120C G2 LED80S/840 PSU TW3 L1500     | No       | -                                  | Not applicable    |
| 96286900   | WT120C G2 LED80S/840 PSU MDU L1500     | Yes      | Movement and light sensor (On/Off) | Not applicable    |
| 40929600   | WT120C G2 LED80S/840 PSD L1500         | Yes      | -                                  | 1%                |
| 40931900   | WT120C G2 LED80S/840 PSU L1500 ELB3    | No       | -                                  | Not applicable    |
| 97578400   | WT120C G2 LED65S/840 WIA L1500         | Yes      | -                                  | 10%               |
| 84047399   | WT120C G2 LED34S/840 PSU L1500         | No       | -                                  | Not applicable    |
| 84049700   | WT120C G2 LED60S/840 PSU L1500         | No       | -                                  | Not applicable    |
| 40928900   | WT120C G2 LED80S/840 PSU L1500         | No       | -                                  | Not applicable    |
| 36934199   | WT120C G2 LED34S/865 PSU L1500         | No       | -                                  | Not applicable    |
| 36935899   | WT120C G2 LED60S/865 PSU L1500         | No       | -                                  | Not applicable    |

### Emergency Operation (1/2)



## CoreLine Waterproof

| Order Code | Full Product Name                            | Central Emergency | Emergency lighting                                | Emergency flux | Type of emergency lighting battery |
|------------|----------------------------------------------|-------------------|---------------------------------------------------|----------------|------------------------------------|
| 91685800   | WT120C G2<br>LED27S/840 PSU<br>TW3 L1200     | -                 | -                                                 | -              | -                                  |
| 96248700   | WT120C G2<br>LED27S/840 PSU<br>MDU L1200     | -                 | -                                                 | -              | -                                  |
| 96249400   | WT120C G2<br>LED27S/840 PSU<br>MDU TW3 L1200 | -                 | -                                                 | -              | -                                  |
| 85418000   | WT120C G2<br>LED27S/840 PSU<br>ELB3 L1200    | No                | Emergency lighting 3 hours duration basic version | 500 lm         | Lithium                            |
| 88307500   | WT120C G2<br>LED27S/840<br>PSD L1200         | -                 | -                                                 | -              | -                                  |
| 88311200   | WT120C G2<br>LED27S/840<br>PSD ELB3 L1200    | No                | Emergency lighting 3 hours duration basic version | 500 lm         | Lithium                            |
| 91687200   | WT120C G2<br>LED40S/840<br>PSU TW3 L1200     | -                 | -                                                 | -              | -                                  |
| 96257900   | WT120C G2<br>LED40S/840<br>PSU MDU TW3 L1200 | -                 | -                                                 | -              | -                                  |
| 16316700   | WT120C G2<br>LED40S/840<br>PSU WEC L1200     | -                 | -                                                 | -              | -                                  |
| 16317400   | WT120C G2<br>LED40S/840<br>PSU TW1 WEC L1200 | -                 | -                                                 | -              | -                                  |
| 88309900   | WT120C G2<br>LED40S/840<br>PSD L1200         | -                 | -                                                 | -              | -                                  |
| 85419700   | WT120C G2<br>LED40S/840<br>PSU ELB3 L1200    | No                | Emergency lighting 3 hours duration basic version | 500 lm         | Lithium                            |
| 88312900   | WT120C G2<br>LED40S/840<br>PSD ELB3 L1200    | No                | Emergency lighting 3 hours duration basic version | 500 lm         | Lithium                            |

| Order Code | Full Product Name                            | Central Emergency | Emergency lighting | Emergency flux | Type of emergency lighting battery |
|------------|----------------------------------------------|-------------------|--------------------|----------------|------------------------------------|
| 84046600   | WT120C G2<br>LED27S/840 PSU<br>L1200         | -                 | -                  | -              | -                                  |
| 84048099   | WT120C G2<br>LED40S/840<br>PSU L1200         | -                 | -                  | -              | -                                  |
| 36933499   | WT120C G2<br>LED40S/865<br>PSU L1200         | -                 | -                  | -              | -                                  |
| 34976399   | WT120C G2<br>LED18S/840 PSU<br>PCO L600      | -                 | -                  | -              | -                                  |
| 34977099   | WT120C G2<br>LED25S/840<br>PSU PCO L1200     | -                 | -                  | -              | -                                  |
| 34978799   | WT120C G2<br>LED31S/840 PSU<br>PCO L1500     | -                 | -                  | -              | -                                  |
| 34979499   | WT120C G2<br>LED37S/840<br>PSU PCO L1200     | -                 | -                  | -              | -                                  |
| 34980099   | WT120C G2<br>LED57S/840<br>PSU PCO L1500     | -                 | -                  | -              | -                                  |
| 34981799   | WT120C G2<br>LED75S/840<br>PSU PCO L1500     | -                 | -                  | -              | -                                  |
| 96244900   | WT120C G2<br>LED19S/840 PSU<br>MDU L600      | -                 | -                  | -              | -                                  |
| 88306800   | WT120C G2<br>LED19S/840 PSD<br>L600          | -                 | -                  | -              | -                                  |
| 84045900   | WT120C G2<br>LED19S/840 PSU<br>L600          | -                 | -                  | -              | -                                  |
| 91686500   | WT120C G2<br>LED34S/840<br>PSU TW3 L1500     | -                 | -                  | -              | -                                  |
| 96267800   | WT120C G2<br>LED34S/840<br>PSU MDU L1500     | -                 | -                  | -              | -                                  |
| 96268500   | WT120C G2<br>LED34S/840<br>PSU MDU TW3 L1500 | -                 | -                  | -              | -                                  |
| 88308200   | WT120C G2<br>LED34S/840<br>PSD L1500         | -                 | -                  | -              | -                                  |

## CoreLine Waterproof

| Order Code | Full Product Name                            | Central Emergency | Emergency lighting                                | Emergency flux | Type of emergency lighting battery |
|------------|----------------------------------------------|-------------------|---------------------------------------------------|----------------|------------------------------------|
| 85420300   | WT120C G2<br>LED34S/840<br>PSU ELB3 L1500    | No                | Emergency lighting 3 hours duration basic version | 500 lm         | Lithium                            |
| 88313600   | WT120C G2<br>LED34S/840<br>PSD ELB3 L1500    | No                | Emergency lighting 3 hours duration basic version | 500 lm         | Lithium                            |
| 91688900   | WT120C G2<br>LED60S/840<br>PSU TW3 L1500     | -                 | -                                                 | -              | -                                  |
| 96275300   | WT120C G2<br>LED60S/840<br>PSU MDU L1500     | -                 | -                                                 | -              | -                                  |
| 96276000   | WT120C G2<br>LED60S/840<br>PSU MDU TW3 L1500 | -                 | -                                                 | -              | -                                  |
| 16318100   | WT120C G2<br>LED60S/840<br>PSU WEC L1500     | -                 | -                                                 | -              | -                                  |
| 16319800   | WT120C G2<br>LED60S/840<br>PSU TW1 WEC L1500 | -                 | -                                                 | -              | -                                  |
| 88310500   | WT120C G2<br>LED60S/840<br>PSD L1500         | -                 | -                                                 | -              | -                                  |
| 85421000   | WT120C G2<br>LED60S/840<br>PSU ELB3 L1500    | No                | Emergency lighting 3 hours duration basic version | 500 lm         | Lithium                            |
| 88314300   | WT120C G2<br>LED60S/840<br>PSD ELB3 L1500    | No                | Emergency lighting 3 hours duration basic version | 500 lm         | Lithium                            |

| Order Code | Full Product Name                         | Central Emergency | Emergency lighting                                | Emergency flux | Type of emergency lighting battery |
|------------|-------------------------------------------|-------------------|---------------------------------------------------|----------------|------------------------------------|
| 40930200   | WT120C G2<br>LED80S/840<br>PSU TW3 L1500  | -                 | -                                                 | -              | -                                  |
| 96286900   | WT120C G2<br>LED80S/840<br>PSU MDU L1500  | -                 | -                                                 | -              | -                                  |
| 40929600   | WT120C G2<br>LED80S/840<br>PSD L1500      | -                 | -                                                 | -              | -                                  |
| 40931900   | WT120C G2<br>LED80S/840<br>PSU L1500 ELB3 | No                | Emergency lighting 3 hours duration basic version | 500 lm         | Lithium                            |
| 97578400   | WT120C G2<br>LED65S/840<br>WIA L1500      | -                 | -                                                 | -              | -                                  |
| 84047399   | WT120C G2<br>LED34S/840<br>PSU L1500      | -                 | -                                                 | -              | -                                  |
| 84049700   | WT120C G2<br>LED60S/840<br>PSU L1500      | -                 | -                                                 | -              | -                                  |
| 40928900   | WT120C G2<br>LED80S/840<br>PSU L1500      | -                 | -                                                 | -              | -                                  |
| 36934199   | WT120C G2<br>LED34S/865<br>PSU L1500      | -                 | -                                                 | -              | -                                  |
| 36935899   | WT120C G2<br>LED60S/865<br>PSU L1500      | -                 | -                                                 | -              | -                                  |

### Emergency Operation (2/2)

| Order Code | Full Product Name                      | Rated duration of the emergency lighting (when fully charged) |
|------------|----------------------------------------|---------------------------------------------------------------|
| 91685800   | WT120C G2 LED27S/840 PSU TW3 L1200     | -                                                             |
| 96248700   | WT120C G2 LED27S/840 PSU MDU L1200     | -                                                             |
| 96249400   | WT120C G2 LED27S/840 PSU MDU TW3 L1200 | -                                                             |

| Order Code | Full Product Name                   | Rated duration of the emergency lighting (when fully charged) |
|------------|-------------------------------------|---------------------------------------------------------------|
| 85418000   | WT120C G2 LED27S/840 PSU ELB3 L1200 | 3 hour(s)                                                     |
| 88307500   | WT120C G2 LED27S/840 PSD L1200      | -                                                             |
| 88311200   | WT120C G2 LED27S/840 PSD ELB3 L1200 | 3 hour(s)                                                     |

CoreLine Waterproof

| Order Code | Full Product Name                      | Rated duration of the emergency lighting (when fully charged) |
|------------|----------------------------------------|---------------------------------------------------------------|
| 91687200   | WT120C G2 LED40S/840 PSU TW3 L1200     | -                                                             |
| 96257900   | WT120C G2 LED40S/840 PSU MDU TW3 L1200 | -                                                             |
| 16316700   | WT120C G2 LED40S/840 PSU WEC L1200     | -                                                             |
| 16317400   | WT120C G2 LED40S/840 PSU TW1 WEC L1200 | -                                                             |
| 88309900   | WT120C G2 LED40S/840 PSD L1200         | -                                                             |
| 85419700   | WT120C G2 LED40S/840 PSU ELB3 L1200    | 3 hour(s)                                                     |
| 88312900   | WT120C G2 LED40S/840 PSD ELB3 L1200    | 3 hour(s)                                                     |
| 84046600   | WT120C G2 LED27S/840 PSU L1200         | -                                                             |
| 84048099   | WT120C G2 LED40S/840 PSU L1200         | -                                                             |
| 36933499   | WT120C G2 LED40S/865 PSU L1200         | -                                                             |
| 34976399   | WT120C G2 LED18S/840 PSU PCO L600      | -                                                             |
| 34977099   | WT120C G2 LED25S/840 PSU PCO L1200     | -                                                             |
| 34978799   | WT120C G2 LED31S/840 PSU PCO L1500     | -                                                             |
| 34979499   | WT120C G2 LED37S/840 PSU PCO L1200     | -                                                             |
| 34980099   | WT120C G2 LED57S/840 PSU PCO L1500     | -                                                             |
| 34981799   | WT120C G2 LED75S/840 PSU PCO L1500     | -                                                             |
| 96244900   | WT120C G2 LED19S/840 PSU MDU L600      | -                                                             |
| 88306800   | WT120C G2 LED19S/840 PSD L600          | -                                                             |
| 84045900   | WT120C G2 LED19S/840 PSU L600          | -                                                             |
| 91686500   | WT120C G2 LED34S/840 PSU TW3 L1500     | -                                                             |
| 96267800   | WT120C G2 LED34S/840 PSU MDU L1500     | -                                                             |
| 96268500   | WT120C G2 LED34S/840 PSU MDU TW3 L1500 | -                                                             |

Approval and Application

| Order Code | Full Product Name                      | Ambient temperature range |
|------------|----------------------------------------|---------------------------|
| 91685800   | WT120C G2 LED27S/840 PSU TW3 L1200     | -20 to +35 °C             |
| 96248700   | WT120C G2 LED27S/840 PSU MDU L1200     | -20 to +35 °C             |
| 96249400   | WT120C G2 LED27S/840 PSU MDU TW3 L1200 | -20 to +35 °C             |
| 85418000   | WT120C G2 LED27S/840 PSU ELB3 L1200    | 0 to +25 °C               |
| 88307500   | WT120C G2 LED27S/840 PSD L1200         | -20 to +35 °C             |
| 88311200   | WT120C G2 LED27S/840 PSD ELB3 L1200    | 0 to +25 °C               |
| 91687200   | WT120C G2 LED40S/840 PSU TW3 L1200     | -20 to +35 °C             |
| 96257900   | WT120C G2 LED40S/840 PSU MDU TW3 L1200 | -20 to +35 °C             |
| 16316700   | WT120C G2 LED40S/840 PSU WEC L1200     | -20 to +35 °C             |
| 16317400   | WT120C G2 LED40S/840 PSU TW1 WEC L1200 | -20 to +35 °C             |
| 88309900   | WT120C G2 LED40S/840 PSD L1200         | -20 to +35 °C             |
| 85419700   | WT120C G2 LED40S/840 PSU ELB3 L1200    | 0 to +25 °C               |
| 88312900   | WT120C G2 LED40S/840 PSD ELB3 L1200    | 0 to +25 °C               |
| 84046600   | WT120C G2 LED27S/840 PSU L1200         | -20 to +40 °C             |
| 84048099   | WT120C G2 LED40S/840 PSU L1200         | -20 to +40 °C             |
| 36933499   | WT120C G2 LED40S/865 PSU L1200         | -20 to +40 °C             |
| 34976399   | WT120C G2 LED18S/840 PSU PCO L600      | -20 to +40 °C             |
| 34977099   | WT120C G2 LED25S/840 PSU PCO L1200     | -20 to +40 °C             |
| 34978799   | WT120C G2 LED31S/840 PSU PCO L1500     | -20 to +40 °C             |
| 34979499   | WT120C G2 LED37S/840 PSU PCO L1200     | -20 to +40 °C             |
| 34980099   | WT120C G2 LED57S/840 PSU PCO L1500     | -20 to +40 °C             |

| Order Code | Full Product Name                      | Rated duration of the emergency lighting (when fully charged) |
|------------|----------------------------------------|---------------------------------------------------------------|
| 88308200   | WT120C G2 LED34S/840 PSD L1500         | -                                                             |
| 85420300   | WT120C G2 LED34S/840 PSU ELB3 L1500    | 3 hour(s)                                                     |
| 88313600   | WT120C G2 LED34S/840 PSD ELB3 L1500    | 3 hour(s)                                                     |
| 91688900   | WT120C G2 LED60S/840 PSU TW3 L1500     | -                                                             |
| 96275300   | WT120C G2 LED60S/840 PSU MDU L1500     | -                                                             |
| 96276000   | WT120C G2 LED60S/840 PSU MDU TW3 L1500 | -                                                             |
| 16318100   | WT120C G2 LED60S/840 PSU WEC L1500     | -                                                             |
| 16319800   | WT120C G2 LED60S/840 PSU TW1 WEC L1500 | -                                                             |
| 88310500   | WT120C G2 LED60S/840 PSD L1500         | -                                                             |
| 85421000   | WT120C G2 LED60S/840 PSU ELB3 L1500    | 3 hour(s)                                                     |
| 88314300   | WT120C G2 LED60S/840 PSD ELB3 L1500    | 3 hour(s)                                                     |
| 40930200   | WT120C G2 LED80S/840 PSU TW3 L1500     | -                                                             |
| 96286900   | WT120C G2 LED80S/840 PSU MDU L1500     | -                                                             |
| 40929600   | WT120C G2 LED80S/840 PSD L1500         | -                                                             |
| 40931900   | WT120C G2 LED80S/840 PSU L1500 ELB3    | 3 hour(s)                                                     |
| 97578400   | WT120C G2 LED65S/840 WIA L1500         | -                                                             |
| 84047399   | WT120C G2 LED34S/840 PSU L1500         | -                                                             |
| 84049700   | WT120C G2 LED60S/840 PSU L1500         | -                                                             |
| 40928900   | WT120C G2 LED80S/840 PSU L1500         | -                                                             |
| 36934199   | WT120C G2 LED34S/865 PSU L1500         | -                                                             |
| 36935899   | WT120C G2 LED60S/865 PSU L1500         | -                                                             |

| Order Code | Full Product Name                      | Ambient temperature range |
|------------|----------------------------------------|---------------------------|
| 34981799   | WT120C G2 LED75S/840 PSU PCO L1500     | -20 to +40 °C             |
| 96244900   | WT120C G2 LED19S/840 PSU MDU L600      | -20 to +35 °C             |
| 88306800   | WT120C G2 LED19S/840 PSD L600          | -20 to +35 °C             |
| 84045900   | WT120C G2 LED19S/840 PSU L600          | -20 to +40 °C             |
| 91686500   | WT120C G2 LED34S/840 PSU TW3 L1500     | -20 to +35 °C             |
| 96267800   | WT120C G2 LED34S/840 PSU MDU L1500     | -20 to +35 °C             |
| 96268500   | WT120C G2 LED34S/840 PSU MDU TW3 L1500 | -20 to +35 °C             |
| 88308200   | WT120C G2 LED34S/840 PSD L1500         | -20 to +35 °C             |
| 85420300   | WT120C G2 LED34S/840 PSU ELB3 L1500    | 0 to +25 °C               |
| 88313600   | WT120C G2 LED34S/840 PSD ELB3 L1500    | 0 to +25 °C               |
| 91688900   | WT120C G2 LED60S/840 PSU TW3 L1500     | -20 to +35 °C             |
| 96275300   | WT120C G2 LED60S/840 PSU MDU L1500     | -20 to +35 °C             |
| 96276000   | WT120C G2 LED60S/840 PSU MDU TW3 L1500 | -20 to +35 °C             |
| 16318100   | WT120C G2 LED60S/840 PSU WEC L1500     | -20 to +35 °C             |
| 16319800   | WT120C G2 LED60S/840 PSU TW1 WEC L1500 | -20 to +35 °C             |
| 88310500   | WT120C G2 LED60S/840 PSD L1500         | -20 to +35 °C             |
| 85421000   | WT120C G2 LED60S/840 PSU ELB3 L1500    | 0 to +25 °C               |
| 88314300   | WT120C G2 LED60S/840 PSD ELB3 L1500    | 0 to +25 °C               |
| 40930200   | WT120C G2 LED80S/840 PSU TW3 L1500     | -20 to +35 °C             |
| 96286900   | WT120C G2 LED80S/840 PSU MDU L1500     | -20 to +35 °C             |
| 40929600   | WT120C G2 LED80S/840 PSD L1500         | -20 to +35 °C             |

CoreLine Waterproof

| Order Code | Full Product Name                   | Ambient temperature range |
|------------|-------------------------------------|---------------------------|
| 40931900   | WT120C G2 LED80S/840 PSU L1500 ELB3 | 0 to +25 °C               |
| 97578400   | WT120C G2 LED65S/840 WIA L1500      | -20 to +35 °C             |
| 84047399   | WT120C G2 LED34S/840 PSU L1500      | -20 to +40 °C             |
| 84049700   | WT120C G2 LED60S/840 PSU L1500      | -20 to +40 °C             |

| Order Code | Full Product Name              | Ambient temperature range |
|------------|--------------------------------|---------------------------|
| 40928900   | WT120C G2 LED80S/840 PSU L1500 | -20 to +40 °C             |
| 36934199   | WT120C G2 LED34S/865 PSU L1500 | -20 to +40 °C             |
| 36935899   | WT120C G2 LED60S/865 PSU L1500 | -20 to +40 °C             |

Initial Performance (IEC Compliant)

| Order Code | Full Product Name                      | Initial chromaticity |
|------------|----------------------------------------|----------------------|
| 91685800   | WT120C G2 LED27S/840 PSU TW3 L1200     | (0.38,0.38)SDCM<=3   |
| 96248700   | WT120C G2 LED27S/840 PSU MDU L1200     | (0.38,0.38)SDCM<=3   |
| 96249400   | WT120C G2 LED27S/840 PSU MDU TW3 L1200 | (0.38,0.38)SDCM<=3   |
| 85418000   | WT120C G2 LED27S/840 PSU ELB3 L1200    | (0.38,0.38)SDCM<=3   |
| 88307500   | WT120C G2 LED27S/840 PSD L1200         | (0.38,0.38)SDCM<=3   |
| 88311200   | WT120C G2 LED27S/840 PSD ELB3 L1200    | (0.38,0.38)SDCM<=3   |
| 91687200   | WT120C G2 LED40S/840 PSU TW3 L1200     | (0.38,0.38)SDCM<=3   |
| 96257900   | WT120C G2 LED40S/840 PSU MDU TW3 L1200 | (0.38,0.38)SDCM<=3   |
| 16316700   | WT120C G2 LED40S/840 PSU WEC L1200     | (0.38,0.38)SDCM<=3   |
| 16317400   | WT120C G2 LED40S/840 PSU TW1 WEC L1200 | (0.38,0.38)SDCM<=3   |
| 88309900   | WT120C G2 LED40S/840 PSD L1200         | (0.38,0.38)SDCM<=3   |
| 85419700   | WT120C G2 LED40S/840 PSU ELB3 L1200    | (0.38,0.38)SDCM<=3   |
| 88312900   | WT120C G2 LED40S/840 PSD ELB3 L1200    | (0.38,0.38)SDCM<=3   |
| 84046600   | WT120C G2 LED27S/840 PSU L1200         | (0.38,0.38)SDCM<=3   |
| 84048099   | WT120C G2 LED40S/840 PSU L1200         | (0.38,0.38)SDCM<=3   |
| 36933499   | WT120C G2 LED40S/865 PSU L1200         | (0.31,0.32)SDCM<=3   |
| 34976399   | WT120C G2 LED18S/840 PSU PCO L600      | (0.38,0.38)SDCM<=3   |
| 34977099   | WT120C G2 LED25S/840 PSU PCO L1200     | (0.38,0.38)SDCM<=3   |
| 34978799   | WT120C G2 LED31S/840 PSU PCO L1500     | (0.38,0.38)SDCM<=3   |
| 34979499   | WT120C G2 LED37S/840 PSU PCO L1200     | (0.38,0.38)SDCM<=3   |
| 34980099   | WT120C G2 LED57S/840 PSU PCO L1500     | (0.38,0.38)SDCM<=3   |
| 34981799   | WT120C G2 LED75S/840 PSU PCO L1500     | (0.38,0.38)SDCM<=3   |
| 96244900   | WT120C G2 LED19S/840 PSU MDU L600      | (0.38,0.38)SDCM<=3   |
| 88306800   | WT120C G2 LED19S/840 PSD L600          | (0.38,0.38)SDCM<=3   |
| 84045900   | WT120C G2 LED19S/840 PSU L600          | (0.38,0.38)SDCM<=3   |

| Order Code | Full Product Name                      | Initial chromaticity |
|------------|----------------------------------------|----------------------|
| 91686500   | WT120C G2 LED34S/840 PSU TW3 L1500     | (0.38,0.38)SDCM<=3   |
| 96267800   | WT120C G2 LED34S/840 PSU MDU L1500     | (0.38,0.38)SDCM<=3   |
| 96268500   | WT120C G2 LED34S/840 PSU MDU TW3 L1500 | (0.38,0.38)SDCM<=3   |
| 88308200   | WT120C G2 LED34S/840 PSD L1500         | (0.38,0.38)SDCM<=3   |
| 85420300   | WT120C G2 LED34S/840 PSU ELB3 L1500    | (0.38,0.38)SDCM<=3   |
| 88313600   | WT120C G2 LED34S/840 PSD ELB3 L1500    | (0.38,0.38)SDCM<=3   |
| 91688900   | WT120C G2 LED60S/840 PSU TW3 L1500     | (0.38,0.38)SDCM<=3   |
| 96275300   | WT120C G2 LED60S/840 PSU MDU L1500     | (0.38,0.38)SDCM<=3   |
| 96276000   | WT120C G2 LED60S/840 PSU MDU TW3 L1500 | (0.38,0.38)SDCM<=3   |
| 16318100   | WT120C G2 LED60S/840 PSU WEC L1500     | (0.38,0.38)SDCM<=3   |
| 16319800   | WT120C G2 LED60S/840 PSU TW1 WEC L1500 | (0.38,0.38)SDCM<=3   |
| 88310500   | WT120C G2 LED60S/840 PSD L1500         | (0.38,0.38)SDCM<=3   |
| 85421000   | WT120C G2 LED60S/840 PSU ELB3 L1500    | (0.38,0.38)SDCM<=3   |
| 88314300   | WT120C G2 LED60S/840 PSD ELB3 L1500    | (0.38,0.38)SDCM<=3   |
| 40930200   | WT120C G2 LED80S/840 PSU TW3 L1500     | (0.38,0.38)SDCM<=3   |
| 96286900   | WT120C G2 LED80S/840 PSU MDU L1500     | (0.38,0.38)SDCM<=3   |
| 40929600   | WT120C G2 LED80S/840 PSD L1500         | (0.38,0.38)SDCM<=3   |
| 40931900   | WT120C G2 LED80S/840 PSU L1500 ELB3    | (0.38,0.38)SDCM<=3   |
| 97578400   | WT120C G2 LED65S/840 WIA L1500         | (0.38,0.38)SDCM<=3   |
| 84047399   | WT120C G2 LED34S/840 PSU L1500         | (0.38,0.38)SDCM<=3   |
| 84049700   | WT120C G2 LED60S/840 PSU L1500         | (0.38,0.38)SDCM<=3   |
| 40928900   | WT120C G2 LED80S/840 PSU L1500         | (0.38,0.38)SDCM<=3   |
| 36934199   | WT120C G2 LED34S/865 PSU L1500         | (0.31,0.32)SDCM<=3   |
| 36935899   | WT120C G2 LED60S/865 PSU L1500         | (0.31,0.32)SDCM<=3   |

Product Data




| Order Code | Full Product Name                      | Product family code |
|------------|----------------------------------------|---------------------|
| 91685800   | WT120C G2 LED27S/840 PSU TW3 L1200     | WT130C              |
| 96248700   | WT120C G2 LED27S/840 PSU MDU L1200     | WT130C              |
| 96249400   | WT120C G2 LED27S/840 PSU MDU TW3 L1200 | WT130C              |
| 85418000   | WT120C G2 LED27S/840 PSU ELB3 L1200    | WT130C              |
| 88307500   | WT120C G2 LED27S/840 PSD L1200         | WT130C              |
| 88311200   | WT120C G2 LED27S/840 PSD ELB3 L1200    | WT130C              |
| 91687200   | WT120C G2 LED40S/840 PSU TW3 L1200     | WT130C              |
| 96257900   | WT120C G2 LED40S/840 PSU MDU TW3 L1200 | WT130C              |
| 16316700   | WT120C G2 LED40S/840 PSU WEC L1200     | WT130C              |
| 16317400   | WT120C G2 LED40S/840 PSU TW1 WEC L1200 | WT130C              |
| 88309900   | WT120C G2 LED40S/840 PSD L1200         | WT130C              |
| 85419700   | WT120C G2 LED40S/840 PSU ELB3 L1200    | WT130C              |
| 88312900   | WT120C G2 LED40S/840 PSD ELB3 L1200    | WT130C              |
| 84046600   | WT120C G2 LED27S/840 PSU L1200         | -                   |

| Order Code | Full Product Name                      | Product family code |
|------------|----------------------------------------|---------------------|
| 84048099   | WT120C G2 LED40S/840 PSU L1200         | WT130C              |
| 36933499   | WT120C G2 LED40S/865 PSU L1200         | -                   |
| 34976399   | WT120C G2 LED18S/840 PSU PCO L600      | -                   |
| 34977099   | WT120C G2 LED25S/840 PSU PCO L1200     | -                   |
| 34978799   | WT120C G2 LED31S/840 PSU PCO L1500     | -                   |
| 34979499   | WT120C G2 LED37S/840 PSU PCO L1200     | -                   |
| 34980099   | WT120C G2 LED57S/840 PSU PCO L1500     | -                   |
| 34981799   | WT120C G2 LED75S/840 PSU PCO L1500     | -                   |
| 96244900   | WT120C G2 LED19S/840 PSU MDU L600      | WT130C              |
| 88306800   | WT120C G2 LED19S/840 PSD L600          | WT130C              |
| 84045900   | WT120C G2 LED19S/840 PSU L600          | -                   |
| 91686500   | WT120C G2 LED34S/840 PSU TW3 L1500     | WT130C              |
| 96267800   | WT120C G2 LED34S/840 PSU MDU L1500     | WT130C              |
| 96268500   | WT120C G2 LED34S/840 PSU MDU TW3 L1500 | WT130C              |

| Order Code | Full Product Name                      | Product family code |
|------------|----------------------------------------|---------------------|
| 88308200   | WT120C G2 LED34S/840 PSD L1500         | WT130C              |
| 85420300   | WT120C G2 LED34S/840 PSU ELB3 L1500    | WT130C              |
| 88313600   | WT120C G2 LED34S/840 PSD ELB3 L1500    | WT130C              |
| 91688900   | WT120C G2 LED60S/840 PSU TW3 L1500     | WT130C              |
| 96275300   | WT120C G2 LED60S/840 PSU MDU L1500     | WT130C              |
| 96276000   | WT120C G2 LED60S/840 PSU MDU TW3 L1500 | WT130C              |
| 16318100   | WT120C G2 LED60S/840 PSU WEC L1500     | WT130C              |
| 16319800   | WT120C G2 LED60S/840 PSU TW1 WEC L1500 | WT130C              |
| 88310500   | WT120C G2 LED60S/840 PSD L1500         | WT130C              |
| 85421000   | WT120C G2 LED60S/840 PSU ELB3 L1500    | WT130C              |
| 88314300   | WT120C G2 LED60S/840 PSD ELB3 L1500    | WT130C              |

| Order Code | Full Product Name                   | Product family code |
|------------|-------------------------------------|---------------------|
| 40930200   | WT120C G2 LED80S/840 PSU TW3 L1500  | WT130C              |
| 96286900   | WT120C G2 LED80S/840 PSU MDU L1500  | WT130C              |
| 40929600   | WT120C G2 LED80S/840 PSD L1500      | WT130C              |
| 40931900   | WT120C G2 LED80S/840 PSU L1500 ELB3 | WT130C              |
| 97578400   | WT120C G2 LED65S/840 WIA L1500      | WT130C              |
| 84047399   | WT120C G2 LED34S/840 PSU L1500      | WT130C              |
| 84049700   | WT120C G2 LED60S/840 PSU L1500      | -                   |
| 40928900   | WT120C G2 LED80S/840 PSU L1500      | -                   |
| 36934199   | WT120C G2 LED34S/865 PSU L1500      | -                   |
| 36935899   | WT120C G2 LED60S/865 PSU L1500      | -                   |




Polar Wide Diagrams



Polar Normal (separate) - WT120CI - 910505100069

Polar Normal (separate) - WT120CI - 910505100036

Polar Normal (separate) - WT120CI - 910505100073




Polar Normal (separate) - WT120CI - 910505100067


Polar Normal (separate) - WT120CI - 910505100042

Polar Normal (separate) - WT120CI - 910505100054


Polar Wide Diagrams




Polar Normal (separate) - WT120CI - 910505100057




Polar Normal (separate) - WT120CI - 910505100072




Polar Normal (separate) - WT120CI - 910505100079




Polar Normal (separate) - WT120CI - 910505100077




Polar Normal (separate) - WT120CI - 910505100049




Polar Normal (separate) - WT120CI - 910505100040



Polar Normal (separate) - WT120CI - 910505100045




Polar Normal (separate) - WT120CI - 910505100064




Polar Normal (separate) - WT120CI - 910505100051


Polar Wide Diagrams




Polar Normal (separate) - WT120CI - 910505100039




Polar Normal (separate) - WT120CI - 910505100061




Polar Normal (separate) - WT120CI - 910505100041




Polar Normal (separate) - WT120CI - 910505100078




Polar Normal (separate) - WT120CI - 910505100047




Polar Normal (separate) - WT120CI - 910505100068



Polar Normal (separate) - WT120CI - 910505100060




Polar Normal (separate) - WT120CI - 910505100080




Polar Normal (separate) - WT120CI - 910505100044


Polar Wide Diagrams




Polar Normal (separate) - WT120CI - 910505100059




Polar Normal (separate) - WT120CI - 910505100062




Polar Normal (separate) - WT120CI - 910505100076




Polar Normal (separate) - WT120CI - 910505100070




Polar Normal (separate) - WT120CI - 910505100053




Polar Normal (separate) - WT120CI - 910505101271



Polar Normal (separate) - WT120CI - 910505100058




Polar Normal (separate) - WT120CI - 910505100038




Polar Normal (separate) - WT120CI - 910505100050







|                                                     |                                                     |                                                     |
|-----------------------------------------------------|-----------------------------------------------------|-----------------------------------------------------|
| Polar Normal (separate) - WT120CI -<br>911401823680 | Polar Normal (separate) - WT120CI -<br>911401823780 | Polar Normal (separate) - WT120CI -<br>910505100066 |
|-----------------------------------------------------|-----------------------------------------------------|-----------------------------------------------------|



Polar Normal (separate) - null - 911401837480      Polar Normal (separate) - null - 911401837080      Polar Normal (separate) - null - 911401837280




Polar Normal (separate) - null - 911401837180      Polar Normal (separate) - null - 911401824481      Polar Normal (separate) - null - 911401824381




Polar Normal (separate) - null - 911401824581      Polar Normal (separate) - null - 911401823480      Polar Normal (separate) - null - 911401823580


Polar Wide Diagrams




Polar Normal (separate) - null - 911401823880



Polar Normal (separate) - null - 911401823980



Polar Normal (separate) - null - 911401836980



Polar Normal (separate) - null - 911401837380

