



MSR Gold™ MiniFastFit – lamp replacement in seconds

MSR Gold™ MiniFastFit (Touring/Stage)

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Benefits

- Lamp replacement in just seconds
- Easy handling, smaller and lighter fixtures
- Reduces early lamp or lamp holder failures. Excellent current transfer
- High perceived brightness
- High beam intensity

Features

- Philips MiniFastFit
- Compact design
- Innovative gold plated pins
- High color temperature
- Very short arc

MSR Gold™ MiniFastFit (Touring/Stage)

Application

- Events
- Shows
- Touring/Stage


Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



MSR Gold™ 1000 MiniFastFit




XPPR_XDMSR_0008-Product photo



XPPR XDMSR 0015



Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR Gold 400 MiniFastFit 1CT/16	23.2 mm	3.0 mm	55 mm	57 mm	56 mm	111 mm	36.5 mm	36 mm	35.3 mm
MSR Gold 575/2 MiniFastFit 1CT/4	23.2 mm	3.5 mm	55 mm	57 mm	56 mm	112 mm	36.5 mm	36 mm	35.3 mm
MSR Gold 700 MiniFastFit 1CT/16	23 mm	3.5 mm	55 mm	57 mm	56 mm	116 mm	36.5 mm	36 mm	35.3 mm
MSR Gold 700/1 MiniFastFit 1CT/4	23.2 mm	3.8 mm	55 mm	57 mm	56 mm	112 mm	36.5 mm	36 mm	35.3 mm
MSR Gold 700/2 MiniFastFit 1CT/4	23.2 mm	3.8 mm	55 mm	57 mm	56 mm	112 mm	36.5 mm	36 mm	35.3 mm

MSR Gold™ MiniFastFit (Touring/Stage)

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR Gold 1000 MiniFastFit 1CT/4	26 mm	5.5 mm	55 mm	57 mm	56 mm	112 mm	36.5 mm	36 mm	35.3 mm

Product	D (max)	O	L (min)	L (max)	L	C (max)
MSR Gold 300/2 MiniFastFit 1CT/4	23 mm	5.0 mm	65.8 mm	67.8 mm	66.8 mm	126 mm

General Information	
Operating Position	UNIVERSAL
Controls and Dimming	
Dimmable	Yes

General Information

Order Code	Full Product Name	Cap-Base
928171405115	MSR Gold 1000 MiniFastFit 1CT/4	PGJX36
928177105115	MSR Gold 300/2 MiniFastFit 1CT/4	PGJX28
928184005115	MSR Gold 575/2 MiniFastFit 1CT/4	PGJX28
928194005114	MSR Gold 400 MiniFastFit 1CT/16	PGJX28

Order Code	Full Product Name	Cap-Base
928194105114	MSR Gold 700 MiniFastFit 1CT/16	PGJX28
928197405115	MSR Gold 700/1 MiniFastFit 1CT/4	PGJX28
928199905115	MSR Gold 700/2 MiniFastFit 1CT/4	PGJX28

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux (Min)	Luminous Flux
928171405115	MSR Gold 1000 MiniFastFit 1CT/4	6000 K	80	-	-	79,300 lm
928177105115	MSR Gold 300/2 MiniFastFit 1CT/4	9300 K	78	2	-	22,700 lm
928184005115	MSR Gold 575/2 MiniFastFit 1CT/4	7500 K	70	2	-	35,500 lm
928194005114	MSR Gold 400 MiniFastFit 1CT/16	6700 K	60	-	-	28,000 lm
928194105114	MSR Gold 700 MiniFastFit 1CT/16	6000 K	72	-	-	48,000 lm
928197405115	MSR Gold 700/1 MiniFastFit 1CT/4	5700 K	73	1	-	53,400 lm
928199905115	MSR Gold 700/2 MiniFastFit 1CT/4	7200 K	75	2	44,000 lm	48,000 lm

Operating and Electrical

MSR Gold™ MiniFastFit (Touring/Stage)

Order Code	Full Product Name	Lamp Current	
		(Nom)	Power Consumption
928171405115	MSR Gold 1000 MiniFastFit 1CT/4	11.4 A	1,000 W
928177105115	MSR Gold 300/2 MiniFastFit 1CT/4	3.75 A	300 W
928184005115	MSR Gold 575/2 MiniFastFit 1CT/4	10.2 A	575 W
928194005114	MSR Gold 400 MiniFastFit 1CT/16	7.2 A	400 W

Order Code	Full Product Name	Lamp Current	
		(Nom)	Power Consumption
928194105114	MSR Gold 700 MiniFastFit 1CT/16	10.8 A	700 W
928197405115	MSR Gold 700/1 MiniFastFit 1CT/4	10.2 A	700 W
928199905115	MSR Gold 700/2 MiniFastFit 1CT/4	10.2 A	700 W

