



# MSR Gold™ MiniFastFit – lamp replacement in seconds

## MSR Gold™ MiniFastFit (Touring/Stage)

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

### Benefits

- Lamp replacement in just seconds
- Lamp replacement in just seconds
- Easy handling, smaller and lighter fixtures
- Easy handling, smaller and lighter fixtures
- Reduces early lamp or lamp holder failures. Excellent current transfer
- Reduces early lamp or lamp holder failures. Excellent current transfer
- High perceived brightness
- High perceived brightness
- High beam intensity
- High beam intensity

# MSR Gold™ MiniFastFit (Touring/Stage)

## Features

- Philips MiniFastFit
- Philips MiniFastFit
- Compact design
- Compact design
- Innovative gold plated pins
- Innovative gold plated pins
- High color temperature
- High color temperature
- Very short arc
- Very short arc

## Application

- Events
- Events
- Shows
- Shows
- Touring/Stage
- Touring/Stage

## Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

## Versions





MSR Gold™ 1000 MiniFastFit



XPPR XDMSR 0015

MSR Gold™ MiniFastFit (Touring/Stage)

Dimensional drawing



General Information	
Operating Position	UNIVERSAL
Controls and Dimming	
Dimmable	Yes

General Information

Order Code	Full Product Name	Cap-Base
928171405115	MSR Gold 1000 MiniFastFit 1CT/4	PGJX36

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
928171405115	MSR Gold 1000 MiniFastFit 1CT/4	6000 K	80	-	79,300 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
928171405115	MSR Gold 1000 MiniFastFit 1CT/4	11.4 A	1,000 W

Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR Gold 700/1 MiniFastFit 1CT/4	23.2 mm	3.8 mm	55 mm	57 mm	56 mm	112 mm	36.5 mm	36 mm	35.3 mm

Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR Gold 1000 MiniFastFit 1CT/4	26 mm	5.5 mm	55 mm	57 mm	56 mm	112 mm	36.5 mm	36 mm	35.3 mm

Order Code	Full Product Name	Cap-Base
928197405115	MSR Gold 700/1 MiniFastFit 1CT/4	PGJX28

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
928197405115	MSR Gold 700/1 MiniFastFit 1CT/4	5700 K	73	1	53,400 lm

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
928197405115	MSR Gold 700/1 MiniFastFit 1CT/4	10.2 A	700 W

## MSR Gold™ MiniFastFit (Touring/Stage)

