



Halogen non-reflector lamps – high-quality light and easy to use

Λαμπήρας προβολής

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

Οφέλη

- Optimal beam performance
- 100% Color Rendering Index (CRI)
- Constant light output throughout lifetime

Χαρακτηριστικά

- Distortion-free, quartz bulb and precisely defined filament position
- Lamp replacement without adjustment
- XHP version with xenon gas for maximum light output
- Flat filament available

Λαμπτήρας προβολής

Εφαρμογή


- Studio, film, theatre and disco lighting
- Slide, overhead, profile and 8/16 mm film projectors
- Microscopes
- Optical equipment
- Slide and film viewers
- Surgery lamps
- Microfilm readers
- Dental lamps
- Spectrography

Versions



XPPR_XHMPSEFF_0002-Product photo

Σχεδιάγραμμα διαστάσεων



Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
14623 95W	11,5 mm	31,5 mm	32,25	32	1,05 mm	1 mm	0,95	50 mm
G6.35 17V 1CT/ 10X10F			mm	mm			mm	
7158XHP 150W	11,5 mm	31,5 mm	33,25	33	1,05 mm	1 mm	0,95	50 mm
G6.35 24V 1CT/ 10X10F			mm	mm			mm	

Γενικές πληροφορίες	
Βάση-κάλυμμα	G6.35
Θέση λειτουργίας	S90
Μηχανικά εξαρτήματα και Περιβλημα	
Υλικό λαμπτήρα	Χαλαζίας, ανοιχτό στην υπεριώδη ακτινοβολία

Τεχνικά χαρακτηριστικά φωτισμού

Λαμπτήρας προβολής

Order Code	Full Product Name	Σχετική θερμοκρασία χρώματος (ονομ.)	Δείκτης χρωματικής απόδοσης (CRI)
41020750	7158XHP 150W G6.35 24V 1CT/10X10F	3450 K	100

Order Code	Full Product Name	Σχετική θερμοκρασία χρώματος (ονομ.)	Δείκτης χρωματικής απόδοσης (CRI)
42667350	14623 95W G6.35 17V 1CT/ 10X10F	-	-

Χαρακτηριστικά ηλεκτρικής λειτουργίας

Order Code	Full Product Name	Κατανάλωση ενέργειας
41020750	7158XHP 150W G6.35 24V 1CT/10X10F	150 W

Order Code	Full Product Name	Κατανάλωση ενέργειας
42667350	14623 95W G6.35 17V 1CT/10X10F	95 W

