



# Actinic BL PL-S/PL-L – compact for design freedom

## Actinic BL PL-S/PL-L

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

### Advantages

- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- Safe for use
- Good environmental choice
- Design freedom

### Fonctions

- Emits long-wave UV-A radiation in the 350-400nm range
- UV-B/UV-A ratio less than 0.1 % (UV-B 280-315nm)
- 100% lead-free
- Low mercury content
- Compact lamp format

### Application

- Insect traps, Electronic Fly Killers (EFKs)

# Actinic BL PL-S/PL-L

## Mises en garde et sécurité



- Un bris de lampe est très peu susceptible d'influer sur votre santé. Si une lampe se brise, aérez la pièce pendant 30 minutes et retirez les morceaux, de préférence avec des gants. Placez-les dans un sac en plastique scellé et portez-le à votre site de gestion des déchets en vue de son recyclage. Évitez d'utiliser un aspirateur.

## Versions



XPPR\_XURPLL\_0001-Product photo      XPPR\_XUAPLS 0001

## Schéma dimensionnel



| Product                              | D1 (max) | D (max) | A (max)  | B (max)  | C (max)  |
|--------------------------------------|----------|---------|----------|----------|----------|
| Actinic BL PL-S 9W/10/2P 1CT/6X10BOX | 13 mm    | 28 mm   | 128.8 mm | 144.5 mm | 167 mm   |
| PL-S 11W/10/2P 1CT/6X10BOX           | 13 mm    | 28 mm   | 198 mm   | 213.3 mm | 236.3 mm |

| Product               | D1 (max) | D (max) | A (max)  | B (max) | C (max)  |
|-----------------------|----------|---------|----------|---------|----------|
| PL-L 18W/10/4P 1CT/25 | 18 mm    | 39 mm   | 194.2 mm | 220 mm  | 226.6 mm |
| PL-L 24W/10/4P 1CT/25 | 18 mm    | 39 mm   | 289.2 mm | 315 mm  | 321.6 mm |

| Données techniques de l'éclairage |               |
|-----------------------------------|---------------|
| Désignation de la couleur         | Ultraviolet A |

## Informations générales

## Actinic BL PL-S/PL-L

| Order Code | Full Product Name     | Culot |
|------------|-----------------------|-------|
| 26018540   | PL-L 18W/10/4P 1CT/25 | 2G11  |
| 95206640   | PL-L 24W/10/4P 1CT/25 | 2G11  |

### Données techniques de l'éclairage

| Order Code | Full Product Name     | Code couleur |
|------------|-----------------------|--------------|
| 26018540   | PL-L 18W/10/4P 1CT/25 | 10           |
| 95206640   | PL-L 24W/10/4P 1CT/25 | 210          |

### Fonctionnement et électricité

| Order Code | Full Product Name                        | Courant lampe<br>(nom.) | Consommation<br>électrique |
|------------|------------------------------------------|-------------------------|----------------------------|
| 26018540   | PL-L 18W/10/4P 1CT/25                    | 0.375 A                 | 18 W                       |
| 95206640   | PL-L 24W/10/4P 1CT/25                    | 0.345 A                 | 24 W                       |
| 95194680   | Actinic BL PL-S 9W/10/2P 1CT/<br>6X10BOX | 0.17 A                  | 8.6 W                      |

### Mécanique et boîtier

| Order Code | Full Product Name     | Forme de la lampe |
|------------|-----------------------|-------------------|
| 26018540   | PL-L 18W/10/4P 1CT/25 | 2xT16             |
| 95206640   | PL-L 24W/10/4P 1CT/25 | 2xT16             |

### Approbation et application

| Order Code | Full Product Name                        | Taux de mercure<br>(Hg) (max.) | Taux de mercure<br>(Hg) (nom.) |
|------------|------------------------------------------|--------------------------------|--------------------------------|
| 26018540   | PL-L 18W/10/4P 1CT/25                    | -                              | -                              |
| 95206640   | PL-L 24W/10/4P 1CT/25                    | 4.4 mg                         | 4.2 mg                         |
| 95194680   | Actinic BL PL-S 9W/10/2P 1CT/<br>6X10BOX | -                              | -                              |

| Order Code | Full Product Name                    | Culot |
|------------|--------------------------------------|-------|
| 95194680   | Actinic BL PL-S 9W/10/2P 1CT/6X10BOX | G23   |
| 95201180   | PL-S 11W/10/2P 1CT/6X10BOX           | G23   |

| Order Code | Full Product Name                    | Code couleur |
|------------|--------------------------------------|--------------|
| 95194680   | Actinic BL PL-S 9W/10/2P 1CT/6X10BOX | 210          |
| 95201180   | PL-S 11W/10/2P 1CT/6X10BOX           | 210          |

| Order Code | Full Product Name          | Courant lampe<br>(nom.) | Consommation<br>électrique |
|------------|----------------------------|-------------------------|----------------------------|
| 95201180   | PL-S 11W/10/2P 1CT/6X10BOX | 0.16 A                  | 11.6 W                     |

| Order Code | Full Product Name                    | Forme de la lampe |
|------------|--------------------------------------|-------------------|
| 95194680   | Actinic BL PL-S 9W/10/2P 1CT/6X10BOX | 2XT12             |
| 95201180   | PL-S 11W/10/2P 1CT/6X10BOX           | 2XT12             |

| Order Code | Full Product Name          | Taux de mercure<br>(Hg) (max.) | Taux de mercure<br>(Hg) (nom.) |
|------------|----------------------------|--------------------------------|--------------------------------|
| 95201180   | PL-S 11W/10/2P 1CT/6X10BOX | -                              | -                              |

