



Actinic BL TL-D(K) Secura

Benefits

- ## Features

- data subject to change

Actinic BL TL-D(K) Secura


Application

- Insect traps, Electronic Fly Killers (EFKs)

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 15W/10 Secura 1SL/25	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm
Actinic BL TL-D 18W/10 Secura 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

General Information	
Cap-Base	G13
Light Technical	
Color Designation	Actinic
Color Code	10
Mechanical and Housing	
Bulb Shape	T26

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
89858640	Actinic BL TL-D 15W/10 Secura 1SL/25	0.335 A	15 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
85383400	Actinic BL TL-D 18W/10 Secura 1SL/25	0.36 A	18 W

Approval and Application

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
89858640	Actinic BL TL-D 15W/10 Secura 1SL/25	5

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
85383400	Actinic BL TL-D 18W/10 Secura 1SL/25	5.0 mg

Actinic BL TL-D(K) Secura

