Actinic BL TL-D(K) Secura – additional safety and HACCP approval

Actinic BL TL-D(K) Secura

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL-D(K) Secura lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

Vantaggi

- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- Safe for use
- Good environmental choice
- No risk of glass particles

Caratteristiche

- Basso contenuto di mercurio

Applicazione

- Insect traps, Electronic Fly Killers (EFKs)

Actinic BL TL-D(K) Secura

Warnings and safety

- È estremamente improbabile che la rottura di una lampada possa avere conseguenze sulla salute dei consumatori. Nel caso in cui una lampada si rompa, ventilare la stanza per 30 minuti e rimuovere i frammenti, preferibilmente indossando dei guanti. Riporre i frammenti in una busta di plastica sigillata e smaltirli presso i luoghi opportuni per il riciclo. Non utilizzare un aspirapolvere.

Versions

XPPR_XUBTLD_0002-Product photo

Disegno tecnico



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 15W/10 Secura 1SL/25	28 mm	437,4 mm	444,5 mm	442,1 mm	451,6 mm
Actinic BL TL-D 18W/10 Secura 1SL/25	28 mm	589,8 mm	596,9 mm	594,5 mm	604 mm

Informazioni generali	
Attacco	G13
Dati tecnici di illuminazione	
Designazione colore	Actinic
Codice colore	10
Meccanica e corpo	
Forma lampadina	T26

Funzionamento e parte elettrica

Order Code	Full Product Name	Corrente lampada (Nom)	Consumo energetico
89858640	Actinic BL TL-D 15W/10 Secura 1SL/25	0,335 A	15 W

Order Code	Full Product Name	Corrente lampada (Nom)	Consumo energetico
85383400	Actinic BL TL-D 18W/10 Secura 1SL/25	0,36 A	18 W

Approvazione e applicazione

Actinic BL TL-D(K) Secura

Order Code	Full Product Name	Contenuto di mercurio (Hg) (Nom)
89858640	Actinic BL TL-D 15W/10 Secura 1SL/25	5

Order Code	Full Product Name	Contenuto di mercurio (Hg) (Nom)
85383400	Actinic BL TL-D 18W/10 Secura 1SL/25	5,0 mg

© 2024 Signify Holding Tutti i diritti riservati. Signify non fornisce alcuna rappresentazione o garanzia relativamente all'accuratezza o alla completezza delle informazioni incluse e non può essere ritenuta responsabile di eventuali azioni basate su di esse. Le informazioni riportate nel presente documento non hanno alcuno scopo commerciale e non fanno parte di alcun preventivo o contratto, salvo diversamente concordato con Signify. Tutti gli altri marchi sono di proprietà di Signify Holding o dei rispettivi proprietari.