




Actinic BL TL-D(K) Secura



Versions



XPPR XUATLDK 0001

XPPR_XUBTLD_0002-Product photo

Måttskiss



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-DK Secura 36W/10 1SL/25	28 mm	589,8 mm	596,9 mm	594,5 mm	604 mm

Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 15W/10 Secura 1SL/25	28 mm	437,4 mm	444,5 mm	442,1 mm	451,6 mm
Actinic BL TL-D 18W/10 Secura 1SL/25	28 mm	589,8 mm	596,9 mm	594,5 mm	604 mm

Allmän information	
Sockel	G13
Ljusteknik	
Färgbeteckning	Actinic
Färgkod	10
Mekanik och armaturhus	
Lampform	T26

Drift och elektricitet

Actinic BL TL-D(K) Secura

Order Code	Full Product Name	Lampström (nom)	Effektförbrukning
928019801003	Actinic BL TL-DK Secura 36W/10 1SL/25	0,865 A	36 W
928024701029	Actinic BL TL-D 15W/10 Secura 1SL/25	0,335 A	15 W

Order Code	Full Product Name	Lampström (nom)	Effektförbrukning
928048201003	Actinic BL TL-D 18W/10 Secura 1SL/25	0,36 A	18 W

Användning och godkännande

Order Code	Full Product Name	Kviksilverinnehåll (Hg) (nom)
928019801003	Actinic BL TL-DK Secura 36W/10 1SL/25	8,0 mg
928024701029	Actinic BL TL-D 15W/10 Secura 1SL/25	5

Order Code	Full Product Name	Kviksilverinnehåll (Hg) (nom)
928048201003	Actinic BL TL-D 18W/10 Secura 1SL/25	5,0 mg

