



MASTER Actinic BL TL-D Secura – the most effective way to eliminate insects, and HACCP-approved

MASTER Actinic BL TL-D Secura

The Philips MASTER Actinic BL TL-D Secura family combines multiple benefits in one lamp. These lamps have the perfect spectrum for attracting insects. Also, they have virtually no UV-B output, and so are perfectly safe. Furthermore, they have the special "MASTER" coating to improve the efficiency, initial UV-A output and maintenance of the lamp. And finally, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, combined with their high efficiency, these lamps represent the best choice for the environment.

Benefits

- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- Safe for use
- Good environmental choice
- High UV-A output during entire season
- No risk of glass particles

MASTER Actinic BL TL-D Secura

Features

- Emits long-wave UV-A radiation in the 350–400nm range
- UV-B/UV-A ratio less than 0.1 % (UV-B 280–315nm)
- 100% lead-free
- Low mercury content
- Special maintenance coating
- Shatterproof sleeve


Application

- Insect traps, Electronic Fly Killers (EFKs)

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER Actinic BL TL-D 15W/10 Secura	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm
MASTER Actinic BL TL-D 18W/10 Secura	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm



MASTER Actinic BL TL-D Secura

General Information	
Cap-Base	G13
Light Technical	
Color Designation	Actinic
Color Code	10
Mechanical and Housing	
Bulb Shape	T26
Approval and Application	
Mercury (Hg) Content (Nom)	3.0 mg

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
928022701003	MASTER Actinic BL TL-D 15W/10 Secura	0.335 A	15.5 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
928044801003	MASTER Actinic BL TL-D 18W/10 Secura	0.36 A	18 W

