



Philips Eletrocutores para insetos BL

Eletrocutores para insetos BL

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Benefícios

- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- Safe for use
- Good environmental choice
- Design freedom

Características

- Emits long-wave UV-A radiation in the 350–400nm range
- UV-B/UV-A ratio less than 0.1 % (UV-B 280–315nm)
- 100% lead-free
- Low mercury content
- Vasta gama de potências

Aplicação

- Insect traps, Electronic Fly Killers (EFKs)

Avisos e Segurança

- É extremamente improvável que a quebra de uma lâmpada tenha qualquer impacto na sua saúde. Se uma lâmpada quebrar, ventile a divisão durante 30 minutos e remova as partes da lâmpada, de preferência com luvas. Coloque-as num saco de plástico fechado e leve-o para o ecocentro mais próximo para reciclagem. Não utilize o aspirador.

Eletrocutores para insetos BL

Versions



XPPR_XUVATLRS_10_10-R_G13-
Product photo






XPPR XUBTL 10 G5



Actinic BL TL-D 15W/10 1SL/25

Desenho dimensional





Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-DK 36W/10 1SL/25	28 mm	589,8 mm	596,9 mm	594,5 mm	604 mm

Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL MINI 15W/10 / 10X25CC	16 mm	288,3 mm	295,4 mm	293,0 mm	302,5 mm

Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 15W/10 1SL/25	28 mm	437,4 mm	444,5 mm	442,1 mm	451,6 mm
Actinic BL TL-D 18W/10 1SL/25	28 mm	589,8 mm	596,9 mm	594,5 mm	604 mm

Eletrocutores para insetos BL

Desenho dimensional



Caraterísticas técnicas da luz	
Designação da cor	Actinic
Código da cor	10

Informações gerais

Order Code	Full Product Name	Casquilho
26026000	Actinic BL TL 40W/10 1SL/25	G13
95148927	ACTINIC BL 15W/10 FAM/10X25BOX	G5
26039027	Actinic BL TL 6W/10 1FM/10X25CC	G5
95145827	Actinic BL TL 11W/10	G5

Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL 11W/10	16 mm	212,1 mm	219,2 mm	216,8 mm	226,3 mm
Actinic BL TL 6W/10 1FM/10X25CC	16 mm	212,1 mm	219,2 mm	216,8 mm	226,3 mm
Actinic BL TL 8W/10 1FM/10X25CC	16 mm	288,3 mm	295,4 mm	293 mm	302,5 mm

Product	D (max)	A (max)	B	C (max)
Actinic BL TL 40W/10 SLV/25	37,25 mm	1.198,4 mm	1.205,4 mm	1.212,4 mm

Funcionamento e caraterísticas elétricas

Order Code	Full Product Name	Corrente de lâmpada (Nom.)	Consumo de Energia
26026000	Actinic BL TL 40W/10 1SL/25	0,43 A	39 W
95148927	ACTINIC BL 15W/10 FAM/10X25BOX	0,40 A	15 W
26039027	Actinic BL TL 6W/10 1FM/10X25CC	0,16 A	6 W
95145827	Actinic BL TL 11W/10	0,400 A	11,5 W

Order Code	Full Product Name	Corrente de lâmpada (Nom.)	Consumo de Energia
26042027	Actinic BL TL 8W/10 1FM/10X25CC	0,145 A	7,1 W
86083200	Actinic BL TL-DK 36W/10 1SL/25	0,865 A	36 W
71093240	Actinic BL TL-D 15W/10 1SL/25	0,34 A	15 W
26325440	Actinic BL TL-D 18W/10 1SL/25	0,36 A	18 W

Características mecânicas e compartimento

Order Code	Full Product Name	Formato da lâmpada
26026000	Actinic BL TL 40W/10 1SL/25	T12
95148927	ACTINIC BL 15W/10 FAM/10X25BOX	T16

Order Code	Full Product Name	Formato da lâmpada
26039027	Actinic BL TL 6W/10 1FM/10X25CC	T16
95145827	Actinic BL TL 11W/10	T16

Eletrôcutores para insetos BL

Order Code	Full Product Name	Formato da lâmpada
26042027	Actinic BL TL 8W/10 1FM/10X25CC	T16
86083200	Actinic BL TL-DK 36W/10 1SL/25	T26

Order Code	Full Product Name	Formato da lâmpada
71093240	Actinic BL TL-D 15W/10 1SL/25	T26
26325440	Actinic BL TL-D 18W/10 1SL/25	T26

Aprovação e aplicação

Order Code	Full Product Name	Conteúdo de mercúrio (Hg) (Nom.)
26026000	Actinic BL TL 40W/10 1SL/25	13,0 mg
95148927	ACTINIC BL 15W/10 FAM/10X25BOX	-
26039027	Actinic BL TL 6W/10 1FM/10X25CC	4,4 mg
95145827	Actinic BL TL 11W/10	4,4 mg

Order Code	Full Product Name	Conteúdo de mercúrio (Hg) (Nom.)
26042027	Actinic BL TL 8W/10 1FM/10X25CC	4,4 mg
86083200	Actinic BL TL-DK 36W/10 1SL/25	8,0 mg
71093240	Actinic BL TL-D 15W/10 1SL/25	5,0 mg
26325440	Actinic BL TL-D 18W/10 1SL/25	5,0 mg

