
PHILIPS

Ledinaire Wall-mounted

WL060V

Scan me!
DOWNLOAD





Pipe 3x
Screw M4x30 3x
Seal plug 2x
Metal gasket 3x


indoor | 220V 240V | 50Hz 60Hz | Ta 25 °C | Max. 40 °C Min. -20 °C | IP44 | IK03 | <10 90%

	Light source of energy efficiency class	P(W)	Driver	Sensor	kg
WL060V gen2 11S/830 PSU WH IP44 D300	E	11	PSU	No	0.53
WL060V gen2 11S/840 PSU WH IP44 D300		11		No	0.53

Dimensions in mm









Inrush current


	LED11S
	Electrical characteristics
Imax (A)	22
Tref (µs)	320
MCB	Luminaires Max.
B-10 A	11
B-13 A	15
B-16 A	18
C-10 A	19
C-13 A	24
C-16 A	31





© 04/2026 Signify Holding. All rights reserved


Data subject to change without notice
Keep for future reference: *www.philips.com/lighting*











©04/2026 Signify Holding.
All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. The information presented in this document is not intended as any commercial ofer and does not form part of any quotation or contract. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.. All other trademarks are owned by Signify Holding or their respective owners.

Signify Holding.
The Netherlands