


	Lumen (lm)	CCT (K)	P (W)	IK	Energy efficiency class of light source	LxWxH (mm)	kg	Safety cable (SC) in the box
RC065B G5 34S/840 PSU W60L60 OC SC	3400	4000	28.0	02	D	595x595x35	1.65	Yes
RC065B G5 34S/840 PSU W60L60 NOC SC	3400	4000	28.0	02	D	595x595x34	1.35	Yes
RC065B G5 34S/840 PSD W60L60 OC SC	3400	4000	28.0	02	D	595x595x35	1.65	Yes
RC066B 34S/840 PSU W62L62 OC	3400	4000	28.0	02	D	620x620x35	1.75	No
RC066B 34S/840 PSD W62L62 OC	3400	4000	28.0	02	D	620x620x35	1.75	No
RC065B G5 34S/840 PSU W60L60 OC 6PK SC	3400	4000	28.0	02	D	595x595x35	1.65	Yes
RC066B 34_36S/830_40 PSU W62L62 OC	3400/ <b>3600</b>	3000/3500/ <b>4000</b>	30.0	02	D	620x620x35	1.75	No
RC065B G5 34_36S/830_40 PSU W60L60 OC SC	3400/ <b>3600</b>	3000/3500/ <b>4000</b>	30.0	02	D	595x595x35	1.65	Yes
RC065B G5 34_36S/830_40 PSU 60x60 NOC SC	3400/ <b>3600</b>	3000/3500/ <b>4000</b>	30.0	02	D	595x595x34	1.35	Yes
RC065B G5 34_36S/830_40 PSD W60L60 OC SC	3400/ <b>3600</b>	3000/3500/ <b>4000</b>	28.0	02	D	595x595x35	1.65	Yes
RC065B G5 34_36S/830_40 PSU 30x120 OC SC	3400/ <b>3600</b>	3000/3500/ <b>4000</b>	30.0	02	D	295x1195x35	1.75	Yes
RC065B G5 34_36S/830_40 PSD 60x60 NOC SC	3400/ <b>3600</b>	3000/3500/ <b>4000</b>	28.0	02	D	595x595x35	1.35	Yes


\* Default setting : 3000/3500K/**4000K** \* Product power included driver




Available as accessory(Need to purchase separately)

<p>Suspension set: 911401809487: RC159Z Suspension set SME-3 WH 911401809387: RC159Z Suspension set SME-4 WH</p>	<p>Plaster set: 911401809287: RC159Z Plaster Ceiling SMB-PLC</p>	<p>Safety cable: 911401809187: RC159Z Safety Cable</p>
--	--	--

Surface mounted set:  
 911401808087:RC059Z SMB W60L60  
 911401808187:RC059Z SMB W62L62  
 911401808287:RC059Z SMB W30L120



Surface mounted set:  
 911401807787:RC159Z SMB W60L60  
 911401807887:RC159Z SMB W62L62  
 911401807987:RC159Z SMB W30L120




The luminaire shall not be covered with thermal insulation or similar material under any circumstance.

If the external flexible cable or cord of this luminaire is damaged, it shall be exclusively replaced by the manufacturer or his service agent or a similar qualified person in order to avoid a hazard.





The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.

Luminaire must not be used or stored in corrosive environment where hazardous materials such as sulphur, chlorine, phthalates, etc. are present.

**Inrush current**




	28W PSU	28W PSD	30W PSD
Electrical characteristics			
I <sub>max</sub> (A)	18.7	25.8	22
T <sub>ref</sub> (µs)	218	255	250
MCB Luminaire's Max.			
B-10 A	13	9	6
B-13 A	18	13	8
B-16 A	23	17	10
C-10 A	24	17	10
C-13 A	32	23	13
C-16 A	39	28	17




**All-in: Multi Color switch set your color temperature 3000K, 3500K or 4000K (=default)**

Colour Temperature selectable			
Drive	3000K	3500K/4000K	Wattage
PSU	3400lm	3600lm	30W
PSD	3400lm	3600lm	28W





**A Visible Profile Ceiling mounting (VPC) - Lay-In mounting**



**B Suspension mounting (SME-3 WH/SME-4WH)**

**PSU**  
 911401809487 RC159Z Suspension set SME-3 WH



**PSD**  
 911401809387 RC159Z Suspension set SME-4 WH

