





SM060C $\frac{1}{3}$




Push-in connectors



1




2




Screw

3




8-10 mm 15-20 mm
Blue (N) Brown (L)

4




Uses click fix
0.75-1.5 mm²
Ø 6-9 mm



Needs screw fix
1-1.5 mm²
Ø 6-9 mm


5




Double
sided sticker

6

MultiLumen selection on driver



WARNING



DIP Switch

Low High
Lumen selectable


PSU	4.000 K	
PIN	Lumen	Power
Low	3.400 lm*	28 W*
High	4.000 lm	33 W

* Default setting




Surface mounted

Step 1 (4x)



Step 2 (4x)




Max.
Ø5 mm

included





included

1


2



3



CLICK



4