

Back-lit panel

RC007B

220V
240V

50Hz
60Hz

IP20

Life
35K hrs
@L70

Max.
35°C
Min.
-10°C

GLOW
WIRE
650 °C

	Lumen (lm)	CCT (K)	P(W)	Energy efficiency class of light source	L xW xH (mm)	
MAZDA G2 RC007B 32S/840 PSU W60L60 NOC	3200	4000	32.0	E	595x595x34	1.26
MAZDA G2 RC007B 32S/840 PSU 6060 NOC CL	3200	4000	32.0	E	595x595x34	1.26
MAZDA G2 RC007B 32S/840 PSU W60L60 OC	3200	4000	32.0	E	595x595x35	1.52
MAZDA G2 RC007B 32S/840 PSU 6060 OC CL	3200	4000	32.0	E	595x595x35	1.52

Available as accessory

Suspension set:
911401809587 :
RC159Z SME-2 WH

Surface mounted set:
911401808087 :
RC059Z SMB W60L60

Plaster set:
911401809287 :
RC159Z SMB-PLC

Safety cable:
911401809187 : RC159Z SC

VPC visible profile ceiling

Wiring Method

Unit : mm

Please use IP20 or higher terminal box
It is not included in package.

The luminaire shall, under no circumstance, be covered with thermal insulation matting or similar material.

If the external flexible cable or cord of this luminaire is damaged, it shall be exclusively replaced by the manufacturer or his service agent or a similar qualified person in order to avoid a hazard.

The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.

Luminaire must not be used or stored in corrosive environment where hazardous materials such as sulphur, chlorine, phthalates, etc. are present.

32W
Electrical characteristics
Imax (A) 40
Tref (µs) 4.5
MCB Luminaires Max
B-10 A 14
B-13 A 15
B-16 A 16
C-10 A 14
C-13 A 18
C-16 A 21

Visible Profile Ceiling mounting(VPC)

Install safety cable (Optional)

Suspension mounting(SME-2)

Unit : mm

Plaster CeilingVersion mounting(SME-PLC)

Install safety cable (Optional)

Safety cable(SC)

Surface mounted

911401808087:RC059Z SMB W60L60

Unit : mm