
























				Energy efficiency			
	Lumen (lm)	CCT (K)	P(W)	class of light source	LxWxH(mm)	H1(mm)	kg
Projectline Panel 3030 1200lm 4000K NOC	1200	4000	15	E	295 x 295 x 34	64	0.55






The luminaire shall, under no circumstance, be covered with thermal insulation matting or similar material.



If the external flexible cable or cord of this luminaire is damaged, it shall be exclusively replaced by the manufacturer or his service agent or a similar qualified person in order to avoid a hazard.


The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.

Luminaire must not be used or stored in corrosive environment where hazardous materials such as sulphur, chlorine, phthalates, etc, are present.



	Electrical characteristics
Imax (A)	10
Tref (µs)	150
MCB	Luminaires Max.
B-10 A	31
B-13 A	41
B-16 A	50
C-10 A	52
C-13 A	69
C-16 A	85





Please use IP20 or above terminal box (dimension can't smaller than $10 \times 20 \times 25$). It is not included in package.

