

PHILIPS

Pomeron Recessed
Light


Recessed Lights

4000K

White



59775/31/H3



Essential lighting for a bright home

Manipulate the direction of your light in different ways with Philips Pomeron LED spotlight's adjustable head in 2 axis rotation. With a stylish white design that enhances your décor, bask in strong, focused beam with an accented feel.

Easy to Experience

- Adjustable light angle

Energy saving

- Built-in Philips conventional ballast

Highlights

Adjustable light angle

Energy efficient, long lasting

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Metal, Plastic

Durability

- Number of switch cycles: 7,500
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Adjustable – rise and fall
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 30 degree(s)
- Color consistency: 5 SDCM
- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Luminous Efficacy (rated) (Nom): 60 lm/W

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes

Other characteristics

- Lamp current: 44 mA

Product dimensions and weight

- Net weight: 0.121 kg
- Recessed distance: 35 mm
- Overall height: 62 mm
- Overall length: 90 mm
- Overall width: 90 mm

Service

- Warranty: 1 year(s)

Technical specifications

- Diameter: 107.4 mm
- Total lumen output fixture: 300
- Light color: 4000
- Mains power: AC 220–240
- Fixture dimmable: No
- Wattage bulb included: 5
- Maximum wattage replacement bulb: 5
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated
- Number of light sources: 1

Packaging dimensions and weight

- EAN/UPC – product: 6947830434558
- Net weight: 0.1 kg
- Gross weight: 0.14 kg
- Height: 7.8 cm
- Length: 9.4 cm
- Width: 9.4 cm



Issue date: 2025-08-30
Version: 0.306

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com