

PHILIPS

Recessed Light

Recessed Lights

4000K

Dark grey



6922341958403



Superior light and style

Deep recessed for visual comfort

Match your interior

- Expressive and elegant form

Light effect

- Multiple layered visual effectDynamic tiered design

Premium quality

- EyeComfort - light that's easy on the eyes

Durability

- Long life span up to 25,000 hours

Highlights

Expressive and elegant form

A clean, modern design provides elegance and sophistication to your rooms.

Multiple layered visual effectDynamic tiered design

This dynamic tiered design makes for a striking impression that adds a creative touch to your rooms.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips s LED bulbs not only deliver

comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Long life span up to 25,000 hours

Philips LED technology extends your product's lifetime up to 25,000 hours

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

Design and finishing

- Color: Dark Grey
- Material: Metal
- Housing Color: Dark gray
- Housing Material: Aluminum die cast
- Optical cover finish: Clear
- Optical cover material: Polycarbonate

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 15,000
- Ambient temperature range: -20 to +40 °C
- Nominal lifetime: 25,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Adjustable - rise and fall
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Guarantee

- Warranty period: 1 years

Light characteristics

- Beam angle: 36 degree(s)
- Color consistency: 5 SDCM
- Color rendering index (CRI): 90
- Color temperature: 4000 K
- Warm-up time to 60% light: 2
- Luminous flux tolerance: +/-10%
- Constant light output: No
- Correlated Color Temperature (Nom): 4000 K
- Initial chromaticity: (0.3779, 0.3683) <5SDCM
- Light source replaceable: No
- Luminaire light beam spread: 36°
- Luminous Flux: 2,150 lm
- Optic material: Polycarbonate
- Optic type: High-gloss mirror
- Reflector material: Polycarbonate
- Luminous Efficacy (rated) (Nom): 93 lm/W

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Office, Hall
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- Lamp current: 107 mA
- EU RoHS compliant: Yes

Power

- Input Voltage: 220 to 240
- Inrush current: 16 A
- Inrush time: 0.18 ms
- Power Factor (Fraction): 0.9

Power consumption

- Power factor: 0.9
- Power Consumption: 23
- Power consumption tolerance: +/-10%

Product dimensions and weight

- Net weight: 0.515 kg
- Recessed distance: 60 mm
- Overall diameter: 110 mm
- Overall height: 110 mm
- Overall length: 110 mm
- Overall width: 110 mm
- Recessed Ceiling cutout: 9.8 cm x 9.8 cm

Service

- Warranty: 3 year(s)

Technical specifications

- Diameter: 110 mm
- Total lumen output fixture: 2150
- Light color: 4000
- Mains power: AC 220-240
- Fixture dimmable: No
- Wattage bulb included: 23
- IP code: IP20 | Finger-protected
- Class of protection: Class II - Double Insulated
- Cable: Cable 0.1m without plug
- Connection: Flying leads/wires
- Dimmable: No
- Driver/power unit/transformer: Power supply unit
- Driver included: Yes
- Fixation material: Aluminum
- Flammability mark: For mounting on normally flammable surfaces
- Glow-wire test: Temperature 650 °C, duration 30 s
- Ingress protection code: IP20 | Finger-protected
- Line Frequency: 50 or 60
- Mech. impact protection code: IK03 | 0.3 J
- Number of gear units: 1 unit
- Number of products on MCB of 16 A type B: 36
- Suitable for random switching: Not applicable
- Number of light sources: 1
- Protection class IEC: Safety class II

Packaging dimensions and weight

- EAN/UPC - product: 6922341958403
- Net weight: 0.52 kg
- Gross weight: 0.57 kg
- Height: 12.2 cm
- Length: 11.6 cm
- Width: 11.4 cm



Issue date: 2025-09-03
Version: 0.143

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com