

PHILIPS

Halogen reflector
bulb

75 W

E27 cap

Clear

8711500887016



Superior halogen lighting

Provides bright, sparkling light with superior dimmability. Perfect for creating focused light effects indoors.

Personal scene setting

- Best dimmability to dims and create a cosy atmosphere

Beacon of trust

- You can trust what the Philips packaging is saying

Create a cosy atmosphere

- Bright halogen light provides better contrast for more focus
- Bright, sparkling lighting to create your light scene at home

Highlights

Best dimmability

This lamp can be used in combination with all dimmers and will not only turn down the light to 0% but also create a cosy atmosphere as you are used to with your incandescent.

Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalent to incandescent lamps.

Halogen contrast for focus

With bright halogen light, contrasts get richer, letters become sharper and visibility gets better. Bright light is more relaxing for your eyes for a better focus.

Bright, sparkling light

Clear halogen is a sparkling light, giving beautiful reflections where it shines, and sharp shadows where it doesn't. Philips halogen lamps give decorative light effect to your room, to bring your room to life.

Specifications

Bulb characteristics

- Shape: Reflector
- Socket: E27
- Dimmable: Yes

Bulb dimensions

- Height: 99 mm
- Width: 97 mm

Durability

- Average life (at 2.7 hrs/day): 2 year(s)
- Number of switch cycles: 8,000
- Nominal lifetime: 2,000

Light characteristics

- Application: Accent light
- Beam angle: 25 degree(s)
- Color rendering index (CRI): 100
- Color temperature: 2800 K
- Light Color Category: Clear
- Warm-up time to 60% light: instant full light s
- Correlated Color Temperature (Nom): 2800 K

Power

- Power Factor (Fraction): 1

Power consumption

- Voltage: 230 V
- Power Consumption: 75.0
- Energy Consumption kWh/1000 h: 75

Rated values

- Rated lifetime: 2,000

Technical specifications

- Dimmable: Yes
- Cap-Base: E27



Issue date: 2025-08-30
Version: 0.634

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com