



## Bulb 9W (Eq.60W) A60 E27

The WiZ LED A60 full color bulb brings smart lighting for your daily living. Retrofit into any lamp shade to create the ambience of your choice with 16 million colors as well as warm to cool white light. You can set schedule to turn lights on and off according to daily or weekly routines, control with your smartphone or your voice and have remote access to your lights even when you're away. WiZ lights connect to your existing Wi-Fi, no additional hardware is needed.

## PRODUCT HIGHLIGHTS

- Full color
- Plastic
- Easy plug and play
- Control with WiZ app or voice



**Easy plug and play. Works with your existing Wi-Fi.**

WIZ works with your existing Wi-Fi router, no additional gateway is needed. Simply plug in your new light, download the WIZ app and you're ready to go!

**Automate your light with schedules**

Automate the lights to fit your daily or weekly routines. Schedule your light to turn on before you arrive home and keep it off when not needed.

**Control anywhere with your smartphone.**

Control your WIZ lights wherever you are with smartphone. No need to worry if you've left your lights on before leaving home. WIZ app is available for iOS and Android.

**Millions of colors and dynamic light modes**

Choose from a palette of millions of light colors to create an amazing atmosphere in your home. Enjoy the subtle differences that our dynamic light effects glow your environment

**Tunable warm to cool white and preset modes**

Choose from a wide range of energizing cool white to soft warm white, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

**Customize Scenes with preset dynamic light modes.**

Mix different color and white lights modes to create the perfect light ambience for your daily moment. Save it and call it out anytime with app, WIZmote or voice.



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Indoor  
Lamp shape: A60  
Socket: E27  
Technology: Smart Wi-Fi  
Type of glass: Frosted  
Dimmable: Wireless Dim

## BULB DIMENSIONS

Height: 12.2 cm  
Weight: 0.06 kg  
Width: 6 cm

## DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)  
Lumen maintenance factor: 70%  
Number of switch cycles: 50,000  
Nominal lifetime: 15,000 hour(s)

## LIGHT CHARACTERISTICS

Color consistency: 6 SDCM  
Color rendering index (CRI): 90  
Color temperature: 2200-6500 K  
Light Color Category: Color & Tunable White  
Nominal luminous flux: 806 lm  
Starting time: <0.5 s  
Warm-up time to 60% light: instant full light

## OTHER CHARACTERISTICS

Lamp current: 75 mA  
Efficacy: 89 lm/W

## PACKAGING INFORMATION

EAN: 8718699782252  
EOC: 871869978225200  
Product title: Wi-Fi Color  
+TunableWhite/9W A60 12/1CT

## POWER CONSUMPTION

Power factor: 0.55  
Voltage: 220-240 V  
Wattage: 9 W  
Wattage equivalent: 60 W

## PRODUCT DIMENSIONS AND WEIGHT

Length: 12.2 cm

## RATED VALUES

Rated lifetime: 15,000 hour(s)  
Rated luminous flux: 806 lm  
Rated power: 9 W

## SERVICE

Warranty: 2 year(s)

## TECHNICAL SPECIFICATIONS

Frequency: 50-60 Hz



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.