



## **Bulb 9W (Eq.60W) A60 E27 x2 + Remote**

Bring human-centric lighting into your life with this smart WiZ LED A60 tunable white bulb. Apply different shades of warm to cool white to help you focus or relax. You can set schedule to turn lights on and off according to your daily or weekly routines, control with your smartphone or your voice and have remote access to your lights even when you're away. WiZ lights connect to your existing Wi-Fi, no additional hardware is needed.

## **PRODUCT HIGHLIGHTS**

- Tunable white
- Plastic
- Easy plug and play
- WiZmote included



**Easy plug and play. Works with your existing Wi-Fi.**

WIZ works with your existing Wi-Fi router, no additional gateway is needed. Simply plug in your new light, download the WIZ app and you're ready to go!

**Automate your light with schedules**

Automate the lights to fit your daily or weekly routines. Schedule your light to turn on before you arrive home and keep it off when not needed.

**Control anywhere with your smartphone.**

Control your WIZ lights wherever you are with smartphone. No need to worry if you've left your lights on before leaving home. WIZ app is available for iOS and Android.

**Energy monitoring**

The WIZ app keeps records of the energy consumption of your lights. View your weekly or daily report and plan your lighting wisely for an optimized energy consumption at home.

**Tunable warm to cool white and preset modes**

Choose from a wide range of energizing cool white to soft warm white, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

**Customize Scenes with preset dynamic light modes.**

Mix different color and white lights modes to create the perfect light ambience for your daily moment. Save it and call it out anytime with app, WIZmote or voice.



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Indoor  
Lamp shape: A60  
Socket: E27  
Type of glass: Frosted  
Dimmable: Yes

## BULB DIMENSIONS

Weight: 0.155 kg

## DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)  
Lumen maintenance factor: 70%  
Number of switch cycles: 50,000  
Nominal lifetime: 15,000

## LIGHT CHARACTERISTICS

Color consistency: 6 SDCM  
Color rendering index (CRI):  $\geq 90$   
Color temperature: 2700-6500 K  
Light Color Category: Tunable white  
Nominal luminous flux: 806 lm  
Starting time:  $< 0.5$  s  
Warm-up time to 60% light: instant full light  
Luminous Efficacy (rated) (Nom): 89 lm/W

## OTHER CHARACTERISTICS

Lamp current: 75 mA

## PACKAGING INFORMATION

EAN: 8719514261143  
EOC: 871951426114300  
Product title: Wi-Fi TW/9W A60 2PK + Remote 6/2CT

## POWER CONSUMPTION

Power factor: 0.55  
Voltage: 220-240 V  
Wattage equivalent: 60 W  
Power Consumption: 9 W  
Energy Consumption kWh/1000 h: 9

## PRODUCT DIMENSIONS AND WEIGHT

Overall height: 122 mm  
Overall length: 122 mm  
Overall width: 60 mm

## RATED VALUES

Rated lifetime: 15,000  
Rated luminous flux: 806 lm  
Rated power: 9 W

## SERVICE

Warranty: 2 year(s)

## TECHNICAL SPECIFICATIONS

Frequency: 50-60

## WHAT'S SUPPORTED

Compatible with Effects: Yes  
WiFi: Wireless G  
Defined support period: Minimum of 60 months after introduction date  
Max. number of accessories: 9999  
Communication protocol: Bluetooth WiFi (2.4GHz)



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.