



High quality LED light designed to last for years

Light up your space with Philips EyeComfort LED Downlight that provides a comfortable light source and ease to your eyes.

Easy to experience

• Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

Light effect

· Uniform light distribution

Durability

· Long life span up to 15,000 hours

Highlights

Suitable for low ceilingsSlim design Uniform light distribution

Throw light across your rooms in an even and uniform manner.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Bulb characteristics

Intended use: IndoorLamp shape: Round

Design and finishing

Color: WhiteMaterial: Plastic

Durability

Average life (at 2.7 hrs/day): 15 year(s)

Lumen maintenance factor: 70%

• Number of switch cycles: 7,500

· Nominal lifetime: 15,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- · Adjustable spot head: Not adjustable
- · Dimmable with remote control: No
- · LED integrated: Yes
- · Remote control included: No

Light characteristics

- Beam angle: 100 degree(s)
- Color consistency: 6 SDCM
- · Color rendering index (CRI): 80
- · Color temperature: 4000 K
- Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 85 lm/W

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Office
- Style: Contemporary
- · Type: Recessed Lights
- EyeComfort: Yes

Other characteristics

· Lamp current: 95 mA

Power consumption

• Power factor: 0.5

Product dimensions and weight

- Net weight: 0.09 kg
- · Recessed distance: 117 mm
- · Overall height: 35 mm
- · Overall length: 165 mm
- · Overall width: 165 mm
- Recessed Ceiling cutout: 15.0 cm x
 15.0 cm

Service

Warranty: 1 year(s)

Technical specifications

- Diameter: 165 mm
- · Total lumen output fixture: 1200
- Light color: 4000
- · Mains power: AC 220-240
- · Fixture dimmable: No
- · Wattage bulb included: 14
- IP code: IP20 | Finger-protected
- Class of protection: Class II Double Insulated

Packaging dimensions and weight

• EAN/UPC - product: 8719514303416

Net weight: 0.09 kgGross weight: 0.13 kg

Height: 16.6 cmLength: 4.2 cmWidth: 16.6 cm



© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips