

# PHILIPS

Robot Plus Desk  
Light

Desk Lights

4000K

White

Dimmable



8719514396838



## With EyeComfort, for light that's easy on your eyes

Designed with advanced optical technologies and honeycomb lenses, this desk light provides an enhanced visibility and reduces harmful glares

### **Premium quality**

- EyeComfort - light that's easy on the eyes

### **Control**

- Step dimming

# Highlights

## **Eyecomfort**

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color

rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality,

output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

## **Step dimming**

Select from different dimming levels to create the right mood for the moment.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

## Design and finishing

- Color: White
- Material: Metal, Plastic

## Durability

- Number of switch cycles: 15,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Bedroom, Living Room, Home Office
- Style: Contemporary
- Type: Desk Lights
- EyeComfort: Yes
- Extra Features: Dimmable

## Other characteristics

- Lamp current: 180 mA
- Efficacy: 57 lm/W

## Product dimensions and weight

- Net weight: 1.8 kg
- Height: 42 cm
- Length: 16 cm
- Width: 36.7 cm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Total lumen output fixture: 800
- Light color: 4000
- Mains power: 100–240
- Wattage bulb included: 14
- IP code: IP20
- Class of protection: Class II

## Packaging dimensions and weight

- EAN/UPC - product: 8719514396838
- Net weight: 1.8 kg
- Gross weight: 2.55 kg
- Height: 45.5 cm
- Length: 21.5 cm
- Width: 21.5 cm



Issue date: 2025-05-12  
Version: 0.301

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)