



6 inch recessed downlight 17W

Bring human-centric lighting into your life with this smart WiZ LED tunable white downlight. Fit into your ceiling and apply different shades of warm to cool white to help you focus or relax. You can set schedule to turn lights on and off according to your daily or weekly routines, control with your smartphone or your voice and have remote access to your lights even when you're away. WiZ lights connect to your existing Wi-Fi, no additional hardware is needed.

PRODUCT HIGHLIGHTS

- Tunable white
- Cut out Ø146-155MM
- IP20/Round/White



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!




Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Create your perfect light scene

Make your own mix of different color and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



Dim your smart lights even without a dimmer

Simply adjust lights to your desired brightness level using your smartphone, the WiZ control accessory or just your voice. No need to install an expensive dimmer!



SPECIFICATIONS

DESIGN AND FINISHING

Color: White

Material: Stainless Steel

EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: No

Dimmable with remote control: Yes

LED integrated: Yes

Remote control included: No

LIGHT CHARACTERISTICS

Beam angle: 90 degree(s)

Color rendering index (CRI): 80

MISCELLANEOUS

Especially designed for: Functional

POWER CONSUMPTION

Voltage: 220-240 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.163 kg

Cut out length: 15 cm

Cut out width: 15 cm

Height: 4.7 cm

Length: 16.5 cm

Recessed distance: 10.1 cm

Width: 16.5 cm

SERVICE

Warranty: 1 year(s)

TECHNICAL SPECIFICATIONS

Lifetime up to: 15,000 hour(s)

Diameter: 165 mm

Total lumen output fixture: 1200

Light color: 2700-6500

Mains power: 220-240 V

Fixture dimmable: Wireless Dim - Do not use with dimmer

LED: Yes

Built in LED: Yes

Wattage bulb included: 17

IP code: IP20

Class of protection: Class II



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.