




Superslim Ceiling 14W

Add tunable warm or cool white light to your living spaces with the WiZ Super Slim smart ceiling light. Use with the WiZ app or your voice to dim and brighten or use preset light modes on Wi-Fi setups.


PRODUCT HIGHLIGHTS

- Tunable white
- Dimensions: Ø242
- IP20/Plastic/White




Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



Create your perfect light scene

Make your own mix of different color and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.




Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



Dim your smart lights even without a dimmer

Simply adjust lights to your desired brightness level using your smartphone, the WiZ control accessory or just your voice. No need to install an expensive dimmer!



Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control, or by using the existing wall switch to toggle between two favorite modes. Works with Google Home, Alexa and Siri Shortcuts.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: Round
Dimmable: Yes

DESIGN AND FINISHING

Color: White
Material: Metal Plastic

DURABILITY

Average life (at 2.7 hrs/day): 20 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 20,000
Nominal lifetime: 20,000

EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: Not adjustable
Dimmable with remote control: Yes
LED integrated: Yes
Remote control included: No

LIGHT CHARACTERISTICS

Color consistency: <6 SDCM
Color rendering index (CRI): ≥80
Color temperature: 2700-6500 K
Warm-up time to 60% light: 2
Luminous Efficacy (rated) (Nom): 92
lm/W

MISCELLANEOUS

Especially designed for: Living Room
Dining Room Bedroom Children's
room

OTHER CHARACTERISTICS

Lamp current: 120 mA

POWER CONSUMPTION

Power factor: 0.5
Voltage: 220-240 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.43 kg
Overall height: 23 mm
Overall length: 242 mm
Overall width: 242 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Diameter: 242 mm
Total lumen output fixture: 1300
Light color: 2700-6500
Wattage bulb included: 14
IP code: IP20 | Finger-protected
Class of protection: Class II - Double
Insulated

WHAT'S SUPPORTED

Compatible with Effects: Yes
WiFi: Wireless G
Defined support period: Minimum of
60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth
WiFi (2.4GHz)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8719514553132
Net weight: 0.43 kg
Gross weight: 0.5 kg
Height: 25 cm
Length: 2.8 cm
Width: 24.5 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.