



Adria Ceiling 17W



Dim the room (without a dimmer switch!) with the WiZ Adria LED dimmable white smart ceiling light. Use with the WiZ app or your voice to turn on and off or dim and brighten the room on Wi-Fi setups.

PRODUCT HIGHLIGHTS

- Daylight
- Dimensions: Ø320
- IP20/Plastic/White




Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



Create your perfect light scene

Make your own mix of different color and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.



Illuminate with bright and cool white light

Brighten up your home with energizing cool white light. A smart light that easily adapts to your daily activities.



Dim your smart lights even without a dimmer

Simply adjust lights to your desired brightness level using your smartphone, the WiZ control accessory or just your voice. No need to install an expensive dimmer!



Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control, or by using the existing wall switch to toggle between two favorite modes. Works with Google Home, Alexa and Siri Shortcuts.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: Round
Dimmable: Yes

DESIGN AND FINISHING

Color: White
Material: Metal Plastic

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 15,000
Nominal lifetime: 15,000

EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: Not adjustable
Dimmable with remote control: Yes
LED integrated: Yes
Remote control included: No

LIGHT CHARACTERISTICS

Color consistency: 6 SDCM
Color rendering index (CRI): ≥80
Color temperature: 6500 K
Warm-up time to 60% light: 2
Luminous Efficacy (rated) (Nom): 88
lm/W

MISCELLANEOUS

Especially designed for: Living Room
Dining Room Bedroom Children's
room

OTHER CHARACTERISTICS

Lamp current: 143 mA

POWER CONSUMPTION

Power factor: 0.5
Voltage: 220-240 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.45 kg
Overall height: 68 mm
Overall length: 320 mm
Overall width: 320 mm

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Diameter: 320 mm
Total lumen output fixture: 1500
Light color: 6500
Wattage bulb included: 17
IP code: IP20 | Finger-protected
Class of protection: Class I - Earthed

WHAT'S SUPPORTED

Compatible with Effects: Yes
WiFi: Wireless G
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth WiFi (2.4GHz)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8719514553170
Net weight: 0.42 kg
Gross weight: 0.64 kg
Height: 35.2 cm
Length: 7.2 cm
Width: 35.2 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.