

PHILIPS

6 inch Eridani
Recessed Light 15W

Recessed Lights

6500/3000/4300K

White

SceneSwitch

8721103108814



One fixture. Your switch. Three light settings.

Change your room ambiance to suit whatever you're doing. With the Philips SceneSwitch LED downlight, you can easily change the setting from bright light, to natural light and to a cozy warm glow. Comfortable light that's easy on your eyes. No dimmer or additional installation required. All you need is your existing switch.

Designed for your living- and bedroom

- Perfect to relax and socialise

Light effect

- Adjustable color temperature

Eye Care

- High quality of LED light brings out vivid colors

Highlights

Perfect to relax and socialise

The living room is the heart of any home – a place where families gather to relax and guests socialise. Lighting for your living- and bedroom has to be flexible and easy to adjust to its different uses throughout the day. Careful placement of different light sources and playing with light layering

helps create the feeling of space and to give the room a warm and welcoming feel.

Adjustable color temperature

Shift seamlessly from cool white light for concentration to a more cozy glow to unwind in.

High quality LED light

Premium LED technology integrated into this Philips lamp. While instantly turned on, it enables an optimal light output and brings out vivid colors to assist kids' identification for color when drawing or reading

Specifications

Bulb characteristics

- Intended use: Indoor
- Dimmable: No

Design and finishing

- Color: White
- Material: Plastic

Durability

- Number of switch cycles: 7,500
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 100 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2
- Luminous Efficacy (rated) (Nom): 80, 86, 86 lm/W

Miscellaneous

- Especially designed for: Bedroom, Dining Room, Kitchen, Living Room
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: SceneSwitch

Other characteristics

- Lamp current: 105 mA

Power consumption

- Power factor: 0.51
- Wattage: 15 W

Product dimensions and weight

- Net weight: 0.095 kg
- Cut out length: 15.0 cm
- Cut out width: 15.0 cm
- Recessed distance: 12 mm
- Overall height: 4 mm

Service

- Warranty: 3 year(s)

Technical specifications

- Diameter: 165 mm
- Total lumen output fixture: 3000K: 12004300K: 13006500K: 1300
- Light color: 6500/3000/4300
- Mains power: AC 220–240
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated
- Number of light sources: 1

Packaging dimensions and weight

- EAN/UPC – product: 8721103108814
- Net weight: 0.1 kg
- Gross weight: 0.13 kg
- Height: 16.6 cm
- Length: 16.6 cm
- Width: 4.2 cm



Issue date: 2025-09-24
Version: 0.90

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com