

PHILIPS

Bulb 100W A65 E27
x3

LED

6500K

1450lm

15000h

8721103114303



State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- No visible flicker

Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

Choose for a sustainable solution

- Contains no mercury

Highlights

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

Replaces standard incandescent



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

Contains no mercury



No mercury allows for non-hazardous waste disposal, so this characteristic provides a simple way to make your current space more sustainable.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Plastic

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 150 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Nominal luminous flux: 1450 lm
- Luminous Efficacy (rated) (Nom): 111 lm/W

Miscellaneous

- EyeComfort: No

Packaging information

- EAN: 8721103114303
- EOC: 872110311430300
- Product title: ESS LEDBulb 13W E27 6500K 230V 3CT/4 MY

Power consumption

- Power factor: 0.5
- Voltage: AC 220-240 V
- Wattage equivalent: 100 W
- Power Consumption: 13 W

Product dimensions and weight

- Overall height: 12 mm
- Overall length: 12 mm
- Overall width: 6 mm

Rated values

- Rated peak intensity: 286 cd

Technical specifications

- Frequency: 50-60

Packaging dimensions and weight

- EAN/UPC - product: 8721103114303
- Net weight: 0.13 kg
- Gross weight: 0.16 kg
- Height: 12.7 cm
- Length: 6.1 cm
- Width: 14.9 cm



Issue date: 2025-08-20
Version: 0.13

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com