





Product Type	CCT (K)	Energy efficiency class of light source	P (W)	Vol. /Fre.	
Projectline Waterproof TW NW 60cm 2000lm			18		0.36
Projectline Waterproof TW NW 120cm 4000lm	4000	E	36	220-240V 50/60Hz	0.71
Projectline Waterproof TW NW 150cm 6000lm			53		0.83



L ± 2 mm	A mm
580	241-339
1185	846-944
1485	1146-1244



ATTENTION
OBSERVE PRECAUTIONS
FOR HANDLING
ELECTROSTATIC
SENSITIVE
DEVICES

- The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
- Product cannot be used in cold storage.
- Luminaire must not be used or stored in corrosive environments where hazardous materials such as sulphur, chlorine, phthalates, etc. are present.
- The light source which can only be replaced by the manufacturer, his service agent, or similar qualified person.
- For use in environments where no unusual accumulation of dust is expected.

