



17337/93/PN



Enjoy a beautiful garden with light

The Philips Hedgehog wall lantern in diecast aluminium adds style and strength to your wall. It distributes the light up and down for a stunning wall-washing effect. All you have to do is enjoy your garden.

Bring design into your garden

· High quality aluminum and superior synthetics

Special characteristics

- Easy installation
- Weather proof

Enjoy your outdoor life

· Create a stylish and welcoming atmosphere

Highlights

High quality material

This Philips lamp is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high quality die-cast aluminum and superior synthetics.

Easy installation



Installing a luminaire can be sometimes difficult, with this Philips outdoor lamp, you can be sure that high attention has been given to facilitate it and simplify it for you. This article is delivered with a torx key to used during installation.

Weather proof



This Philips outdoor lamp is especially designed for humid outdoor environments and has undergone rigorous tests to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This lamp is designed with IP44: it is protected against splashing water, this product is most common and ideal for general outdoor use.

Create a stylish atmosphere

This outdoor wall light is designed around the latest trends and lifestyles to blend effortlessly into your outdoor space and define the ambiance you have always desired.

Specifications

Design and finishing

Color: AnthraciteMaterial: Metal

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

• Fully weatherproof: Yes

LED integrated: No

Garden area

· Garden area: Garden & Patio

Light characteristics

Luminous Efficacy (rated) (Nom): 100 lm/W

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall LightsEyeComfort: No
- · Extra Features: Water Resistant

Product dimensions and weight

Net weight: 0.709 kgOverall height: 91 mmOverall length: 160 mmOverall width: 182 mm

Service

Warranty: 2 year(s)

Technical specifications

- Mains power: 50-60 Hz
- Energy class included light source: no bulb included
- Fitting/cap: E27
- · Wattage bulb included: -
- Maximum wattage replacement bulb: 42
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class II Double Insulated

- Light source replaceable: Yes
- Number of light sources: 1

Packaging dimensions and weight

- EAN/UPC product: 8718696157053
- Net weight: 0.71 kg
- Gross weight: 0.8 kg
- · Height: 21.1 cm
- Length: 9.5 cm
- Width: 16.6 cm



Issue date: 2025-11-12 Version: 0.428 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N V