

PHILIPS


Wawel Ceiling Light
17W

Ceiling Lights

4000/6500/2700K

White

Dimmable;SceneSwitch



31821/31/P5



Quality lighting for a cozy home

Philips myLiving WAWEL LED ceiling light comes with integrated LED to optimize light output and uniformity. Control its brightness according to your mood with step tunable and memory functions.

Light effect

- Even light distribution

Advanced LED light

- Tunable 2700-6500K

Energy saving

- 80% energy saving, compared to traditional light sources

Highlights

Even light distribution



80% energy saving



Tunable



Save up to 80% energy compared to your standard bulb. It pays for itself and saves you money year after year. So reduce your energy bill and start saving Now.

This lamp is tunable. You can tune it to your preferred light color; from warm white (2700K) to cool daylight (6500K).

Specifications

Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

Design and finishing

- Color: White
- Material: Metal, Plastic

Durability

- Number of switch cycles: 15,000
- Nominal lifetime: 20,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700-4000-6500 K
- Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 94

Miscellaneous

- Especially designed for: Kitchen, Bedroom, Dining Room, Garage, Living Room, Office
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: Dimmable, SceneSwitch

Other characteristics

- Lamp current: 130 mA

Product dimensions and weight

- Net weight: 0.64 kg
- Overall height: 66 mm
- Overall length: 350 mm
- Overall width: 350 mm

Service

- Warranty: 5 year(s)

Technical specifications

- Diameter: 350 mm
- Total lumen output fixture: 1600
- Bulb technology: LED
- Light color: Tunable white light
- Mains power: AC 220-240
- IP code: IP20 | Finger-protected
- Class of protection: Class I - Earthed

Packaging dimensions and weight

- EAN/UPC - product: 8718696162774
- Net weight: 0.64 kg
- Gross weight: 1.02 kg
- Height: 39.7 cm
- Length: 7 cm
- Width: 39.6 cm



Issue date: 2026-03-21
Version: 0.466

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com