

# PHILIPS

Halogen linear lamp

100 W

R7s cap

Clear

8711500901736



## Superior halogen lighting

Provides bright, sparkling light with superior dimmability. With its high light output, it's perfect for floodlighting gardens, terraces and other outdoor areas at night.

### **Personal scene setting**

- Best dimmiability to dims and create a cosy atmopshere

### **Create a cosy atmosphere**

- Bright halogen light provides better contrast for more focus
- Bright, sparking lighting to create your light scene at home

### **Floodlighting**

- Maximum light output to create floodlighting

# Highlights

## Best dimmability

This lamp can be used in combination with all dimmers and will not only turn down the light to 0% but also create a cosy atmosphere as you are used to with your incandescent.

## Halogen contrast for focus

With bright halogen light, contrasts get richer, letters become sharper and visibility gets better. Bright light is more relaxing for your eyes for a better focus.

## Bright, sparkling light

Clear halogen is a sparkling light, giving beautiful reflections where it shines, and sharp shadows where it doesn't. Philips halogen lamps give decorative light effect to your room, to bring your room to life.

## Maximum light output

Maximum light output to create floodlighting.

# Specifications

## Bulb characteristics

- Shape: Linear
- Socket: R7s
- Bulb Finish: Clear
- Dimmable: Yes

## Bulb dimensions

- Height: 12 mm
- Width: 78.3 mm

## Durability

- Average life (at 2.7 hrs/day): 2 year(s)
- Nominal lifetime: 2,000

## Light characteristics

- Application: Special application
- Color rendering index (CRI): 100
- Color temperature: 2800 K
- Light Color Category: Clear
- Nominal luminous flux: 1550 lm
- Luminous Flux: 1,550 lm
- Luminous Efficacy (rated) (Nom): 15.5

## Power consumption

- Voltage: 240 V
- Power: 100

## Rated values

- Rated lifetime: 2,000

## Technical specifications

- Dimmable: Yes
- Cap-Base: R7s

## Packaging dimensions and weight

- EAN/UPC - product: 8711500901736
- Net weight: 0.01 kg
- Gross weight: 0.01 kg
- Height: 16.3 cm
- Length: 1.7 cm
- Width: 3.8 cm



Issue date: 2026-03-31  
Version: 0.499

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)