



# Superior halogen lighting

Provides bright, sparkling light with superior dimmability. With its high light output, it's perfect for floodlighting gardens, terraces and other outdoor areas at night.

## Personal scene setting

• Best dimmiablity to dims and create a cosy atmopshere

# Create a cosy atmosphere

- Bright halogen light provides better contrast for more focus
- Bright, sparking lighting to create your light scene at home

# **Floodlighting**

· Maximum light output to create floodlighting

# Highlights

### **Best dimmability**

This lamp can be used in combination with all dimmers and will not only turn down the light to 0% but also create a cosy atmosphere as you are used to with your incandescent.

### Halogen contrast for focus

With bright halogen light, contrasts get richer, letters become sharper and visibility gets better. Bright light is more relaxing for your eyes for a better focus.

### Bright, sparkling light

Clear halogen is a sparkling light, giving beautiful reflections where it shines, and sharp shadows where it doesn't. Philips halogen lamps give decorative light effect to your room, to bring your room to life.

### Maximum light output

Maximum light output to create floodlighting.

# Specifications

### **Bulb characteristics**

Shape: LinearSocket: R7sDimmable: YesBulb Finish: Clear

### **Bulb dimensions**

Height: 12 mmWidth: 78.3 mm

### **Durability**

Average life (at 2.7 hrs/day): 2 year(s)

· Nominal lifetime: 2,000

# **Light characteristics**

Color rendering index (CRI): 100
Color temperature: 2800 K
Light Color Category: Clear
Nominal luminous flux: 1550 lm
Luminous Flux: 1,550 lm

· Application: Special application

 Luminous Efficacy (rated) (Nom): 15.5 lm/W

#### **Power consumption**

· Voltage: 240 V

Power Consumption: 100

### **Rated values**

• Rated lifetime: 2,000

## **Technical specifications**

Dimmable: YesCap-Base: R7s

# Packaging dimensions and weight

• EAN/UPC - product: 8711500901736

Gross weight: 0.01 kgHeight: 16.3 cmLength: 1.7 cmWidth: 3.8 cm

· Net weight: 0.01 kg



Issue date: 2025-11-01 Version: 0.499 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips