

PHILIPS

Bulb

E14

Clear

8718699754778



Appliance Oven Tubular

Reliable operation when used in special lampholders at high oven temperatures (up to 250°C). Application in electrical and standard ovens, rotisseries and similar places subject to high operating temperatures.

Specifications

Bulb characteristics

- Socket: E14
- Lamp shape code: T25

Durability

- Average life (at 2.7 hrs/day): 1 year(s)
- Nominal lifetime: 1,000

Light characteristics

- Application: Special application, General light
- Color rendering index (CRI): 100
- Color temperature: 2700 K
- Nominal luminous flux: 80 lm
- Starting time: 0.0 s

Luminaire fit

- Shape: Tubular

Power consumption

- Voltage: 230 – 240 V
- Power: 15
- Energy Consumption kWh/1000 h: 15

Technical specifications

- Lamp holder: E14
- Number of light sources: 2

Packaging dimensions and weight

- EAN/UPC – product: 8718699754778
- Net weight: 0.03 kg
- Gross weight: 0.03 kg
- Height: 6 cm
- Length: 2.6 cm
- Width: 5.2 cm



Issue date: 2025-11-29
Version: 0.145

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com