



Spot 50W PAR16 GU10

Spotlight on your comfort and well-being! These smart spots have a standard GU10 shape, but they give you something that's anything but standard: tunable white light for all your needs and moods. Schedule cool light when you need to focus, or cozy light when you want to relax—whatever works for you to live your best, most beneficial life at home. All Wi-Fi controllable using the WiZ app, WiZ remote, or your voice.

PRODUCT HIGHLIGHTS

- Tunable white smart bulb
- Up to 345 lumens
- Easy plug and play
- Control with app or voice




Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and have lights turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.



Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Create your perfect outdoor light Scene

Mix different color and white light modes to create the perfect light ambience for your perfect garden moments. Save your scene and select it anytime with app, voice or control accessory.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Lamp shape: PAR16
Socket: GU10
Type of glass: Frosted
Dimmable: Yes

BULB DIMENSIONS

Weight: 0.05 kg

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 15,000

EXTRA FEATURE/ACCESSORY INCL.

LED integrated: Yes
Solar Energy: No
Warm glow dimmable light: No

LIGHT CHARACTERISTICS

Beam angle: 36
Color consistency: 6 SDCM
Color rendering index (CRI): ≥ 90
Color temperature: 2700-6500 K
Light Color Category: Tunable white
Nominal luminous flux: 345 lm
Starting time: < 0.5 s
Warm-up time to 60% light: instant full light
Luminous Efficacy (rated) (Nom): 73

OTHER CHARACTERISTICS

Lamp current: 40 mA

PACKAGING INFORMATION

EAN: 8718699787110
EOC: 871869978711001
Product title: Wi-Fi BLE 50W GU10
927-65 TW 1PF/6

POWER CONSUMPTION

Power factor: 0.51
Voltage: 220-240 V
Wattage equivalent: 50 W
Energy Efficiency Label (EEL): G
Power: 4.7 W
Energy Consumption kWh/1000 h: 5

PRODUCT DIMENSIONS AND WEIGHT

Overall height: 58 mm
Overall length: 58 mm
Overall width: 50 mm

RATED VALUES

Rated lifetime: 15,000
Rated luminous flux: 345 lm
Rated peak intensity: 550 cd
Rated power: 4.7 W

TECHNICAL SPECIFICATIONS

Frequency: 50-60
Bulb technology: LED
EPREL Registration Number: 804321
Flux measurement reference: Narrow Cone

THE BULB

Software upgradable: Yes

WHAT'S SUPPORTED

Compatible with Effects: Yes
WiFi: 802.11b/g/n
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Compatible operating systems: iOS
Android
Communication protocol: Bluetooth
WiFi (2.4GHz)
Compatibility with 3rd party systems:
Alexa Enki Google Home Homey
IFTTT Matter Samsung Smartthings
Siri Shortcuts
Matter functionality: Via 3rd party hubs (Wi-Fi)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8718699787110
Net weight: 0.05 kg
Gross weight: 0.09 kg
Height: 16 cm
Length: 7 cm
Width: 7 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.