



Spot 50W PAR16 GU10

Bring human-centric lighting into your living and working environments with this smart WiZ LED GU10 spot beam bulb. Apply different shades of warm to cool white to help you focus or relax. You can set schedule to turn lights on and off according to your daily or weekly routines, control with your smartphone or your voice and have remote access to your lights even when you're away. WiZ lights connect to your existing Wi-Fi, no additional hardware is needed.

PRODUCT HIGHLIGHTS

- Tunable white smart bulb
- Up to 345 lumens
- Easy plug and play
- Control with app or voice

EAN: 8718699787110 wizconnected.com





Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and have lights turn on and off automatically with motion detection.It's simple. It's SpaceSense. It's WiZ.



Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



Dim your smart lights even without a dimmer

Simply adjust lights to your desired brightness level using your smartphone, the WiZ control accessory or just your voice. No need to install an expensive dimmer!



Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control, or by using the existing wall switch to toggle between two favorite modes. Works with Google Home, Alexa and Siri Shortcuts.

EAN: 8718699787110 wizconnected.com



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor Lamp shape: PAR16 Socket: GU10

Type of glass: Frosted

Dimmable: Yes

BULB DIMENSIONS

Weight: 0.05 kg

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s) Lumen maintenance factor: 70% Number of switch cycles: 50,000 Nominal lifetime: 15.000

LIGHT CHARACTERISTICS

Beam angle: 36 degree(s)
Color consistency: 6 SDCM
Color rendering index (CRI): ≥90
Color temperature: 2700-6500 K
Light Color Category: Tunable white
Nominal luminous flux: 345 lm

Starting time: <0.5 s

Warm-up time to 60% light: instant

full light

Luminous Efficacy (rated) (Nom): 70

Im/W

OTHER CHARACTERISTICS

Lamp current: 40 mA

PACKAGING INFORMATION

EAN: 8718699787110 EOC: 871869978711000

Product title: Wi-Fi BLE 50W GU10

927-65 TW 1PF/6

POWER CONSUMPTION

Power factor: 0.51 Voltage: 220-240 V Wattage equivalent: 50 W Energy Efficiency Label (EEL): G Power Consumption: 4.9 W Energy Consumption kWh/1000 h: 5

PRODUCT DIMENSIONS AND WEIGHT

Overall height: 58 mm Overall length: 58 mm Overall width: 50 mm

RATED VALUES

Rated lifetime: 15,000 Rated luminous flux: 345 lm Rated peak intensity: 550 cd

Rated power: 4.9 W

SERVICE

Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS

Frequency: 50-60

EPREL Registration Number: 804321

WHAT'S SUPPORTED

Compatible with Effects: Yes

WiFi: Wireless G

Defined support period: Minimum of 60 months after introduction date Max. number of accessories: 9999 Communication protocol: Bluetooth

WiFi (2.4GHz)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 8718699787110

Net weight: 0.05 kg Gross weight: 0.09 kg

Height: 16 cm Length: 7 cm Width: 7 cm

(s)ignify

© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

EAN: 8718699787110 wizconnected.com