



Bright LED lighting with excellent light quality

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

Designed for the comfort of your eyes

High quality LED light that lasts for decades

· Switch to extra brightness

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

EyeComfort with concaved optical design

This bulb brings a comfortable, energyefficient and long-lasting lamp with a concave design that casts a wide beam for extra brightness.

Specifications

Bulb characteristics

Intended use: IndoorLamp shape: T70Socket: E27Bulb Finish: Frosted

• Dimmable: No

Durability

Number of switch cycles: 50,000Nominal lifetime: 15,000

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

Beam angle: 150 degree(s)

· Color rendering index (CRI): 80

· Color temperature: 6500 K

. Nominal luminous flux: 2350 lm $\,$

· Warm-up time to 60% light: 0.5

Color Code: 865 | CCT of 6500K

Luminous Efficacy (rated) (Nom): 138 lm/W

Miscellaneous

• EyeComfort: Yes

LED Innovations: EyeComfort

Packaging information

• EAN: 8719514252356

• EOC: 871951425235600

 Product title: LEDBright 17W E27 6500K 230V 1PF/6 AU

Power consumption

Power factor: 0.5Voltage: 220-240 V

Wattage equivalent: 145 WPower Consumption: 17 W

• Energy Consumption kWh/1000 h: 17

Product dimensions and weight

Overall height: 125.7 mmOverall length: 125.7 mmOverall width: 70 mm

Technical specifications

• Frequency: 50-60

Packaging dimensions and weight

• EAN/UPC - product: 8719514252356

Net weight: 0.07 kgGross weight: 0.09 kg

Height: 16 cmLength: 7 cm

· Width: 7 cm



Issue date: 2025-11-01 Version: 0.233 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips