

PHILIPS


Downlight

Recessed Lights

3000/4000/6500K

White

Dimmable; Water Resistant



8719514317314



Trusted performance, everyday. Tri-colour enabled downlight.

With its robust design and optimal performance, Philips LED Performance downlight is the perfect luminaire that brings quality and brightness to any home spaces. Comfortable light that's easy on your eyes.

Light effect

- Available in Warm White, Cool White or Cool Daylight

Safety

- No harmful UV radiation
- IP54 seal rating. Ideal for balconies or moist areas. Direct spray of water to be avoided.

Control

- Dimmable

Durability

- Long life span up to 30,000 hours
- Energy saving

Highlights

Available in Warm White, Cool White or Cool Daylight

Different light colors can affect mood: warm white is perfect for relaxation, cool white for concentration and cool daylight for energizing you

No harmful UV radiation

The product is designed to eliminate any potentially harmful UV radiation.

IP54 seal rating. Ideal for balconies or moist areas. Direct spray of water to be avoided.

This means the product can withstand moisture, so you can use it on balconies, porches and similar areas.

Dimmable

Allows you to change the mood by reducing LED brightness levels, from bright white light, to a cozy glow - just like traditional lamps.

Long life span up to 30,000 hours

Philips LED technology extends your product's lifetime up to 30,000 hours.

Energy saving

Saves energy - which is good for your bills, and the environment.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Metal, Plastic

Durability

- Number of switch cycles: 15,000
- Nominal lifetime: 30,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 100
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700-4000-6500 K
- Luminous Efficacy (rated) (Nom): 106

Miscellaneous

- Especially designed for: Bathroom, Kitchen, Bedroom, Dining Room, Living Room, Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- Extra Features: Dimmable, Water Resistant

Other characteristics

- Lamp current: 38 mA

Product dimensions and weight

- Net weight: 0.23 kg
- Recessed distance: 0 mm
- Overall height: 56 mm
- Overall length: 114 mm
- Overall width: 114 mm
- Recessed Ceiling cutout: 9.0 cm x 9.0 cm

Service

- Warranty: 3 year(s)

Technical specifications

- Diameter: 114 mm
- Total lumen output fixture: 800
- Bulb technology: LED
- Light color: Tunable white light
- Mains power: AC 220-240
- Fixture dimmable: Yes
- Wattage bulb included: 7.5
- IP code: IP20 | Finger-protected, IP54 | Dust-accumulation-protected and splash-proof
- Class of protection: Class II - Double Insulated

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8719514317314
- Net weight: 0.92 kg
- Gross weight: 1.03 kg
- Height: 12.5 cm
- Length: 13 cm
- Width: 23 cm



Issue date: 2026-04-15
Version: 0.156

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com