



A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

· No visible flicker

Choose for a sustainable solution

• You can trust what the Philips packaging is saying.

Create the right light for your home

· A simple LED for everyday use

Highlights

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because

Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won $\phi_{\overline{1}}$ t fade.

A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

Specifications

Bulb characteristics

· Intended use: Indoor

· Lamp shape: Non directional candle

Socket: B15Dimmable: NoBulb Finish: Clear

Durability

• Number of switch cycles: 20,000

• Nominal lifetime: 15,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

· Color rendering index (CRI): 80

• Color temperature: 2700 K

• Nominal luminous flux: 470 lm

• Warm-up time to 60% light: 0.5

• Color Code: 827 | CCT of 2700K

 Luminous Efficacy (rated) (Nom): 109 lm/W

Miscellaneous

· EyeComfort: Yes

· LED Innovations: EyeComfort

Packaging information

• EAN: 8719514327405

EOC: 871951432740500Product title: LED classic 40W B35

B15 WW CL ND

Power consumption

Power factor: 0.41Voltage: 220-240 V

• Wattage equivalent: 40 W

• Power Consumption: 4.3 W

Product dimensions and weight

· Overall height: 97 mm

· Overall length: 97 mm

• Overall width: 35 mm

Technical specifications

Frequency: 50-60

Packaging dimensions and weight

• EAN/UPC - product: 8719514327405

Net weight: 0.01 kg

· Gross weight: 0.03 kg

· Height: 14 cm

· Length: 4.5 cm

• Width: 4.5 cm



Issue date: 2025-11-01 Version: 0.107

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips