



# A light bulb like no other

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

# High quality light

• Designed for the comfort of your eyes

# Light beyond illumination

• Dims to a warm glow

# Designed to be seen, looks good on and off

· Looks good on and off

# Highlights

# Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Dims to a warm glow

With this dimmable bulb, you can dim from a 2200k warm light to a 2700K light. The more you dim, the warmer the light...

# Looks good on and off



"These beautiful lamp with visible filament add a sense of styleand nostalgia to any room. Looks good on and off."

# Specifications

#### **Bulb characteristics**

· Intended use: Indoor

· Lamp shape: Non directional globe

Socket: E27Dimmable: Yes

#### **Durability**

• Number of switch cycles: 20,000

• Nominal lifetime: 15,000

# **Environmental**

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

# **Light characteristics**

· Beam angle: 270 degree(s)

· Color rendering index (CRI): 80

· Color temperature: 2200 K

· Nominal luminous flux: 650 lm

· Warm-up time to 60% light: 0.5

· Color Code: 822 | CCT of 2200K

Luminous Efficacy (rated) (Nom): 90 lm/W

#### Miscellaneous

EveComfort: Yes

· LED Innovations: EyeComfort

· Extra Features: Dimmable, Decorative

# **Packaging information**

• EAN: 8719514338845

• EOC: 871951433884500

 Product title: LEDclassic7.2-50W G120E27 2200KGOLD CL D

#### **Power consumption**

• Power factor: 0.7

· Voltage: 220-240 V

· Wattage equivalent: 50 W

• Power Consumption: 7.2 W

• Energy Consumption kWh/1000 h: 8

# Product dimensions and weight

• Overall height: 180 mm

• Overall length: 180 mm

Overall width: 125 mm

#### **Technical specifications**

• Frequency: 50-60

# Packaging dimensions and weight

• EAN/UPC - product: 8719514338845

Net weight: 0.1 kgGross weight: 0.2 kg

Height: 22.6 cmLength: 12.8 cmWidth: 12.8 cm



Issue date: 2025-10-22 Version: 0.131 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips