



Experience dimmable, warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

Choose for a sustainable solution

· Saves up to 90% Energy

Create the right light for your home

· Perfect for general room lighting

Highlights

Saves up to 90% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 90% in energy by replacing your existing incandescent or halogen bulbs

Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

Specifications

Bulb characteristics

· Intended use: Indoor

· Lamp shape: Non directional globe

Socket: E27Dimmable: YesBulb Finish: ClearBulb Material: Glass

Durability

• Number of switch cycles: 20,000

• Ambient temperature range: -20 to $+45\,^{\circ}\mathrm{C}$

Nominal lifetime: 15.000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

· Color rendering index (CRI): 90

· Color temperature: 2700 K

· Nominal luminous flux: 806 lm

· Warm-up time to 60% light: 0.5 s

· Color Code: 927 | CCT of 2700K

Correlated Color Temperature (Nom):
 2700 K

· Luminous Flux: 806 lm

• Luminous Efficacy (rated) (Nom): 134

Miscellaneous

• Extra Features: Dimmable

Other characteristics

• EU RoHS compliant: Yes

Packaging information

• EAN: 8719514385887

• EOC: 871951438588700

 Product title: LEDclassic 60W E27 2700K G120 D CL AU

Power

• Power Factor (Fraction): 0.7

Power consumption

Power factor: 0.7Voltage: 220-240 V

Wattage equivalent: 60 WPower Consumption: 6 W

• Energy Consumption kWh/1000 h: 6

Product dimensions and weight

Overall height: 178 mmOverall length: 178 mmOverall width: 124 mm

Rated values

· Rated lifetime: 15,000

Technical specifications

Frequency: 50-60Diameter: 124 mm

• Dimmable: Only with specific

dimmers
• Cap-Base: E27

Packaging dimensions and weight

• EAN/UPC - product: 8719514385887

Net weight: 0.17 kgGross weight: 0.23 kgHeight: 22.6 cmLength: 12.9 cm

• Width: 12.9 cm



Issue date: 2025-11-01 Version: 0.75 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips