



Comfortable LED light that's easy on your eyes

With its robust design and optimal performance, Philips LED Performance desk light is the perfect luminaire that brings quality and brightness to any home spaces. Comfortable light that's easy on your eyes.

Premium quality

• EyeComfort - light that's easy on the eyes

Highlights

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria

including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philip s LED bulbs not only deliver comfortable light, but also stay that

way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Specifications

Bulb characteristics

Intended use: IndoorLamp shape: Rectangle

Design and finishing

Color: WhiteMaterial: Plastic

Durability

Average life (at 2.7 hrs/day): 15 year(s)

Lumen maintenance factor: 70%

Number of switch cycles: 50,000

· Nominal lifetime: 15,000

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- · Adjustable spot head: Not adjustable
- · Dimmable with remote control: No
- LED integrated: Yes
- · Remote control included: No

Light characteristics

- · Color consistency: 6 SDCM
- · Color rendering index (CRI): 90
- Color temperature: 2700-4000-6500 K
- Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 161 lm/W

Miscellaneous

 Especially designed for: Bedroom, Living Room, Office

Style: Contemporary

Type: Desk Lights

EyeComfort: Yes

· Extra Features: Dimmable

Other characteristics

· Lamp current: 900 mA

Product dimensions and weight

Net weight: 0.37 kg

• Overall height: 390 mm

• Overall length: 155 mm

• Overall width: 94 mm

Service

Warranty: 2 year(s)

Technical specifications

Total lumen output fixture: 80

• Light color: 3000/4000/5700

• Mains power: 5 V

• Battery type: 18650

· Fixture dimmable: Yes

· Wattage bulb included: 4.5

• IP code: IP20 | Finger-protected

Class of protection: Class III - Safe

Extra Low Voltage

Packaging dimensions and weight

• EAN/UPC - product: 8719514443778

· Net weight: 0.37 kg

· Gross weight: 0.44 kg

· Height: 26.6 cm

· Length: 10 cm

• Width: 10 cm



Issue date: 2025-11-01 Version: 0.404 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.