



Bright LED lighting with excellent light quality

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

• Designed for the comfort of your eyes

Choose for a sustainable solution

- · Saves up to 90% Energy
- · Long life bulb Lasts up to 50 years

Designed to be seen, looks good on and off

· Classic glass LED

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Saves up to 90% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 90% in energy by replacing your existing incandescent or halogen bulbs

Long life bulb - Lasts up to 50 years



With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 50 years.

Specifications

Bulb characteristics

· Intended use: Indoor

· Lamp shape: Non directional bulb

Socket: E27Dimmable: NoBulb Finish: ClearBulb Material: Glass

Durability

Number of switch cycles: 50,000
Ambient temperature range: -20 to +45 °C

· Nominal lifetime: 50,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Glass Clear Design

The look you love, the performance you expect. Classic clear glass designs that replicate the beautiful sparkling light of traditional bulbs, for a perfect fit throughout your home.

Light characteristics

· Color rendering index (CRI): 80

• Color temperature: 4000 K

• Nominal luminous flux: 485 lm

· Warm-up time to 60% light: 0.5 s

· Color Code: 840 | CCT of 4000K

• Correlated Color Temperature (Nom):

4000 K

· Luminous Flux: 485 lm

• Luminous Efficacy (rated) (Nom): 210

lm/W

Miscellaneous

EyeComfort: Yes

 LED Innovations: UltraEfficient, EyeComfort

Other characteristics

• EU RoHS compliant: Yes

Packaging information

· EAN: 8719514454958

• EOC: 871951445495800

• Product title: LED CLA 40W A60 E27

4000K CL EELA SRT AU

Power

• Power Factor (Fraction): 0.4

Power consumption

Power factor: 0.4Voltage: 220-240 V

• Wattage equivalent: 40 W

• Power Consumption: 2.3 W

Product dimensions and weight

Overall height: 105 mmOverall length: 105 mm

· Overall width: 60 mm

Rated values

· Rated lifetime: 50,000

Technical specifications

Frequency: 50-60Diameter: 60 mm

Dimmable: NoCap-Base: E27

Packaging dimensions and weight

• EAN/UPC - product: 8719514454958

Net weight: 0.04 kgGross weight: 0.06 kg

Height: 14.6 cmLength: 6.6 cm

· Width: 6.4 cm



Issue date: 2025-11-01 Version: 0.64 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N V