

8719514470934



Bright LED lighting with excellent light quality

Familiar shapes you know and love. They use around 80% less energy than traditional light bubls and last ten times longer.

High quality light

· No visible flicker

Choose for a sustainable solution

· Long life bulbs - Lasts up to 15 years

Highlights

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's

output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

Bulb characteristics

Intended use: Indoor

Lamp shape: Non directional reflector

Socket: E27
Dimmable: No
Bulb Finish: Frosted
Bulb Material: Plastic

Durability

• Number of switch cycles: 50,000

· Nominal lifetime: 15,000

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

• Beam angle: 120 degree(s)

· Color rendering index (CRI): 80

· Color temperature: 2700 K

· Nominal luminous flux: 1150 lm

Warm-up time to 60% light: instant

full light

· Color Code: 827 | CCT of 2700K

· Luminous Efficacy (rated) (Nom): 115

lm/W

Miscellaneous

· EyeComfort: No

Packaging information

• EAN: 8719514470934

• EOC: 871951447093400

• Product title: LEDspot 10W E27

2700K R80 1PF/6 NZ

Power consumption

• Power factor: 0.51

· Voltage: 220-240 V

· Wattage equivalent: 80 W

• Power Consumption: 10 W

Product dimensions and weight

· Overall height: 115 mm

• Overall length: 115 mm

· Overall width: 80 mm

Technical specifications

• Frequency: 50-60

Packaging dimensions and weight

• EAN/UPC - product: 8719514470934

Net weight: 0.05 kgGross weight: 0.07 kg

Height: 11.3 cmLength: 7.8 cmWidth: 7.8 cm



Issue date: 2025-11-01 Version: 0.65 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips