









Our most energyefficient LED lights yet

Philips has developed an UltraEfficient solar LED outdoor light that uses new technology to cut carbon emissions, reduce material waste, and lower energy usage. With an amazing 50,000 hour lifetime it lasts more than 5 times longer than the Philips LED outdoor light equivalents. Just what is needed for a more sustainable planet.

Easy installation

· No wiring requried

Sustainable light solutions

- · Long lifetime up to 50,000 hours
- · Ultra Efficient Solar

Advanced LED light

• 5 year warranty on LED system

Premium quality

· High quality aluminum and superior synthetics

Designed for outdoors

· IP44 - weather proof

Special characteristics

- Dual-brightness light
- · Motion and Dusk-to-dawn sensor integrated

Highlights

No wiring requried



This light is powered entirely by solar energy. No wiring is needed, making these lights easy to position and reposition anywhere in your garden or other outdoor area.

Long lifetime up to 50,000 hours



Reliable high-quality LED light lasts up to 50,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while enjoying the perfect garden light every night.

Ultra Efficient Solar



With the Philips Ultra Efficient Solar system, these luminaires provide light for up to 40 hours on a fully-charged battery. Enjoy bright light all night, or even in bad or overcast weather conditions.

5 year warranty on LED system



In addition to the standard 2-year warranty offered for this luminaire, Philips also offers a 5-year warranty on the LED system (the LED module and driver).

High quality aluminum and superior synthetics



This Philips light is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high quality die-cast aluminum and superior synthetics.

IP44 - weather proof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water—perfect for general outdoor use.

Dual-brightness light

Create a flexible and appealing ambiance with the dual-brightness feature. The light dims when idle and automatically brightens when people are present, delivering the right level of light whenever you need it.

Motion and Dusk-to-dawn sensor integrated



With a built-in motion sensor, these lights automatically welcome you when you return home after dark, or light up when visitors arrive. The unique dusk-to-dawn feature turns the lights on automatically when it gets dark outside--perfect for those long summer evenings or to ensure your safety.

Specifications

Design and finishing

Color: AnthraciteMaterial: Metal

Durability

· Nominal lifetime: 50,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- · Adjustable spot head: Not adjustable
- · Anti rust anti dust: Yes
- · Bi-directional light beams: No
- · click!FIX mounting: Yes
- · Day-and-night sensor: Yes
- Fully weatherproof: Yes
- · LED integrated: Yes
- · Motion sensor: Yes
- · Solar Energy: Yes
- · Warm White Light: No
- Centerpiece: No

Garden area

· Garden area: Garden & Patio

Light characteristics

- · Color rendering index (CRI): 80
- · Color temperature: 3000 K

Miscellaneous

- Especially designed for: Garden, Patio
- Style: ContemporaryType: Wall Lights

EyeComfort: No

- LED Innovations: UltraEfficient
- Extra Features: Sensor, Solar, Water Resistant

Product dimensions and weight

Net weight: 0.7 kgOverall height: 188 mmOverall length: 184 mm

· Overall width: 158 mm

Service

· Warranty: 2 year(s)

Technical specifications

- · Total lumen output fixture: 250
- Light color: 3000
- Mains power: 4 V
- Fixture dimmable: No
- Energy class included light source: A
- Maximum wattage replacement bulb:
 12
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class III Safe Extra Low Voltage
- · Light source replaceable: No

Packaging dimensions and weight

- EAN/UPC product: 8719514476912
- Net weight: 0.65 kgGross weight: 1 kg
- Height: 20 cmLength: 17.5 cm
- Width: 21.5 cm



Issue date: 2025-11-19 Version: 0.394 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips