



Selectable colour temperatures help you to make the right choice

Philips LED light bulbs provide a beautiful light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

High quality light

• Designed for the comfort of your eyes

Choose for a sustainable solution

· Long life bulbs - Lasts up to 15 years

Light beyond illumination

Instant on

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home. Instant on

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

Bulb characteristics

- · Intended use: Indoor
- · Lamp shape: Non directional bulb
- Socket: E27Dimmable: NoBulb Finish: FrostedBulb Material: Plastic

Durability

- Number of switch cycles: 50,000
- Ambient temperature range: -20 °C to 45 °C
- · Nominal lifetime: 15,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 200 degree(s)
- · Color rendering index (CRI): 80
- Color temperature: 3000-4000-6500 K
- · Nominal luminous flux: 700 lm
- Warm-up time to 60% light: 0.5 s
- · Color Code: 3000/4000/6500
- Correlated Color Temperature (Nom): 3000, 4000, 6500 K
- · Luminous Flux: 700 lm
- Luminous Efficacy (rated) (Nom): 116 lm/W

Miscellaneous

- EveComfort: Yes
- · LED Innovations: EyeComfort

Other characteristics

• EU RoHS compliant: Yes

Packaging information

EAN: 8719514478930EOC: 871951447893000

 ${\boldsymbol \cdot}$ Product title: LEDStick 6W E27 DS FR

ND 1CT/6 AU

Power

• Power Factor (Fraction): 0.4

Power consumption

Power factor: 0.4Voltage: 220-240 VWattage equivalent: 50 WPower Consumption: 6 W

Product dimensions and weight

Overall height: 108 mmOverall length: 108 mmOverall width: 37 mm

Rated values

• Rated lifetime: 15,000

Technical specifications

Frequency: 50-60Diameter: 37 mmDimmable: No

• Line Frequency: 50 to 60

· Cap-Base: E27

Packaging dimensions and weight

• EAN/UPC - product: 8719514478930

Net weight: 0.04 kgGross weight: 0.05 kgHeight: 11.1 cm

Length: 4 cmWidth: 4 cm



Issue date: 2025-10-25 Version: 0.78 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.