

PHILIPS

Bulb 50W Stick B22

LED

3000/4000/6500K

700lm

15000h

8719514478954



Selectable colour temperatures help you to make the right choice

Philips LED light bulbs provide a beautiful light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

High quality light

- Designed for the comfort of your eyes

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

Light beyond illumination

- Instant on

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Instant on

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Plastic

Durability

- Number of switch cycles: 50,000
- Ambient temperature range: -20 °C to 45 °C
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Beam angle: 200 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000-4000-6500 K
- Nominal luminous flux: 700 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 3000/4000/6500
- Correlated Color Temperature (Nom): 3000, 4000, 6500
- Luminous Flux: 700 lm
- Luminous Efficacy (rated) (Nom): 116

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- EU RoHS compliant: Yes

Packaging information

- EAN: 8719514478954
- EOC: 871951447895400
- Product title: LEDStick 6W B22 DS FR ND 1CT/6 AU

Power

- Power Factor (Fraction): 0.4

Power consumption

- Power factor: 0.4
- Voltage: 220–240 V
- Wattage equivalent: 50
- Power: 6

Product dimensions and weight

- Overall height: 107 mm
- Overall length: 107 mm
- Overall width: 37 mm

Rated values

- Rated lifetime: 15,000

Technical specifications

- Frequency: 50–60
- Diameter: 37 mm
- Bulb technology: LED
- Dimmable: No
- Line Frequency: 50 to 60
- Cap-Base: B22

Packaging dimensions and weight

- EAN/UPC - product: 8719514478954
- Net weight: 0.04 kg
- Gross weight: 0.05 kg
- Height: 11.1 cm
- Length: 4 cm
- Width: 4 cm



Issue date: 2026-03-21
Version: 0.78

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com